





## Wobble extensions



*Inaccessible with a socket or a universal joint?  
Use a wobble extension!*



### R.S 1/4" drive wobble extensions

- Square drive profile gives 6° working angle.

	B	D	L	ΔΔ
	mm	mm	mm	g
<b>R.209S</b>	8,2	12	55	30
<b>R.210S</b>	8,2	12	100	45




### R 1/4" drive flexible extension 150 mm

#### R.216

- Reaches fasteners out of direct access line.
- Unsuitable for high torques : max. 2.8 N.m.

ΔΔ : 66 g.




### 1/4" universal joint

#### R.240A

- ▷ Performance : to ISO 3316, DIN 3123, NF ISO 3316.
- Spring-stiffened joints. Stays in position when reaching for fasteners.

- Significant time savings.

ΔΔ : 20 g.



### 1/4" to 3/8" coupler

#### R.232

- 1/4" female to 3/8" male square drive.
- For adapting 3/8" drive sockets.

ΔΔ : 16 g.

