

Intashield IX-400/450 PCI Express 4 Port RS232

PRODUCT INFORMATION

- IX-400 Standard height
 Bracket Height = 120mm
- IX-450 Low profile Bracket Height = 80mm

OPERATING SYSTEMS:

- Windows 7 32/64 bit
- Windows Vista 32/64 bit
- Windows XP 32/64 bit

PRODUCT FEATURES:

- 4x9 pin, D type RS232 Serial Ports on adaptor cable 44 Way D Female to 4x9 Way D Male
- PCI Express Bus will fit into any PCIe slot i.e.
 x1, x4, x8 & x16 lane
- Fully Plug & Play simple installation and test software provided
- 1 year Warranty with option to sign up for additional free year

SPECIFICATIONS:

UART: 16550

• Speed: 115,200 maximum baud rate

Data Bits: 5, 6, 7 or 8Stop Bits: 1, 1.5 or 2

Parity: odd, even, none, mark or space

FIFO Size: 16 byteOuad Cable included

IX-400/450

This card provides 4 industry standard 9 pin RS232 serial COM ports in a single PCI Express slot. As PCI Express is fully Plug and Play compatible your BIOS and operating system will automatically configure the card ensuring conflict free installation. Choose between standard height and low profile options.

IX-400

