



Sta-Kon®

Ring Terminal
T&B Catalog Number:

UPC Number: 10RC-10
Status: 78621080042
Description: Active

Insulated Vinyl Ring Terminal For Wire Range 12-10 Stud Size #10, Yellow

WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

These terminals are self-insulated with a PVC insulation sleeve of extra length to give protection and relieve bending stress at wire's flex point. Brazed seam barrel is serrated to obtain high pull-out value.

General

| | |
|-----------------|---------------------|
| Insulation Type | Insulated Vinyl |
| Terminal Series | RC |
| Material | Copper |
| Finish | Electro -Tin Plated |
| Color | Yellow |
| Wire Range | 12-10 |
| Stud Size | #10 |

Dimension Information

| | |
|-----------------------------|------|
| Maximum Insulation (inches) | .210 |
| Stock Thickness | .04 |
| A (inches) | 1.06 |
| B (inches) | .31 |
| C (inches) | .27 |
| M (inches) | .90 |

Specifications


| | |
|---------------------|-----------|
| Temperature Rating | 105°C |
| Voltage Rating | 600V |
| Flammability Rating | UL 94 V-0 |

Tooling

| | |
|-------------------|--|
| Tool Charts | Available on Website |
| Application Tools | WT145C, WT2000, WT112M, ERG4001, ERG4003 |
| Recommended Tool | ERG4001 |

Packaging

| | |
|-----------------------|-------------------|
| T&B Order Multiple | 50 |
| T&B Inner Pack | 50 |
| Package in Units | 250 |
| Package Type | Standard |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 0.52 lbs. per 100 |
| Alternate Package Qty | RC367 |



Application Support

| | |
|-------------------|----------------------|
| Overview | Available on Website |
| Wire Guide Tables | Available on Website |

Certifications

| | |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

Certifications



File Nbr:
E9809