

# Catamount®

**Blade Terminal**  
**T&B Catalog Number:**

TV18-10BL-L

**UPC Number:**

78620993782

**Status:**


Active

**Description:**

Insulated Vinyl Blade Terminal for Wire Range 22-16 , Red

**Features**

For use in DIN-Style Blade Terminal blocks. Molded Funnel Entry Insulator. Brazed Seam. Internal Barrel Serrations.



**General**

Insulation Type	Insulated Vinyl
Material	Copper
Finish	Electro -Tin Plated
Color	Red
Wire Range	22-16

**Dimension Information**

d1 (inches)	.067
D (inches)	.157
E (inches)	.433
F (inches)	.394
L (inches)	.819
T (inches)	.030
W (inches)	.091

**Specifications**

Temperature Rating	75°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

**Tooling**

Application Tools	WT112M, CM2000A
-------------------	-----------------

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	0.2 lbs. per 100

**Certifications**



File Nbr:

E9809