

PICCOLO PC B 65 G



Sample photo

Order symbol: PC B 65 G
Product nbr: 8724303
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074001955
El. number:
Finland: 3423401
Denmark: 8212001475
Italy: 7201010
Sweden: 2536801
Norway: 2536501

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

| Dimensions: | | Length | Width | Height | Rating: |
|-------------------------------|--|----------------------------|-------|--------|--|
| mm: | | 110 | 80 | 65 | Ingress Protection (EN 60529): IP 66/67 |
| inch: | | 4.3 | 3.1 | 2.6 | Impact Resistance (EN 62262): IK 08 |
| Materials: | | | | | Electrical insulation: Totally insulated |
| Material: | | Polycarbonate | | | Halogen free (DIN/VDE 0472, Part 815): Yes |
| Base colour: | | RAL 7035 | | | UV resistance: UL 508 |
| Cover colour: | | RAL 7035 | | | Flammability Rating (UL 746 C 5): UL 746C 5V |
| Cover screws material: | | Polyamide | | | Glow Wire Test (IEC 695-2-1) °C: 960 |
| Cover screws colour: | | Grey | | | NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13 |
| Gasket material: | | Polyurethane | | | |
| Temperatures: | | | | | Certificates: |
| Short term: | | -40 ... 120 °C | | | Germanischer Lloyd (GL) |
| Continuous: | | -40 ... 80 °C | | | Underwriters Laboratories |
| Short term: | | -40 ... 250 °F | | | Fimko |
| Continuous: | | -40 ... 175 °F | | | Europe EN 62208: 2003 |
| Accessories: | | | | | UL Canada |
| B-MP | | Mounting plate | | | Gost R |
| B-3 | | DIN-35 Mounting rail | | | |
| FP 22040 | | Wall fastening lug (2 pcs) | | | |

PICCOLO 110x80x65-85

