

**FEX FEX 1919 13 G**



Sample photo

**Order symbol:** FEX 1919 13 G  
**Product nbr:** 4130800  
**Description:** Enclosure, PC  
**Remarks:** Ex e II, EN 60079; IK 4J

**EAN:** 6418074007872  
**El. number:**  
 Finland: 3424637  
 Denmark: 8212026308  
 Italy: 7801110  
 Sweden: 4130800  
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

**Dimensions:**      **Length**      **Width**      **Height**      **Rating:**

<b>mm:</b>	188	188	130	Ingress Protection (EN 60529): IP 54
<b>inch:</b>	7.4	7.4	5.1	Impact Resistance (EN 50014): 4J

**Materials:**

<b>Material:</b>	Polycarbonate
<b>Base colour:</b>	RAL 7035
<b>Cover colour:</b>	RAL 7035
<b>Cover screws material:</b>	Polyamide
<b>Cover screws colour:</b>	Grey
<b>Gasket material:</b>	Silicone

**Certificates:**

ATEX  
 EC Certificate of Conformity

**Temperatures:**

<b>Short term:</b>	-40 ... 120 °C
<b>Continuous:</b>	-10 ... 80 °C
<b>Short term:</b>	-40 ... 250 °F
<b>Continuous:</b>	14 ... 175 °F

**Accessories:**

EKHVT	Mounting plate
EKJVT	Mounting plate
EKMVT	Mounting plate
EKOVT	Mounting plate
EKPVT	Mounting plate
EKTVT	Mounting plate
EKUVT	Mounting plate
EKV 12	DIN-35 Mounting rail
EKV 22	DIN-35 Mounting rail
EKV 32	DIN-35 Mounting rail

