

**CAB CAB PC 403018 G**



Sample photo

**Order symbol:** CAB PC 403018 G  
**Product nbr:** 8113350  
**Description:** Cabinet, PC  
**Remarks:** Latches on the long side

**EAN:** 6418074020208  
**El. number:**  
 Finland: 3424114  
 Denmark: 8212020249  
 Italy: 7821040  
 Sweden: 2539971  
 Norway:

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		400	300	180	Ingress Protection (EN 60529): IP 65
<b>inch:</b>		15.7	11.8	7.1	Impact Resistance (EN 62262): IK 08
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7035			UV resistance: UL 508
<b>Cover colour:</b>		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
<b>Gasket material:</b>		EPDM			Glow Wire Test (IEC 695-2-1) °C: 960
					UL Type: UL TYPE 1, 4, 4X, 12, 13
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 120 °C			Germanischer Lloyd (GL)
<b>Continuous:</b>		-40 ... 80 °C			Underwriters Laboratories
<b>Short term:</b>		-40 ... 250 °F			Fimko
<b>Continuous:</b>		-40 ... 175 °F			Lloyds Register of Shipping (LR)
<b>Accessories:</b>					Europe EN 62208: 2003
EKIV 43		Mounting plate			UL Canada
EKIV 43 PL		Mounting plate, Plastic			Gost R
EKIV 27		DIN-35 Mounting rail			
DS35270E1		DIN-35 Mounting rail			
EKIV 37		DIN-35 Mounting rail			
DS35370E1		DIN-35 Mounting rail			
FP A 43		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 43		Front plate			
FP 12x2-43		Front plate			
FP 12x3-43		Front plate			
DRF 43/44		DIN rail frame set			

