

CAB CAB PC 504020 G



Sample photo

Order symbol: CAB PC 504020 G
Product nbr: 8113360
Description: Cabinet, PC
Remarks: Latches on the long side

EAN: 6418074020321
El. number:
 Finland: 3424120
 Denmark: 8212020265
 Italy: 7821055
 Sweden: 2539977
 Norway:

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

| Dimensions: | | Length | Width | Height | Rating: |
|-------------------------|--|----------------------------|-------|--------|--|
| mm: | | 500 | 400 | 200 | Ingress Protection (EN 60529): IP 65 |
| inch: | | 19.7 | 15.7 | 7.9 | Impact Resistance (EN 62262): IK 08 |
| Materials: | | | | | Electrical insulation: Totally insulated |
| Material: | | Polycarbonate | | | Halogen free (DIN/VDE 0472, Part 815): Yes |
| Base colour: | | RAL 7035 | | | UV resistance: UL 508 |
| Cover colour: | | RAL 7035 | | | Flammability Rating (UL 746 C 5): UL 746C 5V |
| Gasket material: | | EPDM | | | Glow Wire Test (IEC 695-2-1) °C: 960 |
| Temperatures: | | | | | UL Type: UL TYPE 1, 4, 4X, 12, 13 |
| Short term: | | -40 ... 120 °C | | | Certificates: |
| Continuous: | | -40 ... 80 °C | | | Germanischer Lloyd (GL) |
| Short term: | | -40 ... 250 °F | | | Underwriters Laboratories |
| Continuous: | | -40 ... 175 °F | | | Fimko |
| Accessories: | | | | | Lloyds Register of Shipping (LR) |
| EKIV 54 | | Mounting plate | | | Europe EN 62208: 2003 |
| EKIV 37 | | DIN-35 Mounting rail | | | UL Canada |
| DS35370E1 | | DIN-35 Mounting rail | | | Gost R |
| EKIV 47 | | DIN-35 Mounting rail | | | |
| DS35470E1 | | DIN-35 Mounting rail | | | |
| FP A 54 | | Swing-out door/Front plate | | | |
| MB 12225 AL | | Swing door set | | | |
| FP 54 | | Front plate | | | |
| FP 18X2-54 | | Front plate | | | |
| DRF 54 | | DIN rail frame set | | | |

