

**EK EKPE 130 G-2FSH**



Sample photo

**Order symbol:** EKPE 130 G-2FSH  
**Product nbr:** 9996207  
**Description:** Enclosure, PC  
**Remarks:** Grey hinged cover

**EAN:** 6418074053060  
**El. number:**  
 Finland: 3435842  
 Sweden: 9996207  
 Norway:

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		380	280	130	Ingress Protection (EN 60529): IP 65
<b>inch:</b>		15.0	11.0	5.1	Impact Resistance (EN 62262): IK 08
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
<b>Base colour:</b>		RAL 7035		UV resistance: UL 508	
<b>Cover colour:</b>		RAL 7035		Flammability Rating (UL 746 C 5): UL 746C 5V	
<b>Cover screws material:</b>		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Cover screws colour:</b>		Grey		NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
<b>Gasket material:</b>		Polyurethane			
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 120 °C		Gost R	
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			

**Accessories:**

EKPE	Base, PC
EKPG	Base, PC
EKP 30-G	Cover
EKP 80-G	Cover
EKP 30-T	Cover
EKP 80-T	Cover
EKPVT	Mounting plate
EKPXT	Mounting plate Pertinax
EKV 22	DIN-35 Mounting rail
EKV 32	DIN-35 Mounting rail
EKPZR	Extension frame

