

CAB CAB ABS 604022 G3B



Sample photo

Order symbol: CAB ABS 604022 G3B
Product nbr: 8183372
Description: Cabinet, ABS, Grey door
Remarks: Locks on the long side

EAN: 6418074020505
El. number:
 Finland: 3424328
 Denmark: 8212019085
 Italy: 7811070
 Sweden: 2540085
 Norway:

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Rating:
mm:		600	400	220	Ingress Protection (EN 60529): IP 65
inch:		23.6	15.7	8.7	Impact Resistance (EN 62262): IK 08
Materials:					
Material:		ABS			Electrical insulation: Totally insulated
Base colour:		RAL 7035			Halogen free (DIN/VDE 0472, Part 815): Yes
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Gasket material:		EPDM			Glow Wire Test (IEC 695-2-1) °C: 650
Temperatures:					
Short term:		-40 ... 80 °C			NEMA Class: NEMA 1, 4, 4X, 12, 13
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
EKIV 64H		Mounting plate			
EKIV 37		DIN-35 Mounting rail			
DS35370E1		DIN-35 Mounting rail			
FP A 64		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 64		Front plate			
FP 18x3-64		Front plate			
DRF 63/64		DIN rail frame set			
Certificates:					
Fimko					
Europe EN 62208: 2003					
Gost R					

