


Two Post Mounting Cantilever Shelf *RAS Series*

Features



- Allows easy rack mounting of narrow equipment or items that do not have rack mounting capabilities.
- Shelves feature formed 16-gauge steel construction.
- Front & back edge folded - acting as both stiffeners and equipment retainers.
- Mounts to rack rails either as an internal shelf or external shelf/work area
- Choice of two depths - 7" or 14.5"
- Available in either vented or unvented versions
- Shelves include tie down slots on each side & four tie down holes.
- Rugged textured - black powder paint finish

19 Inch Mounting Shelves

Part No.	Part No.	Mounting Dimensions				Stiffener Lip(s)	Suggested Load Capacity
		Rack Units	Height	Width	Depth		
Vented	Solid					Up (Front & Back)	
RASV190107UBK1	RASU190107UBK1	1U	1.75	19.00	7.00	Down (Front & Back)	40
RASV190107DBK1	RASU190107DBK1	1U	1.75	19.00	7.00	Up (Back Only)	40
RASV190115BK1	RASU190115BK1	1U	1.75	19.00	15.00	Up (Back Only)	40
RASV190120BK1	RASU190120BK1	1U	1.75	19.00	20.00	Up (Back Only)	40
RASVL190314BK1	RASUL190314BK1	2U	3.50	19.00	14.50	Up (Back Only)	65
RASVL190514BK1	RASUL190514BK1	2U	3.50	19.00	14.50	Up (Back Only)	80
RASV190315BK1	RASU190315BK1	2U	3.50	19.00	15.00	Up (Back Only)	100
RASV190320BK1	RASU190320BK1	2U	3.50	19.00	20.00	Up (Back Only)	100
RASV190515BK1	RASU190515BK1	3U	5.25	19.00	15.00	Up (Back Only)	200
RASV190520BK1	RASU190520BK1	3U	5.25	19.00	20.00	Up (Back Only)	200
RASV190715BK1	RASU190715BK1	4U	7.00	19.00	15.00	Up (Back Only)	200
RASV190720BK1	RASU190720BK1	4U	7.00	19.00	20.00	Up (Back Only)	200

23 Inch Mounting Shelves

Part No.	Part No.	Mounting Dimensions	Stiffener Lip(s)	Suggested
----------	----------	---------------------	------------------	-----------

Vented	Solid	Rack Units	Height	Width	Depth	Folded	Load Capacity
RASV230515BK1	RASU230515BK1	3U	5.25	23.00	15.00	Up (Back Only)	200
RASV230520BK1	RASU230520BK1	3U	5.25	23.00	20.00	Up (Back Only)	200

24 Inch Mounting Shelves

Part No.	Part No.	Mounting Dimensions			Stiffener Lip(s)	Suggested Load Capacity	
Vented	Solid	Rack Units	Height	Width	Depth	Folded	
RASV240520BK1	RASU240520BK1	3U	5.25	24.00	20.00	Up (Back Only)	200
RASV240515BK1	RASU240515BK1	3U	5.25	24.00	15.00	Up (Back Only)	200

Data subject to change without notice.