


Four Post Mounting Adjustable Depth Shelf *RMAS Series*

Features



- Adjustable mounting depth.
- Choice of vented or solid options.
- Constructed of 14-Gauge Steel.
- Finished in a rugged textured powder paint finish
- Weight load tested up to 200 pounds (Heavy Duty version).
- Includes all mounting hardware
- MOUNTS ON TWO PAIR OF PANEL RAILS (FRONT & BACK)

Light Duty Shelves



Part No. Solid	Part No. Vented	Adjustable Depth Range		Rack Units
		Min	Max	
RMA SU1917BK1	RMA SV1917BK1	17.00	27.00	1U
RMA SU1925BK1	RMA SV1925BK1	25.00	35.00	1U
RMA SU1930BK1	RMA SV1930BK1	30.00	40.00	1U

Suggested Load Capacity of 75 lbs

Heavy Duty Shelves

Part No. Solid	Part No. Vented	Adjustable Depth Range		Rack Units
		Min	Max	
RMA SUHD1917BK1	RMA SVHD1917BK1	17.00	27.00	2U
RMA SUHD1925BK1	RMA SVHD1925BK1	25.00	35.00	2U
RMA SUHD1936BK1	RMA SVHD1936BK1	30.00	40.00	2U

Suggested Load Capacity of 200 lbs

Data subject to change without notice.