

Lite Duty Steel Knockdown 2-Post Open Frame Rack

DC2R Series

Front Punched Square Holes



Features

- **COMING SOON! NEW SELF-SQUARING DESIGN**
- Constructed in 12-gauge steel.
- 19" EIA-310-D compliant front square hole punched.
- Side ganging and accessory mounting holes.
- One (1) bonding stud located inner bottom of rail.
- Finished in smooth black powder paint.
- Ships un-assembled in a flat pack container for easy handling and shipping protection.
- Maximum load capacity of 800 lb.
- RoHS EU Directive 2002/95/EC compliant.
- Manufactured by Hammond Manufacturing, an ISO 9001:2008 certified company, located in North America.

Accessories

- [Equipment Rail Depth Adapter](#)
- [Two Post Mounting Adjustable Shelf](#)
- [Two Post Centered Shelf](#)
- [Two Post Mounting Keyboard & Monitor Shelf](#)
- [Two Post Mounting Adjustable Depth DIN Rail](#)
- [Mounting Hardware](#)
- [Outlet Strips](#)
- [Lite Duty Caster Set for Open Frame Rack](#)
- [Rack Unit Label](#)
- [Two Post Mounting Cantilever Shelf](#)
- [Two Post Mounting Clamping Shelf](#)
- [Two Post Mounting Deep Channel Battery Shelf](#)
- [Two Post Mounting Deep Channel Monitor Shelf](#)
- [Hinged Acrylic Door Panel Cover](#)
- [Cable Management](#)
- [Grounding](#)
- [Rack Panels](#)

Part No.	Overall Dimensions			Mounting Dimensions		
	Height	Width	Depth	Height	Width	Rack Units
DC2R44	83.13	20.56	15.00	77.00	19.00	44U

Data subject to change without notice.

