



Tenma 72-10400

SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	400mV/4V/40V/600V	±(0.8%+3)
AC Voltage	4V/40V/400V/600V	±(1.2%+3)
DC Current	400μA/4mA/40mA/400mA	±(1.0%+3)
AC Current	400μA/4mA/40mA/400mA	±(1.5%+5)
Capacitance	4nF/40nF/400nF/4μF/40μF/100μF	±(4%+3)
Frequency	10Hz-10MHz	±(0.5%+3)
Special Functions		
Display Count		3999
Auto Range		√
Duty Cycle	0.1%~99.9%	√
Diode		√
Auto Power Off	Around 30 Minutes	√
Continuity Buzzer		√
Low Battery Indication	≅ 2.4V	√
Data Hold		√
Relative Mode		√
Input Impedance for DCV	Around :10MΩ	√
GENERAL CHARACTERISTICS		
Power	3V Battery (CR2032)	
LCD Size	43 x 22mm	
Product Colour	Orange and Grey	
Product Net Weight	76g	
Product Size	110 x 58.2 x 10.8mm	
Standard Accessories	Battery, Carrying Case	
Standard Individual Packing	Blister, English Manual	
Standard Quantity Per Carton	90pcs	
Standard Carton Measurement	528 x 323 x 400mm(0.068 CBM Per Standard Carton)	
Standard Carton Gross Weight	13.5kg	