

UPS Network Management Cards

AP9631

UPS Network Management Card 2 with Environmental Monitoring



Remote monitoring and control of an individual UPS by connecting it directly to the network.

Includes: CD with software, Temperature Sensor, User Manual

Standard Lead Time: Usually in Stock

Product Category

- Computer and Peripheral (6)
- Home UPS (2)
- Network and Server (4)
- Data Center and Facility 3 Phase (15)
- UPS Management
 - > PowerChute Personal Edition
 - > PowerChute Business Edition
 - > PowerChute Network Shutdown
 - > **UPS Network Management Cards**
 - > Additional Management Cards and Options
 - > Interface Cables
 - > Battery Management

Return to Uninterruptible Power Supply (UPS)

[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Software & Firmware](#) [Options](#) [Ratings and Reviews](#)

Communications & Management	
Protocols	HTTP, HTTPS, IPv4, IPv6, NTP, SMTP, SNMP v1, SNMP v2c, SNMP v3, SSH V1, SSH V2, SSL, TCP/IP, Telnet
Network Interface Connections	RJ-45 10/100 Base-T
Authentication	Radius
Physical	
Net Weight	0.09 KG
Maximum Height	38.00 mm
Maximum Width	121.00 mm
Maximum Depth	114.00 mm
Shipping Weight	0.34 KG
Shipping Height	51.00 mm
Shipping Width	235.00 mm
Shipping Depth	159.00 mm
Color	Black
Environmental	
Operating Environment	0 - 45 °C
Storage Temperature	-5 - 45 °C
Operating Relative Humidity	0 - 95%
Storage Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Elevation	0-4500 meters
Conformance	
Regulatory Approvals	AS/NZS 3548 (C-Tick) Class A, EN 55022 Class A, EN 55024, FCC Part 15 Class A, GOST, ICES-003, VCCI Class A
Standard Warranty	2 years repair or replace
Sustainable Offer Status	
RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant
Battery Notes	Contains Lithium Battery