



# Lockout / Tagout



At Brady Corporation, we identify and protect your premises, products and people with complete solutions to meet all your safety and compliance needs



## Brady – When Performance Matters The Most

With a comprehensive product range consisting of high-performance labels and signs, safety devices, printing systems and software, sorbents, and precision die-cut materials, Brady is your trusted adviser for safety, facility and identification requirements. Since 1914, we helped customers in electronics, telecommunications, manufacturing, electrical, construction, education, marine, oil & gas, medical and a variety of other industries globally to increase safety, security, productivity and performance. Brady is a company that you can rely on when performance matters the most.

Brady is headquartered in Milwaukee and employs more than 6,500 people at operations in the Americas, Europe and Asia Pacific. Within the Asia Pacific, Brady has local presence in Australia, China, Hong Kong, India, Indonesia, Japan, Korea, Malaysia, New Zealand, Philippines, Singapore, Taiwan, Thailand and Vietnam. **Brady is right where you need us.**

To contact us, please refer to the back cover of this publication or visit our website at [www.bradyid.com/ap](http://www.bradyid.com/ap). Alternatively, please email in your enquiries to [ContactUs\\_SEA@bradycorp.com](mailto:ContactUs_SEA@bradycorp.com).



# TABLE OF CONTENTS

<b>Lockout/Tagout Overview</b>	
Why Use Lockout/Tagout (LOTO)	3
OSHA Standards	4
Selecting the right tools and devices	5
<b>Keys &amp; Padlocks</b>	
Keying & Charting Options	6
Safety Padlocks	7
Aluminum Padlocks	8
Key Retaining Steel Padlocks	9
Steel Padlocks	10
Padlock Accessories	11
<b>Tags</b>	
Tags Requirements	12
Tags	13
Perforated Tags	15
Tags Holder & Fastener	16
<b>Group LOTO Hasps</b>	17
<b>Circuit Breaker Lockout</b>	
EZ Panel Loc™ System	19
Circuit Breaker Lockout	21
Minature Circuit Breaker Lockout	23
<b>Electrical Lockout</b>	24
<b>Gas and Air Line Lockout</b>	
Air Line Lockout	26
Gas Lockout	27
<b>Cable &amp; Chain Lockout</b>	28
<b>Valve Lockout</b>	30
<b>Lockout Boards</b>	32
<b>Padlock Centers</b>	
Padlock Centers	33
Padlock Management System	34
<b>Group Lockout Boxes</b>	35
<b>Lockout Kits</b>	
Personal Lockout Kits	38
Standard Lockout Kits	40
Combination Lockout Kits	43
Customizable Lockout Kits	45
<b>Lockout Stations</b>	
Lockout Stations	47
Prinzing Kits & Stations	50
Ready Access Storage Stations	52
<b>Training &amp; Awareness Aids</b>	
Training & Awareness Aids	54
OSHA Training Requirements	56
<b>Energy Control Procedures</b>	57
<b>Workplace Safety And Compliance Solutions</b>	58

# LOCKOUT/TAGOUT OVERVIEW

## WHY USE LOCKOUT/TAGOUT?

### Contact

Contact your local Brady staff at [www.bradyid.com/ap](http://www.bradyid.com/ap) or mail us at [ContactUs\\_SEA@bradycorp.com](mailto:ContactUs_SEA@bradycorp.com)

## Why Use Lockout/Tagout (LOTO)?

- OSHA Focus #1 most cited violation for general industry
- Best Practice - Being adopted across industries & geographies
- Saves Lives - Prevents an estimated 120 fatalities & 50,000 injuries annually
- Significantly Cuts Costs - Both lost time and insurance costs
- Improves Productivity - Minimizes equipment downtime



## 5-Steps Effective Lockout/Tagout Program

Effective Lockout procedures can dramatically increase your company's productivity by making Lockout activities more efficient. Your procedures serve as a checklist that allows workers to quickly move through the steps without confusion or mistakes, reducing downtime and damage to machinery.



### 1. Hazard analysis

Develop and document your energy control policy/program



### 2. Identification of steps

Create and post written, equipment-specific lockout procedures



### 3. Documentation

Identify and mark all energy control points



### 4. Train Employees

Train your employees, communicate and conduct periodic inspections



### 5. Equip Employees

Equip your employees with the proper lockout tools and warning devices

# LOCKOUT/TAGOUT OVERVIEW

## OSHA STANDARDS

Singapore Standard 571:2011, the Code of Practice for Energy Lockout and Tagout deals with the control of hazardous energy in workplace situations and provides detailed guidance on procedures, techniques and methods for energy lockout and tagout. The SS571:2011 takes reference from OSHA Regulations (Standards-29 CFR-1910.147, ANSI Z244.1:2003 (2008) and CSA Z460:2005. Brady is part of the working group appointed by the Technical Committee of Singapore's Workplace Safety and Health to assist in the preparation of SS 571 : 2011. For more information, please visit [www.standards.org.sg](http://www.standards.org.sg)



### OSHA 29 CFR §1910.147 The control of hazardous energy (Lockout/Tagout).

#### Scope, application and purpose

- (1) Scope. (i) This standard covers the servicing and maintenance of machines and equipment in which the unexpected energization, start up of the machines/equipment, or release of stored energy could cause injury to employees. This standard establishes minimum performance requirements for the control of such hazardous energy.
- (2) Application. (i) This standard applies to the control of energy during servicing and / or maintenance of machines and equipment.
- (3) Purpose. (i) This section requires employers to establish a program and utilize procedures for affixing appropriate lockout devices or tagout devices to energy isolating devices, and to otherwise disable machines or equipment to prevent unexpected energization, start-up or release of stored energy in order to prevent injury to employees.

#### 1910.147(c) OSHA Energy Control Policy;

##### Synopsis of Requirements

An energy control policy must be documented and at a minimum, should cover the following aspects of the program:

- Purpose and scope of the program
- Personnel authorized to perform LOTO
- Enforcement policy
- Training methods
- Group lockout procedures
- Shift transfer procedures
- Lock removal procedures
- Method for auditing & updating procedures
- Coordination with outside contractors

#### 1910.147(c)(4) Energy Control Procedures;

##### Synopsis of Requirements

- Procedures must be documented and must identify the equipment covered
- A separate procedure must be created for each piece of equipment to be locked out. There are exceptions where multiple machines may be grouped under a single procedure
- The procedure must include specific steps for shutting down, isolating, blocking and securing equipment to control hazardous energy
- Specific steps for the placement, removal and transfer of lockout/tagout devices should also be included
- The employer shall conduct and certify periodic inspections at least annually

#### 1910.147(c)(4) Energy Control Procedures;

##### LOCKOUT DEVICES MUST:

- Be provided by the employer
- Be standardized by size, shape or color
- Be distinguishable from locks used for other purposes. Lockout locks should only be used for lockout
- Identify the individual who applied the lock (both tags and lock labels are acceptable for this purpose)
- Be durable
- Be strong enough to prevent removal except by using excessive force
- Remain under the exclusive control of the individual who attached them

#### 1910.147(c)(5)(ii)(B) Standardized

Lockout and Tagout devices shall be standardized within the facility in at least one of the following criteria:

Color; shape; or size; and additionally, in the case of Tagout devices, print and format shall be standardized.

#### 1910.147(c)(5)(ii)(A) Durable

Lockout and tagout devices shall be capable of withstanding the environment to which they are exposed for the maximum period of time that exposure is expected.



## SELECTING THE RIGHT TOOLS AND DEVICES

### When selecting your devices two questions should be asked:

- How many employees are involved in the procedure?
- What is the Energy source (Electrical, Valve, etc)?



### Effective Energy Isolation Programs

Using appropriate Lockout/Tagout tools and devices is critical to the success of your program implementation.

Brady's selection of Lockout/Tagout products helps to facilitate an effective Energy Isolation Program that can prevent potentially fatal injuries in your workplace.



**Valve & Cable Lockout devices** enable you to isolate various energy sources, when used in conjunction with padlocks. Brady's extensive range of devices enables you to select and use the most appropriate tools for your procedure, in accordance with your specific application.

See pages 30-31



**For Lockout situations** where up to 6 employees are involved in the process, a Hasp is an effective device where all personnel can be involved in maintenance activities simultaneously. Non-conductive, stainless steel and vinyl coated hasps are widely used in mining applications.

See pages 17-18



**In all Lockout procedures**, an employee or maintenance team doing the servicing must have exclusive control of the lockout devices and padlocks.



Studies have shown that an effective **Lockout/Tagout program** can reduce accidents by up to 50%, and some insurance companies even offer lower premiums to companies with demonstrated, effective Lockout programs.


KEYING AND CHARTING OPTIONS



KEYING & CHARTING OPTIONS


**Keyed Alike**

- When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee. Remember, however, that under OSHA regulations no employee should be able to open a lock applied by someone else. Therefore, keyed alike locks from the same set should never be distributed to multiple employees




**Keyed Different**

- Brady padlocks come "keyed different" when purchased from stock. This means that the key for one lock should not open another. Brady padlocks use 5- or 6-pin cylinders. Moreover, both cylinders and keys are precision-machined to exacting standards. This enables us to offer a greater number of unique keys than other locks with the same number of pins, making it highly unlikely that you will ever receive a duplicate lock
- To guarantee that each lock is different, we can chart your locks, ensuring that each Brady padlock you receive is different from the others (see below)



**Master Keyed**

- A master key can be used to open multiple locks that are keyed differently. This allows supervisors to easily remove a lock in the event of an emergency. In order for employees to retain exclusive control, master keys should be kept in a secure location that is accessible only to management



**Keyed Charting**

- Brady can track or "chart" your key codes upon request, in order to simplify ordering of replacement locks and to avoid duplicates when ordering additional locks

There is no extra charge for charting. Please contact Brady for details.

**Choose the lock that's best suited for the job!**

Feature	Compact Safety Padlocks	Safety Padlocks	Aluminum Padlocks	Key-retaining Steel Padlocks	Steel Padlocks
Compact, lightweight	✓	✓	✓		
Non-conductive body & keyway	✓	✓			
Most corrosion resistant	✓	✓	✓	✓	✓
Most spark resistant	✓	✓			
Most tamperproof		✓	✓	✓	✓
Most rugged		✓		✓	✓

# SAFETY PADLOCKS

The Ultimate Lockout Lock!



Brady Safety Padlock complies with all OSHA requirements and is a safer alternative to metal locks for lockout applications. The body is nonconductive, while the unique key cylinder prevents electricity from traveling from the shackle to the key, protecting workers when key is inserted. Safety Padlocks also deliver superior corrosion resistance. Third-party tests confirm that Brady outperforms the leading competitor when subjected to repeated salt water sprays.

## Features & Benefits

- Superior temperature, chemical and corrosion resistance
- “Danger” and “Property of” labels provided in English, Spanish, and French and are printed on 100% recycled paper
- Reserved paracentric keyway provides optimal security (prevents someone from getting a copy made at a local key shop)
- Key-retaining safety feature prevents key from being removed until shackle is securely closed
- Locks come keyed-differently or in keyed-alike sets. Custom keying and charting also available (see page 6)
- Lock bodies can be custom laser-engraved upon request
- Ribbed sides promote secure gripping – even when wearing gloves
- One key is supplied with each padlock for safer key management

## Compact Safety Padlocks

- Extremely compact and lightweight - the smallest safety lock on the market
- Fits in small spaces easily (e.g. circuit breaker panels) and the ideal lock for electrical contractors/maintenance personnels/electricians
- 5-pin cylinder - able to support the same keying system as our current Safety Padlocks
- Fiberglass reinforced nylon body for extra impact resistance
- Aluminum shackle gives superior spark and corrosion resistance
- Service temperature: 0°F - 250°F (-20°C - 120°C)
- Lock body dimensions: 1<sup>2</sup>/<sub>5</sub>”, 1<sup>1</sup>/<sub>5</sub>”, 5<sup>5</sup>/<sub>8</sub>”
- Shackle clearance: 1”; shackle diameter: 1<sup>1</sup>/<sub>5</sub>”

Color	Keyed Different 1 Padlock/Pack	Keyed Different 6 Padlock/Pack	Keyed Alike 3 Padlock/Pack	Keyed Alike 6 Padlock/Pack
Red	143150	118926	118953	118954
Green	143152	118927	118955	118956
Orange	143154	118928	118957	118958
Blue	143156	118929	118959	118960
Yellow	143158	118930	118961	118962
Brown	143160	118931	118963	118964
White	143162	118932	118965	118966
Purple	143164	118933	118967	118968
Black	143166	118934	118969	118970

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.

## Safety Padlocks

- Lightweight, nonconductive and non-sparking body
- Special 6-pin cylinder resists tampering
- Fiberglass reinforced nylon body and triple-coated hardened steel shackle
- Service temperature: 0°F - 250°F (-20°C - 120°C)
- Lock body dimensions: 1<sup>3</sup>/<sub>4</sub>”, x 1<sup>1</sup>/<sub>2</sub>”, x 4<sup>1</sup>/<sub>5</sub>”
- Shackle clearance: 1<sup>1</sup>/<sub>2</sub>”; shackle diameter: 1<sup>1</sup>/<sub>4</sub>”

Color	Keyed Different 1 Padlock/Pack	Keyed Different 6 Padlock/Pack	Keyed Alike 3 Padlock/Pack	Keyed Alike 6 Padlock/Pack
Red	99552	51339	105886	105890
Blue	99556	51344	105887	105891
Green	99564	51345	105889	105893
Yellow	99570	51346	105888	105892
Orange	99576	51347	-	-
Black	99580	51353	-	-
Brown	103033	101956	118947	118948
Purple	104919	104916	118951	118952
White	143123	118925	118949	118950

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.



Compact Safety Padlocks



Safety Padlocks



# ALUMINUM PADLOCKS



## Features & Benefits

- Lightweight yet rugged with solid aluminum body and shackle - lightest-weight aluminum lock in the market and made from recycled material
- 6-pin cylinder offers more unique key changes - better tamper resistance
- Reserved paracentric keyway provides optimal security (prevents someone from getting a copy made at a local key shop)
- FDA approved lubricant in cylinder
- Anodized aluminum finish gives better fade resistance when used outdoors
- Key retaining safety feature prevents key from being removed until closed
- Aluminum shackle gives better corrosion resistance (four times better than the hardened chrome-plated steel shackle) and is spark resistant
- Two shackle sizes: 1" and 1 1/2", shackle diameter: 1/4"
- Lock body: 1 3/5" x 1 1/2" x 3/4"
- Two keys supplied with each lock. Custom keying and charting also available
- Lock labels sold separately (made from 100% recycled paper)

## Aluminum Padlocks - 1" Shackle

Color	1 Padlock/Pack	6 Padlock/Pack
Red	99608	51360
Blue	99609	51361
Green	99610	51362
Yellow	99611	51363
Orange	99612	51368
Black	99613	51369
Brown	104574	104575
Purple	104572	104573

## Aluminum Padlocks - 1 1/2" Shackle

Color	Keyed Different 1 Padlock/Pack	Keyed Different 6 Padlock/Pack	Keyed Alike 3 Padlock/Pack	Keyed Alike 6 Padlock/Pack
Red	99615	51370	105902	105882
Blue	99616	51371	105903	105883
Green	99617	51376	105881	105885
Yellow	99618	51377	105904	105884
Orange	99619	51378	-	-
Black	99620	50274	-	-
Brown	104578	104579	-	-
Purple	104576	104577	-	-

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.



# KEY RETAINING STEEL PADLOCKS



## Features & Benefits

- Reinforced laminated steel withstands severe physical abuse
- Hardened steel shackle resists tampering, cutting, prying, and rusting
- Body plates individually coated for superior rust protection, offering 13 times better corrosion resistance than normal steel locks
- 5 - pin cylinder offers more unique key cuts and increased tamper resistance
- Two shackle sizes: 3/4" or 2", shackle diameter: 17/64"
- Lock body: 1 1/5" x 1 5/16" x 1"
- Colored bumpers supplied for identification and protection (custom stamping available)
- Custom keying and charting also available
- One key supplied with each padlock for safer key management
- Lock labels sold separately and made from 100% recycled paper
- Made from recycled material
- Key retaining safety feature prevents key from being removed until closed
- Lighter weight than standard Laminated Steel Padlocks

## Key Retaining Steel Padlocks - 3/4" Shackle

Color	Keyed Different 1 Padlock/Pack	Keyed Different 6 Padlock/Pack
Red	143126	118935
Green	143128	118936
Blue	143130	118937
Yellow	143132	118938
White	143134	118939
Black	143136	118940

## Key Retaining Steel Padlocks - 2" Shackle

Color	Keyed Different 1 Padlock/Pack	Keyed Different 6 Padlock/Pack	Keyed Alike 3 Padlock/Pack	Keyed Alike 6 Padlock/Pack
Red	143144	118944	118977	118978
Green	143142	118943	118975	118976
Blue	143140	118942	118973	118974
Yellow	143148	118946	118981	118982
White	143146	118945	118979	118980
Black	143138	118941	118971	118972

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.



# STEEL PADLOCKS



## Features & Benefits

- Reinforced laminated steel withstands severe physical abuse
- Hardened steel shackle resists tampering
- Body plates individually coated for superior rust protection
- 5 - pin cylinder offers more unique key cuts, better tamper resistance than conventional 4 - pin locks
- One key supplied with each padlock for safer key management
- Two shackle sizes: 3/4" or 2", shackle diameter: 17/64"
- Lock body: 1 1/3" x 1 9/16" x 7/8"
- Colored bumpers supplied for identification and protection (custom stamping available)
- Locks come keyed-different. Custom keying and charting also available
- Lock labels sold separately

## Steel Padlocks - 3/4" Shackle

Color	Keyed Different 1 Padlock/Pack	Keyed Different 6 Padlock/Pack
Red	99500	51279
Blue	99504	51280
Green	99508	51281
Yellow	99512	51282
Orange	99516	51283
Black	99520	51284
Brown	101957	102696
Purple	104920	104917

## Steel Padlocks - 2" Shackle

Color	Keyed Different 1 Padlock/Pack	Keyed Different 6 Padlock/Pack	Keyed Aliked 3 Padlock/Pack	Keyed Aliked 6 Padlock/Pack
Red	99524	51290	105894	105898
Blue	99528	51291	105895	105899
Green	99533	51292	105897	105901
Yellow	99539	51297	105896	105900
Orange	99543	51298	-	-
Black	99548	51299	-	-
Brown	101958	102698	-	-
Purple	104921	104918	-	-

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.



**PADLOCK ACCESSORIES**



**Combination Padlocks**

- Compact, Lightweight
- 4-digit resettable code
- Steel shackle

Catalog #	Description
101963	Combination Padlock



**Safety Padlock Labels**

Safety padlock labels help send a clear message to workers when a machine is down for service or maintenance. Labels are designed to fit Brady Safety Padlocks and are available in English.

Catalog #	Description	Qty
51379	English	6/pack



**Aluminum Padlock Labels**

- Made of durable B-826 vinyl
- Writable using pencil, pen or marker

Catalog #	Dimensions	Description
50289	0.8" x 1.1", 6/pack	English
50292	0.8" x 1.1", 6/pack	Spanish
50293	0.8" x 1.1", 6/pack	English

**Steel Padlock Labels**

- Made of durable B-826 vinyl and includes overlaminates strips for enhanced durability
- Writable using pencil, pen or marker

Catalog #	Dimensions	Description
50280	3/4" x 4 1/2", 6/pack	English
50281	3/4" x 4 1/2", 6/pack	Spanish
50283	3/4" x 4 1/2", 6/pack	French



# TAGS REQUIREMENTS

Communicate safety and lockout information at the point of need with Brady's wide selection of OSHA-compliant Lockout/Tagout tags. Brady's Lockout Tags come in a variety of materials to suit your application needs.



## OSHA Tags Requirements

The following requirements apply only to tags used as tagout devices (i.e., tags used alone without locks). Tags used in combination with locks are not required to meet the same restrictions as tagout devices.

- Be provided by the employer
- Be standardized by size, shape or color
- Be distinguishable from tags used for other purposes
- Be understandable to all employees
- Identify the individual who applied the tag
- Withstand the usage environment to which they are exposed for the maximum period of time that exposure is intended. Tag should not deteriorate or the message become illegible when exposed to weather, wet or damp conditions, chemical or corrosive environments
- Employ a means of attachment that is substantial enough to prevent accidental removal. The means of attachment must be of a non-reusable type, attachable by hand, self-locking, and non-releasable with a minimum unlocking strength of no less than 50 pounds
- Warn against hazardous conditions if the machine or equipment is energized
- Tag shall also include a legend such as the following: Do Not Operate, Do Not Start, Do Not Open, Do Not Close, etc

## How to Order Tags

- Determine the best tag material below for your application
- Choose the tag legend for your tag
- Order by part number for desired reverse side legend

Description	Dimensions
Heavy Duty Polyester (B-837)	5 1/2" x 3", 25/pack
Economy Polyester (B-851)	5 3/4" x 3", 25/pack
Cardstock (B-853)	5 3/4" x 3", 25/pack

## Tag Materials

### Heavy Duty Polyester (B-837)

- Durable polyester laminate completely encapsulates and protects graphics
- Withstands moisture, grease, chemicals, and extreme temperature
- Accepts pencil, pen and marker. Pen and marker can be completely erased using isopropyl alcohol, allowing for repeated use
- Heavy duty construction withstands up to 80 lbs of pull force, preventing accidental removal
- 3/8" diameter heavy-duty brass grommet accepts most padlock shackles
- Tags come with OSHA-compliant nylon fasteners


### Economy Polyester (B-851)

- Rigid polyester surface is easy to write on and stays legible longer than cardstock
- Exceeds OSHA 50 lb. pull requirement for tagout devices
- 3/8" diameter rolled brass eyelet accepts most padlock shackles
- Tags come with OSHA-compliant nylon fasteners

### Cardstock (B-853)

- Cost-effective tags designed for one-time use
- Does NOT meet OSHA 50 lb. pull test for tagout devices, but can be used in conjunction with locks (see OSHA Tag Requirements above)
- 3/8" diameter rolled brass eyelet accepts most padlock shackles
- Tags come with attachment strings





Reverse Side B



Front Side A




Front Side B



Front Side C



Front Side D



Reverse Side F



Reverse Side G



Front Side E



Front Side F



Front Side G



Front Side H



Front Side I

Font Side A	Font Side B	Font Side C	Font Side D
<b>Heavy Duty Polyester (B-837)</b>			
Rev. Side B - 65502	Rev. Side B - 65520	Rev. Side B - 65515	Rev. Side B - 65526
Rev. Side F - 65535	Rev. Side F - 65525	Rev. Side F - 65524	Rev. Side F - 65527
Rev. Side G - 65670	Rev. Side G - 65671	-	-
<b>Economy Polyester (B-851)</b>			
Rev. Side B - 66050	Rev. Side B - 66063	Rev. Side B - 66061	Rev. Side B - 66066
Rev. Side F - 66051	Rev. Side F - 66064	Rev. Side F - 66062	Rev. Side F - 66067
Rev. Side G - 66052	Rev. Side G - 66065	-	-
<b>Cardstock (B-853)</b>			
Rev. Side B - 65407	Rev. Side B - 65451	-	Rev. Side B - 65454
Rev. Side F - 65408	Rev. Side F - 65452	Rev. Side F - 65450	Rev. Side F - 65455
Rev. Side G - 65440	Rev. Side G - 65453	-	-

Font Side E	Font Side F	Font Side G	Font Side H	Font Side I
<b>Heavy Duty Polyester (B-837)</b>				
Rev. Side B - 65503	Rev. Side B - 65504	-	Rev. Side B - 65506	Rev. Side B - 65505
Rev. Side F - 65521	Rev. Side F - 65522	-	Rev. Side F - 65534	Rev. Side F - 65523
<b>Economy Polyester (B-851)</b>				
Rev. Side B - 66053	Rev. Side B - 66055	Rev. Side B - 50198	-	-
Rev. Side F - 66054	Rev. Side F - 66056	Rev. Side F - 50199	Rev. Side F - 66060	-
<b>Cardstock (B-853)</b>				
Rev. Side B - 65441	Rev. Side B - 65443	-	Rev. Side B - 65447	Rev. Side B - 65445
Rev. Side F - 65442	Rev. Side F - 65444	Rev. Side F - 50250	Rev. Side F - 65448	Rev. Side F - 65446

# TAGS

# TAGS



## Padlock Tags

- Calendered vinyl accepts pencil, pen or marker
- Employs 3/8" metal grommet that fits over most padlock shackles

Catalog #	Dimensions	Description
105722	3" x 2"	Equipment Locked Out
105723	3" x 2"	Do Not Operate
105724	3" x 2"	Do Not Operate - English/Spanish

Grommet adds another 1" to height



## Self-Laminating Photo Tags

- Include employee photos for easy identification and greater impact
- Constructed using durable B-851 polyester with 1 mil polyester overlay on front
- 10 tags and nylon fasteners per package

Catalog #	Dimensions
65501	5 3/4" x 3", 10/pack
96222	7" x 4", 10/pack



Peel away liner



Front

Back

## TAGS

# PERFORATED TAGS

Two-part tags provide enhanced operational control and record-keeping. Stub is removed when tag is attached to a lockout point. Only the employee in possession of the stub has the authority to remove the tag. After the job is done, stub is returned to management for verification and monitoring of lockout/tagout activity in the plant. Matching identification numbers are printed on each part.



### Heavy Cardstock Tags

- Economical cardstock tags are easy to write on using pen, pencil or permanent marker
- Employs  $\frac{3}{8}$ " rolled brass eyelet that resists tearing
- Tie strings included for quick, easy attachment

Catalog #	Dimensions	Description
105372	7.5" x 4", 25/pack	Equipment Locked Out
105373	7.5" x 4", 25/pack	Do Not Operate

### Plastic Tags

- 10 mil-thick polyester enhances durability and makes it easy to remove chemicals, grease and grime
- Write-on surface accepts marker, pen or pencil
- Weatherproof for indoor or outdoor use.
- Employs  $\frac{3}{8}$ " rolled brass eyelet that fits over most padlock shackles
- Nylon cable ties included for easy, secure attachment

Catalog #	Dimensions	Description
105370	7.5" x 4", 25/pack	Equipment Locked Out
105371	7.5" x 4", 25/pack	Do Not Operate

### Tags with Detachable Key Stub

Perforated cardstock tag comes with detachable key stub, making it easy to match up tags attached to padlocks with the right key. Matching identification numbers are printed on each part.

- Heavy cardstock accepts pencil, pen or marker
- Tie strings provided for easy tag attachment
- 1" diameter metal ring provided for attaching stub to key

Catalog #	Dimensions	Description
105368	5 $\frac{3}{8}$ " x 3", 25/pack	Equipment Locked Out
105269	5 $\frac{3}{8}$ " x 3", 25/pack	Do Not Operate





## TAGS

# TAG HOLDERS AND FASTENERS



### 1-Pocket Economy Tag Holder

- Compact, clear plastic holder is designed to hold 50 tags, ties and a marking pen
- Comes with adhesive strips, magnetic strips, and screws for mounting in a variety of ways
- Tags and pen not included

Catalog #	Dimensions	Description
TH2	7 1/2" x 4 1/2" x 1 1/2"	1-Pocket Economy Tag Holder



### Pocket Premium Tag Center

- Acrylic center features 8 pockets for displaying and dispensing tags
- Each polystyrene pocket holds up to 30 tags
- Four pre-drilled holes for wall mounting
- Tags not included

Catalog #	Dimensions	Description
TC8	15 3/4" x 23 1/2" x 2"	8-Pocket Premium Tag Center



### 10-Pocket Tag Safety Station

- Made of rugged polycarbonate
- Four pre-drilled holes for wall mounting
- Tags not included

Catalog #	Dimensions	Description
81773	22" x 16 1/2" x 2 1/4"	10-Pocket Tag Safety Station



### Tag Fasteners

- Three fastener styles available to meet every application
- Nylon fasteners meet OSHA requirements for attaching tagout devices

Catalog #	Dimensions	Description
81760	12", 100/pack	26 Gauge Wire
81761	8", 100/pack	Reusable Beaded Ties
81762	8", 100/pack	Nylon Fasteners



## GROUP LOCKOUT HASPS

# GROUP LOCKOUT HASPS



### Steel Group Lockout Hasps

- Constructed of vinyl-coated high tensile steel with rest resistant plating
- Lock holes:  $\frac{3}{8}$ " diameter

Catalog #	Dimensions
65375	1" Diameter Jaws, 12/pack
65376	1 1/2" Diameter Jaws, 12/pack



### Aluminum Economy Group Lockout Hasps

- Non-sparking, aluminum small hasps are a great addition to your tool box
- Lightweight - only 1 1/2 ounces
- Maximum  $\frac{3}{8}$ " shackle diameter

Catalog #	Dimensions
105720	1" Diameter Jaws, 1/pack
105721	1 1/2" Diameter Jaws, 1/pack



### Non-conductive Group Lockout Hasps

- Made of strong, rigid yellow plastic resin
- Has excellent electrical insulating characteristics
- Performs at low temperatures, excellent heat resistance
- Patent #7, 124,606

Catalog #	Description
LH220A-YW	Yellow Lockout Hasp
LH220A	Red Lockout Hasp



### Corrosion-Resistant Group Lockout Hasps

- Manufactured from 12 gauge steel that is epoxy coated to give superior resistance to rust and added dielectric strength
- Yellow plastic coating is added to the lock area for visibility
- Lock holes:  $\frac{5}{16}$ " diameter

Catalog #	Dimensions
T218	1" Diameter Jaws, 1/pack
T220	1 1/2" Diameter Jaws, 1/pack



### Steel Group Lockout Hasps with Tabs

- Tamperproof interlocking tabs prevent unauthorized opening
- Constructed of case-hardened steel with rust proof plating and bright red vinyl insulation.
- Maximum  $\frac{3}{8}$ " shackle diameter

Catalog #	Dimensions
105718	1" Diameter Jaws, 1/pack
105719	1 1/2" Diameter Jaws, 1/pack

## GROUP LOCKOUT HASPS

# GROUP LOCKOUT HASPS



### SHOCK-STOP™ Group Lockout Hasps

- Highly visible hasp uses stop sign design to draw attention
- Includes 6 lock holes and a slot for daisy-chaining hasps together
- Also sold with companion storage board and lock box
- Lock holes:  $\frac{5}{16}$ " diameter

Catalog #	Dimensions	Description
87693	5 $\frac{1}{2}$ " x 3 $\frac{3}{8}$ " x $\frac{3}{16}$ ", 5/pack	Shock-Stop™ Hasps



### Non-Conductive Nylon Group Lockout Hasp

- Nonconductive nylon hasps accommodates up to 6 locks
- Withstands up to 1,000 lbs, yet weighs only 1 oz
- Lock holes:  $\frac{3}{8}$ " diameter

Catalog #	Dimensions	Description
99668	7" x 1 $\frac{3}{4}$ "	Nylon Lockout Hasp



### Labeled Group Lockout Hasps

- Constructed from tough 5052 anodized aluminum alloy
- Includes tamperproof locking tabs
- Write-on label surface accepts pencil, pen or marker
- Pen and pencil markings can be easily erased, allowing repeated use
- For permanent marking, use the marker sold below
- Lock holes:  $\frac{5}{16}$ " diameter
- Dimensions: 7 $\frac{7}{14}$ " x 3" x  $\frac{3}{16}$ "
- Standard package: 5 hasps/pack



#### Labeled Lockout Hasps – Aluminum

Color	Reverse Side #1	Reverse Side #2
Red	65960	65970
Silver	65961	65971
Blue	65962	65972
Green	65963	65973
Gold	65964	65974
Combination	65967	65975

Also available in Spanish - contact your local distributor for details



Reverse Side #1



Reverse Side #2

# CIRCUIT BREAKER LOCKOUT

## EZ PANEL LOC™ SYSTEM



### Features & Benefits

- Works on a wide range of breakers, including single and multi-pole configurations
- Makes use of unique lock rail system
- Allows panel door to be closed even when lockouts are in place
- Accommodates multiple locks - facilitating group lockout activity without hasps
- Keeps weight off the breakers, protecting delicate electrical components from damage
- Positions locks and tags outside the panel, making sure lockout activity is clearly visible to anyone in the area
- Patent No. 6,727,441

(Not recommended for use with multilock hasps)

### EZ Panel Loc™ System



Lockout device is unlocked by inserting and turning the black plastic key.



**Step 1:** Peel liner off bottom of lock rail, exposing the super-bond adhesive. Permanently affix lock rail to any location on the panel. No drilling required!



**Step 2:** Attach the lockout device to the breaker and snap into locked position.



**Step 3:** Pass plastic key through lock rail and attach lock.

This prevents key from sliding down cable and opening lockout device.



**Step 4:** For group lockouts, run key through multiple loops in lock rail and apply the locks. No hasps required!

(Not recommended for use with multilock hasps)



**Step 5:** Low-profile lockouts allow panel doors to be closed on most breaker panels.

### Covers Most 120V – 277V Breakers

The EZ Panel Loc™ System includes two types of lockout devices, accommodating an exceptionally wide range of breaker models.

#### SNAP-ON

For use on Square D NQO and other breakers that have a hole in the switch tongue. Just align pins with hole and snap closed. Pins prevent switch from being thrown.

#### CLAMP-ON

For use on breakers that do not have a hole in the switch tongue, including multipole breakers with tie-bars. Turn thumbscrew to clamp lockout securely onto switch, then snap the cover closed to prevent thumbwheel from being loosened.



Snap-On

Clamp-On

# CIRCUIT BREAKER LOCKOUT

## EZ PANEL LOC™ SYSTEM



### “No Shackle” EZ Panel Locks

The EZ Panel Loc™ system can be used with most padlocks. A shackle-less padlock designed specifically for use with the EZ Panel Loc™ key is also available. This is especially useful when lockout devices will be kept at the panel in accordance with NEC regulations (see below). Everything you need to lockout breakers is kept conveniently right at the point of need!

### Do You Know?

“The provisions for locking or adding a lock to the disconnecting means shall be permanently installed on or at the switch or circuit breaker used as the disconnecting means.”


- NEC 2002, Article 430.102(B) Motor




### Spacing Gasket

For low profile panels, a spacing gasket can be installed, pushing out the panel frame and adding an additional 3/8" of clearance between the panel surface and the door. Self-adhesive backing makes installation quick and easy.

Catalog #	Dimensions	Description
89256	3/8" x 1" x 15'	EZ Panel Loc™ Spacing Gasket



Snap-On



Clamp-On

### Technical Information

- Lockout devices constructed of high-impact Isoplast Polymers
- Cables are 2' in length
- Lock rails made of durable Isoplast Polymers with acrylic adhesive backing
- Lock rails available in 4" or 8" lengths (containing 7 or 15 lock loops)
- Patent No. 6,727,441

	Outer Dimensions (in.)			Switch Clearance (in.)	
	A	B	C	D	E
Snap-On Style	0.90"	1.88"	0.74"	0.40"	0.35"
Clamp-On Style	0.95"	2.56"	0.74"	0.35"	0.42"

Description	1 Per Pack	6 Per Pack
Snap-On Lockout Device	51252	65815
Clamp-On Lockout Device	51254	65810
4" Lock Rail	51256	65814
8" Lock Rail	51258	51260
No-Shackle Lock	59505	51263
Spacing Gasket	89256	-

## CIRCUIT BREAKER LOCKOUT

# CIRCUIT BREAKER LOCKOUT



### 120V Snap-On Breaker Lockout

- Designed for 120V breakers that have holes in the switch tongue
- Quick and easy – just snap in place and apply lock
- Dual cavities accommodate different size switch tongues
- Accepts locks shackles up to  $\frac{9}{32}$ " in diameter

Catalog #	Dimensions	Description
65387	0.83" x 0.35" x 2.15", 1/pack	120V Snap-On Breaker Lockout
65688	0.83" x 0.35" x 2.15", 6/pack	120V Snap-On Breaker Lockouts



The Brady Clamp-On Circuit Breaker Lockout works on an extremely wide range of breakers

### Clamp-On Breaker Lockouts

- Extremely versatile – works on wide range of single-pole and internal-trip multi-pole breakers
- Two sizes, one for 120/277V breakers and one for 480/600V breakers
- Made of rugged polypropylene and impact modified nylon
- Use thumbscrew to clamp lockout securely onto switch tongue, then pull cover over thumbscrew and lock in place to prevent clamp from being loosened
- New blade design provides tighter grip with less torque on thumb screw
- Detachable cleats (included) expand the range of applicable breakers
- Accepts locks shackles up to  $\frac{9}{32}$ " in diameter

Catalog #	Description	Quantity
65396	120/277V Clamp-On Breaker Lockout	1/pack
65965	120/277V Clamp-On Breaker Lockout	6/pack
65397	480/600V Clamp-On Breaker Lockout	1/pack
65966	480/600V Clamp-On Breaker Lockout	6/pack



Step 1

Step 2

Step 3

### Extra Cleats for Clamp-On Breaker Lockouts

- Use in conjunction with clamp-on breaker lockouts (sold above)
- Easily clips onto the bottom of the lockout body
- Assures positive restraint for breakers with long, sliding switch throws

Catalog #	Description	Quantity
65404	Cleats For 120/277V Lockout	6/pack
65406	Cleats For 480/600V Lockout	6/pack



Universal Multi-Pole Lockout works with most two or three pole breakers utilizing a tie-bar

### Universal Multi-Pole Breaker Lockout

- Single device works with most major multi-pole breakers that employ a tie-bar
- Made of durable impact-modified nylon
- Compatible with GE, ITE, Sylvania, Challenger, Bryant, Westinghouse, General Switch Co
- Use thumbscrew to clamp lockout securely over tie bar, then insert lock to prevent clamp from being loosened
- Patent No. 5,300,740

Catalog #	Description	Quantity
66321	Universal Multi-Pole Breaker Lockout	1/pack
66320	Universal Multi-Pole Breaker Lockout	6/pack

## CIRCUIT BREAKER LOCKOUT

# CIRCUIT BREAKER LOCKOUT



### Oversized Clamp On Breaker Lockout

- Oversized 480/600V frame lockout fits breaker switches up to 2 1/4" wide and 7/8" thick
- Made of durable polypropylene and glass filled-impact-modified nylon
- New blade design gets better grip, works on even more breaker models
- Patent No. 5,500,495

Catalog #	Description	Quantity
65329	Oversized Breaker Lockout	1/pack
65321	Oversized Breaker Lockout	6/pack

### 480-600V Breaker Blocker

- Perfect for locking out oversized and irregularly shaped switches
- Self-adhesive backed rails are permanently installed into an electrical panel – simply clean panel surface and adhere, no drilling required
- Red blocking bar indicates locked off, green bar indicates locked on

#### Breaker Blocker Kit

Catalog #	Description
90891	Breaker Block Kit

\* Kit includes 2 yellow mounting rails, 1 red blocking bar, 1 green blocking bar and 3 alcohol wipes

#### Breaker Blocker Components

Catalog #	Dimensions	Description
90892	7.6", 5/pack	Red Blocking Bar
90893	7.6", 5/pack	Green Blocking Bar
51264	4", 2/pack	Yellow Mounting Rails
51265	5/pack	Blocking Bar Holder



### Not Sure Which Circuit Breaker Lockout To Use?

Check out Brady's Circuit Breaker Lockout Reference Guide. We've tested over 750 makes and models of breakers, including popular brands such as Allen Bradley, ABB, Cutler Hammer, General Electric, Siemens, Square D and more! The Reference Guide makes it easy to find the right lockout device for the breakers you use. Download the reference guide from [www.bradyid.com/LockoutTagout](http://www.bradyid.com/LockoutTagout), or email in your enquiries to [ContactUs\\_SEA@bradycorp.com](mailto:ContactUs_SEA@bradycorp.com).

# CIRCUIT BREAKER LOCKOUT

# MINIATURE CIRCUIT BREAKER LOCKOUT

## Features & Benefits

- A safe and effective method for locking out miniature circuit breakers, commonly used in European and Asian equipment
- Miniature Breaker Lockouts require NO TOOLS to install! The lockout easily installs with the aid of a push button (tie-bar lockout has a convenient thumb wheel for quick application)
- Available for single and multi-pole breakers
- Recommended to lock with lightweight Brady Safety padlocks or other padlocks, the lockouts can take padlocks with a shackle diameter up to 9/32"
- Material: Glass-filled nylon
- Available in 1 or 6 packs



Tie-Bar Lockout (TBLO)

Pin-Out Standard (POS)



Pin-In Standard (PIS)

Pin-Out Wide (POW)

- 4 Different types:
- POS** Pin Out Standard
  - PIS** Pin In Standard
  - POW** Pin Out Wide
  - TBLO** Tie Bar Lockout

## Miniature Circuit Breaker Lockout

Catalog #	Description	Qty
90844	POS	1
90845	POS	6
90847	PIS	1
90848	PIS	6
90850	POW	1
90851	POW	6
90853	TBLO	1
90854	TBLO	6

## Breaker Compatibility Chart


Brand	Poles	Model No.	Catalog # 1/pkg	Type
ABB	1	S222	90844	POS
ABB	1	F374	90844	POS
ABB	1	S251, S261, S263	90844	POS
ABB	1	S272, S253	90844	POS
ABB	2	S253	90844	POS
AEG	3	E82S	90847	PIS
Allen-Bradley	1,2,3	1492-CB1, 2, 3	90844	POS
Buschmat	1	S46	90844	POS
Clipsal	1	4CB116	90844	POS
Clipsal	3	4CB320	90844	POS
E-T-A	1	911225	90847	PIS
E-T-A	2	911220G	90844	POS
FAZ	4	C16	90844	POS
FAZ	1	C16	90844	POS
GE Vynckier	3	Series E	90847	PIS
GE Vynckier	3	Series G	90847	PIS
GE Vynckier	4	Series E	90847	PIS
GE Vynckier	1	Series G	90847	PIS
GE Vynckier 16A	2	Series E	90847	PIS
GE Vynckier C16, 16A	1	Series E	90847	PIS
Hager	3	453717	90844	POS
Hager	2	MW216A	90844	POS
Hager	4	MW620A	90844	POS
Kapp	1	LS68	90844	PIS
Legrand	2	01935	90844	TBLO
Legrand	3	01980	90844	TBLO
Legrand	4	01980	90844	TBLO
Legrand	2	04302	90847	PIS
Legrand	3	06469	90847	PIS
Legrand	1	01908	90844	POS
Merlin Gerin	3	C80A	90850/90853	TBLO/POW
Merlin Gerin	2	B100A	90850/90853	TBLO/POW
Merlin Gerin	1	C60N	90844	POS
Merlin Gerin	1	C32N	90844	POS
Merlin Gerin	2	C60N	90844	POS
Merlin Gerin	4	C60N	90844	POS
Merlin Gerin	3	C32N	90844	POS
Merlin Gerin	3	C45AD	90844	POS
Proteus	1	C16	90844	POS
Proteus	1	C6	90844	POS
Proteus	3	C6	90844	POS
Siemens 17U	2	5SQ12	90853	TBLO
Siemens 17U	3	5SQ13	90853	TBLO
Siemens 17U	4	5SQ16	90853	TBLO
Siemens 17U	1	5SQ11	90850	POW
Siemens C10	1	5SX1	90850	POW
Siemens C32	2	5SX1-2	90853	TBLO
Siemens C70	3	5SX13	90853	TBLO
Siemens L20A	2	5SN2-2	90853	TBLO
Sursum	3	EA53	90847	PIS
Wylex	2	WRS40/2	90844	POS

View the full compatibility chart at [www.BradyID.com/LockoutTagout](http://www.BradyID.com/LockoutTagout)



## ELECTRICAL LOCKOUT

## ELECTRICAL LOCKOUT



### 3-In-1 Electrical Plug Lockout

- Accommodates high and low-voltage plugs up to 3" in diameter and 5 1/2" in length
- 2 sliding top lids can be used individually or together to accommodate small, medium and large-diameter cords up to 1 1/4"
- Made of bright yellow thermoplastic
- Available with English or English/Spanish instruction labels

Catalog #	Description
PLO23	3-in-1 Plug Lockout - English
PLO23-BI	3-in-1 Plug Lockout - English/Spanish



### Brady Electrical Plug Lockouts

- Plug lockouts prevent electrical plugs from being inserted into a wall outlet. Use when plug will not remain under the exclusive control of the person performing service or maintenance
- Made of rugged polypropylene

Catalog #	Dimensions	Description
65674	2" x 2" x 3 1/2", 1/2" diameter hole for cable	Small 110V Plugout
65675	3 1/4" x 3 1/4" x 7", 1" diameter hole for cable	Large 220/500V Plugout



### Electrical/Pneumatic Plug Lockout

- Accommodates a large variety of electrical plugs up to 3 1/2" in diameter and 5" in length as well as male air hose connectors
- Holes accommodate electrical cord or "necked down" pneumatic male fittings commonly attached to compressed air hose
- Works on 110V, 220V & 550V plugs
- Made of Polystyrene material

Catalog #	Description
PL027E	Electrical/Pneumatic Plug LO



### Push Button Lockouts

- Guard against unauthorized operation or accidental activation.
- Two sizes to accommodate standard NEMA 30.5 mm and IEC 22.5 mm buttons
- Emergency Stop Safety Covers:
  - Permanently install over push/pull or twist-release emergency stops
  - Durable metal bar locks button in the depressed (off) position when lock shackle is inserted
- Push Button Safety Covers:
  - 104602: Clear Lexan hinged cover completely covers button, preventing access (white legend plate included)
  - 104603: Clear Lexan & metal hinged cover completely covers button preventing access

Catalog #	Description
104600	Emergency Stop Safety Covers - NEMA 30.5 mm
104601	Emergency Stop Safety Covers - IEC 22.5 mm
104602	Push Button Safety Covers - NEMA 30.5 mm
104603	Push Button Safety Covers - IEC 22.5 mm



Emergency Stop Cover  
NEMA 30.5mm (104600)



Emergency Stop Cover  
IEC 22.5mm (104601)



Push Button Cover  
NEMA 22.5mm (104603)



Push Button Cover IEC  
30.5 mm (104602)

## ELECTRICAL LOCKOUT

## ELECTRICAL LOCKOUT



### Stoppower™ Plug Lockouts

- Ideal for office equipment and other frequently locked out cords
- For use on 2 or 3 pronged polarized plugs
- Cord cannot be plugged in with Stoppower™ in place
- Device cannot be removed without a key
- Standard pack: 1 device/ package

Catalog #	Description
65673	Red

To order multiple Stoppower Plug Lockouts that are keyed alike, use catalog #98209



### Hubbell Plugout™

- Two sizes available to fit most heavy industrial plug applications
- Small version accepts plugs with maximum 2<sup>3</sup>/<sub>4</sub>" diameter and 4<sup>3</sup>/<sub>4</sub>" length with 1" cord
- Large version accepts plugs with maximum 4<sup>1</sup>/<sub>2</sub>" diameter and 10<sup>3</sup>/<sub>20</sub>" length with 1<sup>9</sup>/<sub>20</sub>" cord
- Standard pack: 1 device/ package

Catalog #	Description
65695	Small Plugout™
65968	Large Plugout™



### Opaque Wall Switch Lockout

- Clear plastic lockout uses existing wall plate screws to mount
- Patented non-hinge design
- Made of strong, clear polycarbonate
- Lock not included

Catalog #	Description
WSLO	Wall Switch Lockout

### Clear Wall Switch Lockout

- Device may be used with most wall-mounted switches
- Easy to install using existing screws
- High visibility red color
- Locks switch in "on" or "off" position
- Lock not included

Catalog #	Quantity
65392	1/pack
65696	6/pack



Clear Wall Switch Lockout

Opaque Wall Switch Lockout

### Fuse Lockout Devices

- Unique locking mechanism prevents device from being accidentally removed from fuse block
- Available in two sizes for most commonly used fuses

Catalog #	Dimensions
65750	1 <sup>3</sup> / <sub>32</sub> ", 6/pack
65751	9 <sup>1</sup> / <sub>16</sub> ", 6/pack



### Fuse Blockout Devices

- Block out 1/4" to 11/16" and blade type fuses
- Use these highly visible devices in conjunction with Brady Lockout Tags to comply with OSHA's Lockout/Tagout Standard

Catalog #	Dimensions	Description
65690	1/4", 9/32", 13/32" & 9/16"	Fuses
65691	13/16", 1 1/16"	Blade Type Fuses



## GAS & AIR LINE LOCKOUTS

### AIR LINE LOCKOUT

Air Line Lockout and Pneumatic Lockout are critical for de-energizing and isolating compressed air sources of power. Brady developed pneumatic quick-disconnect lockouts that easily attach to the male fitting, effectively prohibiting any pneumatic connection without the inconvenience of installing in-line lockout valves. The pneumatic lockouts are also convenient for storage and holding the air hose while it's not in use, keeping your facility orderly and air hoses from getting tangled. Air Line lockouts will snap on over the regulator knob to deny access to the air line regulator.



### Pneumatic Quick-Disconnect Lockout

- Isolates pneumatic energy without the expense and inconvenience of installing in-line lockout valves
- Device is applied to the male fitting, isolating equipment from all compressed air sources
- Accommodates the majority of 1/4", 1/8", 1/2" male fittings
- Hole in center of device allows for permanent storage on an air hose and a loop on the side can be used to hang the hose and lockout device
- Lockout using a padlock with 1/4" or 9/32" shackle

Catalog #	Quantity
64221	1/pack
65645	6/pack



### SMC Air Line Regulator Lockout

- Enables regulator to be locked in the on, off or throttled position
- Easy installation: remove snap cap, install lockout on regulator rod, snap replacement cap on regulator
- Comes with lockout, cap and allen wrench

Catalog #	Description
64539	Lockout for Miniature SMC Models AR2000/NAR2000
64540	Lockout for Intermediate SMC Models AR3000/NAR3000

GAS & AIR LINE  
LOCKOUTS

GAS LOCKOUT



**Snap Cap™ Gas Cylinder Lockout**

- Designed to fit most North American high and low pressure gas cylinders
- SNAP CAP cylinder safety device meets DOT standards
- The SNAP CAP denies access to the main cylinder control and regulator attachment
- Welded steel construction and powder coated for many years of use

Catalog #	Qty
90496	6.5" x 3 1/8" x 11 UN, High Pressure Fine Thread
95137	6.5" x 3 1/2" x 11 UN, Low Pressure Fine Thread
95138	6.5" x 3 1/8" x 11 UN, High Pressure Coarse Thread
95139	6.5" x 3 1/2" x 11 UN, Low Pressure Coarse Thread



**PRINZING Gas Cylinder Lockout**

- Prevents access to the main cylinder valve
- No need to match your lockout device to varying diameters and threads of cylinder caps
- Accommodates neck rings up to 3 1/2" diameter
- Installs in seconds to save time


Catalog #	Description
LM023E	Gas Cylinder Lockout



## CABLE AND CHAIN LOCKOUT

# CABLE & CHAIN LOCKOUT

- Greater versatility - used in variety of applications
- Able to lockout multiple items with one device
- Great for isolating unconventional devices
- Portable and ease of usage compared to Chain lockout



## All Purpose Cable Lockout

- Compact, lightweight body made of rugged Isoplast Polymer
- Ergonomic design makes it a "cinch" to tighten cable – hold device in one hand and cinch tight with the other
- Superior chemical, corrosion and temperature resistance properties
- Two types of interchangeable cables:
  - Nonconductive nylon cable ( $\frac{1}{8}$ " diameter)
  - Sheathed metal cable ( $\frac{3}{16}$ " diameter, vinyl coating)
- Built-in cable loop keeps cable neatly coiled when stored, also keeps extra cable from dangling loose and posing a hazard when in use
- 4 lock holes in handle accommodate most lock shackles and hasps
- Max. Service temperature of cables:
  - Sheathed Metal: -30°F to 180°F
  - Non-Conductive Nylon: -40°F to 200°F

Catalog #	Dimensions	Description
50943	8'	APCLO with sheathed metal cable
50941	8'	APCLO with non-conductive nylon cable
50944		APCLO without cable

## Sheathed Metal Cables (Sold Separately)

Catalog #	Dimensions	Description
50947	8'	Sheathed metal cable
50950	12'	Sheathed metal cable
50953	16'	Sheathed metal cable
50956	20'	Sheathed metal cable

## Non-conductive Nylon Cables (Sold Separately)

Catalog #	Dimensions	Description
50945	8'	Non-conductive Nylon cable
50948	12'	Non-conductive Nylon cable
50951	16'	Non-conductive Nylon cable
50954	20'	Non-conductive Nylon cable

## Mini Cable Lockout


- Perfect for use on disconnect switches, small gate valves, etc
- Extremely compact and portable. Cable stored internally
- Push-button self-winding mechanism automatically cinches cable tight
- Body made of impact modified nylon
- Superior chemical, corrosion and temperature resistant properties.
- Comes with vinyl-coated steel cable or nonconductive nylon cable
- 6 lock holes accommodate most padlock shackles and hasps
- Cable dimensions:  $\frac{1}{16}$ " outside diameter x 8' length



Catalog #	Dimensions	Description
50940	4" diameter x $1\frac{3}{4}$ " deep	Mini Cable Lockout w/ Steel Cable
51442	4" diameter x $1\frac{3}{4}$ " deep	Mini Cable Lockout w/ Nylon Cable

## CABLE AND CHAIN LOCKOUT

## CABLE & CHAIN LOCKOUT



### Original Cable Lockout

- Brady's original cable lockout
- Body made of impact modified nylon, available in red, blue or yellow
- Comes with 6' galvanized steel cable ( $\frac{1}{8}$ " outside diameter)

### Cable Lockout Device with 6 ft. cable

Catalog #	Description
65318	Red
45191	Blue
45192	Yellow

### Additional Cables

Catalog #	Description
65319	8 ft. cable
65320	10 ft. cable

Other cable lengths available upon request



### PRINZING Economy Cable Lockout

- Unique lockout device accepts up to six  $\frac{9}{32}$ " diameter padlocks
- Cable Diameter  $\frac{3}{16}$ " outside diameter
- Plastic-coated steel cable comes in two lengths: 6' and 10'

Catalog #	Description
CABLO	Cable Lockout Device with 6' cable
CABLO-10	Cable Lockout Device with 10' cable



### PRINZING Chain Lockout Kit

- An inexpensive way to lockout assorted applications

#### Components:

- 3 x  $1\frac{1}{2}$ " Steel Lockout Hasp (T220)
- 3 x Padlocks (LCO44-RD)
- 3 x Lockout Tags with Ties
- 1 x 48" Chain
- 1 x Durable Carrying Case (7" x 12" x 5")

Catalog #	Description
LK041R	Single Lockout Kit
LK042R	Double Lockout Kit*

\*Same as LK041R plus an extra chain



### PRINZING Cable Lockout Kit

- Cable lockout kit with handy carrying case

#### Components:

- 2 x Cable Lockout Devices (CABLO)
- 2 x Blue Prinzing Padlocks (LC041-BU)
- 1 x 1" Steel Lockout Hasp (T218)
- 2 x English-labelled Lockout Tags with Ties
- 1 x Rugged Polyethylene Carrying Case (7" x 12" x 5")

Catalog #	Description
LK520B	Cable Lockout Kit



# VALVE LOCKOUT

# VALVE LOCKOUT



## Plug Valve Lockout

- Four Sizes to Fit Most 1" to 8" Diameter Manually-Actuated Plug Valves
- Effective Fit for Difficult-to-Secure Plug Valves
- Durable and Tamper-Resistant
- Service Temperatures from -25°F to 200°F
- Compact in Size and Easy to Use



With Brady's Plug Valve Lockout, you can easily and effectively secure manual plug valves to OSHA-compliant standards

Catalog #	Description
113231	Plug Valve Lockout for up to 7/8" Stem Diameter
113232	Plug Valve Lockout for 15/16" - 1 1/8" Stem Diameter
113233	Plug Valve Lockout for 1 3/4" - 2 1/8" Stem Diameter
113234	Plug Valve Lockout for 2 5/16" - 2 1/2" Stem Diameter

## Universal Valve Lockout

- Versatile, rugged, easy to use, lightweight
- Made of industrial-grade steel and nylon for extra impact and chemical resistance
- New open-ended clamp fits over closed rings, wide handles
- Can also be used to lock out large levers, T-handles and other hard-to-secure mechanical devices
- Cable attachment offers choice of 1/8" nonconductive nylon or rustproof sheathed metal cable
- Small UVLO: for use on handle widths up to 1" (max handle thickness of 0.6")
- Large UVLO: for use on handle widths up to 1.6" (max handle thickness of 1.1")
- Patent No. 5,415,017 and 7,207,198

### Universal Valve Lockout - Complete Sets

Catalog #	Description
51394	Small UVLO with 8' Sheathed Cable Attachment & Blocking Arm
51390	Small UVLO with 8' Nylon Cable Attachment & Blocking Arm
51392	Large UVLO with 8' Sheathed Cable Attachment & Blocking Arm
51388	Large UVLO with 8' Nylon Cable Attachment & Blocking Arm

### Universal Valve Lockout - Individual Components

Catalog #	Description
50924	Small UVLO Base Clamping Unit
50899	Large UVLO Base Clamping Unit
65402	Small Blocking Arm
65403	Large Blocking Arm
51395	Cable Attachment with 8' Sheathed Cable
50932	Cable Attachment with 8' Nylon Cable

Other cable lengths also available



No need for multiple types and sizes of lockouts - now one device does it all!



Use blocking arm to lock out quarter-turn ball valves



Use cable attachment to lock out gate valves



Use two blocking arms to lock out 3-, 4- or 5-way valves, or to lock valves in the "on", "off", or "throttled" position for operational control



Clamp attaches to butterfly handles, preventing trigger handle from being squeezed, ensuring valve cannot be repositioned

## VALVE LOCKOUT

## VALVE LOCKOUT



### Adjustable Gate Valve Lockout

- Versatile lockout adjusts to fit 1" to 6 1/2" valve handles, replacing 3 conventional gate valve lockouts
- Durable polypropylene is resistant to temperature changes from -13°F to 194°F
- Compact for easy carrying and storage
- Comes with danger labels in English, Spanish and French

Catalog #	Description
64057	Adjustable Gate Valve Lockout



### Gate Valve Lockouts

- Made of rugged injection-molded polypropylene
- Service temperatures from -25°F to 200°F
- Unique knockout center accommodates OS&Y or "rising stem" valves
- Available in 5 sizes and 4 colors
- Accepts locks with shackles up to 3/8" in diameter
- Supplied with danger labels in English, Spanish and French



Valves handle	Catalog #			
Diameter	Red	Yellow	Green	Blue
1" - 2 1/2"	65560	65590	65595	65585
2 1/2" - 5"	65561	65591	65596	65586
5" - 6 1/2"	65562	65592	65597	65587
6 1/2" - 10"	65563	65593	65598	65588
10" - 13"	65564	65594	65599	65589

### Standard Ball Valve Lockout

- Easy to use, single-piece design locks quarter-turn ball valves in OFF position
- Two sizes fit most valves up to 3"
- 65692, 65669 and 65693 are made of powder-coated steel
- 65666 is made of super-tough nylon (service temp -40° to 248° F)



Catalog #	Max Shackle Diameter	Valve Size/ Pipe Diameter	Max Handle Width (inches)	Max Handle Thickness (inches)
65666	9/32"	1/4" - 1"	1 1/2"	3/4"
65692	3/8"	1/4" - 1"	1 1/2"	3/4"
65669	9/32"	1 1/4" - 3"	2 1/10"	1 1/4"
65693	3/8"	1 1/4" - 3"	1 9/10"	1 1/4"

### PRINZING Ball Valve Lockout

- Made from ultra-tough polypropylene
- Small lockout (BS07A) locks out pipes 1/2" to 2 1/2" in diameter
- Small lockout can also be used to lock valves OPEN on pipes from 1/2" to 1 1/4" in diameter
- Large lockout (BS08A) locks out pipes 2" to 8" in diameter
- Available in 4 colors
- Patent No: 6,622,536




Description	Red	Blue	Green	Yellow
Small Ball Valve Lockout	BS07A	BS07A-BU	BS07A-GN	BS07A-YW
Large Ball Valve Lockout	BS08A	BS08A-BU	BS08A-GN	BS08A-YW



# LOCKOUT BOARDS

# LOCKOUT BOARDS



## 5-Lock Board

- Includes 5 padlocks (99552 or 99500), one 1" metal hasp (65375), one 1 1/2" metal hasp (65376) and 12 heavy duty tags (65520)

Catalog #	Dimensions	Description
51181	11 1/2" x 15 1/2"	5-Lock Board (Includes Brady Safety Padlocks)
51186	11 1/2" x 15 1/2"	5-Lock Board (Includes Brady 3/4" Steel Padlocks)
50989	11 1/2" x 15 1/2"	5-Lock Board (Board Only)



## 10-Lock Board

- Includes 10 padlocks (99552 or 99500), two 1" hasps (65375), two 1 1/2" hasps (65376) and 12 heavy duty tags (65520)

Catalog #	Dimensions	Description
51187	13 1/2" x 13 1/2"	10-Lock Board (Includes Brady Safety Padlocks)
51188	13 1/2" x 13 1/2"	10-Lock Board (Includes Brady 3/4" Steel Padlocks)
50990	13 1/2" x 13 1/2"	10-Lock Board (Board Only)



## 20-Lock Board

- Includes 20 padlocks (99552 or 99500), two 1" hasps (65375), two 1 1/2" hasps (65376) and 24 heavy duty tags (65520)

Catalog #	Dimensions	Description
51189	23 1/2" x 11 1/2"	20-Lock Board (Includes Brady Safety Padlocks)
51194	23 1/2" x 11 1/2"	20-Lock Board (Includes Brady 3/4" Steel Padlocks)
50991	23 1/2" x 11 1/2"	20-Lock Board (Board Only)



## 36-Lock Board


- Includes 36 padlocks (99552 or 99500), three 1" hasps (65375), three 1 1/2" hasps (65376) and 36 heavy duty tags (65520)

Catalog #	Dimensions	Description
51195	21 1/2" x 23 1/2"	36-Lock Board (Includes Brady Safety Padlocks)
51196	21 1/2" x 23 1/2"	36-Lock Board (Includes Brady 3/4" Steel Padlocks)
50992	21 1/2" x 23 1/2"	36-Lock Board (Board Only)



## PADLOCK CENTERS

## PADLOCK CENTERS



### Padlock Stations

- Constructed of 14 gauge steel with red plastic coating
- Padlocks not included

Catalog #	Dimensions	Description
LR060E	2 1/4" x 3" x 1 1/4"	Small Padlock Station
LR360E	3" x 16" x 1 1/4"	Large Padlock Station



### Steel Padlock Control Centers

- Red powder-coated 22 gauge steel with white silk-screened graphics
- Each nickel coated metal hook can hold 2 locks
- Two sizes available for holding 16 or 32 locks
- Two keys supplied for cabinet lock
- Padlocks sold separately

Catalog #	Dimensions	Description
LR008E	10" x 12" x 2"	Small Padlock Control Center
LR018E	15 1/2" x 18" x 2"	Large Padlock Control Center



### Enclosed Padlock Storage Modules

- Provides safe storage and controls access to padlocks
- Constructed of sintra with lockable, transparent acrylic doors
- Each metal hook can hold 2 locks
- Two sizes available for holding 16 or 40 locks
- Padlocks sold separately

Catalog #	Description	Description
65240	15" x 15" x 3 1/2"	Small Padlock Storage Module
65241	30" x 15" x 3 1/2"	Large Padlock Storage Module



### Did you know?

Brady uses a space-saving design to hold more locks. Board is made of 7.7mm thick yellow acrylic with acrylic lock rails. Tag pockets, made of clear polycarbonate, hold tags up to 76.2mm wide.

# PADLOCK MANAGEMENT SYSTEM



## Padlock Management System

- Reduces theft by controlling access to locks
- 7 different sizes hold from 1 to 75 locks (10 lock station shown)
- Each lock individually secured into a numbered port on the lock board
- Locks can only be removed by personnel with assigned access keys. Access key is retained in lock board until lock is returned
- Employees photos can be applied to locks. See below for file requirements\*

Catalog #	Dimensions	Locks Per Unit
CST1154	5 <sup>3</sup> / <sub>8</sub> " x 21 <sup>3</sup> / <sub>8</sub> " x 4"	5
CST1154	7" x 21 <sup>3</sup> / <sub>8</sub> " x 4"	10
CST1154	10" x 21 <sup>3</sup> / <sub>8</sub> " x 4"	15
CST1154	17 <sup>1</sup> / <sub>2</sub> " x 21 <sup>3</sup> / <sub>8</sub> " x 4"	25
CST1154	32 <sup>1</sup> / <sub>2</sub> " x 21 <sup>3</sup> / <sub>8</sub> " x 4"	50
CST1154	47 <sup>3</sup> / <sub>8</sub> " x 21 <sup>3</sup> / <sub>8</sub> " x 4"	75

For Keyed Alike or Master Keyed Padlocks, call your local Brady Distributor for pricing

### SPECIFY THE FOLLOWING TO ORDER YOUR MANAGEMENT SYSTEM

#### 1. LOCKS PER UNIT (Choose one)

- |                                                                                                                         |                                                                                                                             |
|-------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| <input type="checkbox"/> 5 locks (board size – 5 <sup>3</sup> / <sub>8</sub> " x 21 <sup>3</sup> / <sub>8</sub> " x 4") | <input type="checkbox"/> 25 locks (board size – 17 <sup>1</sup> / <sub>2</sub> ", x 21 <sup>3</sup> / <sub>8</sub> ", x 4") |
| <input type="checkbox"/> 10 locks (board size – 7" x 21 <sup>3</sup> / <sub>8</sub> " x 4")                             | <input type="checkbox"/> 50 locks (board size – 32 <sup>1</sup> / <sub>2</sub> ", x 21 <sup>3</sup> / <sub>8</sub> ", x 4") |
| <input type="checkbox"/> 15 locks (board size – 10" x 21 <sup>3</sup> / <sub>8</sub> " x 4")                            | <input type="checkbox"/> 75 locks (board size – 47 <sup>3</sup> / <sub>8</sub> ", x 21 <sup>3</sup> / <sub>8</sub> ", x 4") |

#### 2. COLOR OF LOCKS (Total must equal choice above)

- |                                         |                                      |
|-----------------------------------------|--------------------------------------|
| <input type="checkbox"/> Yellow ____Qty | <input type="checkbox"/> Red ____Qty |
| <input type="checkbox"/> Green ____Qty  |                                      |

#### 3. KEYING

- |                                          |                                                                               |
|------------------------------------------|-------------------------------------------------------------------------------|
| <input type="checkbox"/> Keyed ALIKE     | <input type="checkbox"/> Master Key w/ Keyed Alike ____Qty of Master Keys     |
| <input type="checkbox"/> Keyed DIFFERENT | <input type="checkbox"/> Master Key w/ Keyed Different ____Qty of Master Keys |

#### 4. COLOR OF ACCESS KEYS (Total must equal no. of locks)

- |                                         |                                         |
|-----------------------------------------|-----------------------------------------|
| <input type="checkbox"/> Yellow ____Qty | <input type="checkbox"/> Green ____Qty  |
| <input type="checkbox"/> White ____Qty  | <input type="checkbox"/> Blue ____Qty   |
| <input type="checkbox"/> Red ____Qty    | <input type="checkbox"/> Silver ____Qty |

(Other colors also available)

### SPECIFY THE FOLLOWING TO ORDER ADDITIONAL LOCKS OR ACCESS KEYS

#### 1. ADDITIONAL LOCKS

- |                                         |                                         |
|-----------------------------------------|-----------------------------------------|
| <input type="checkbox"/> Yellow ____Qty | <input type="checkbox"/> Green ____Qty  |
| <input type="checkbox"/> White ____Qty  | <input type="checkbox"/> Blue ____Qty   |
| <input type="checkbox"/> Red ____Qty    | <input type="checkbox"/> Silver ____Qty |

#### 3. KEYING

- |                                          |                                                                               |
|------------------------------------------|-------------------------------------------------------------------------------|
| <input type="checkbox"/> Keyed DIFFERENT | <input type="checkbox"/> Master Key w/ Keyed Alike ____Qty of Master Keys     |
| <input type="checkbox"/> Keyed ALIKE     | <input type="checkbox"/> Master Key w/ Keyed Different ____Qty of Master Keys |

#### 4. ADDITIONAL ACCESS KEYS

- |                                         |                                         |
|-----------------------------------------|-----------------------------------------|
| <input type="checkbox"/> Yellow ____Qty | <input type="checkbox"/> Green ____Qty  |
| <input type="checkbox"/> White ____Qty  | <input type="checkbox"/> Blue ____Qty   |
| <input type="checkbox"/> Red ____Qty    | <input type="checkbox"/> Silver ____Qty |

(Other colors also available)

## GROUP LOCKOUT BOXES

# GROUP LOCKOUT BOXES

A great idea for group lockout involving a large number of workers and equipment, offering more advantages than using hasps

Brady group lockout products are ideal for situations where a large number of workers have a high volume of energy control points that need to be locked out. With lock boxes, single job locks, multiple padlock management systems and lockout tool storage, Brady has several options for group lockout that can save time, track lockout workers, store padlocks and keep group lockout procedures efficient and organized.



### HOW GROUP LOCKOUT BOXES WORK:

- Supervisor uses a single job lock on each energy control point to lock out equipment
- Keys for job locks are put in a lockout box
- Each worker applies his own lock to the lock box. As long as any one worker's lock remains on the lockout box, the keys to the job locks cannot be accessed, and the energy isolating devices cannot be operated. Each employee retains exclusive control, as required by OSHA

### HOW GROUP LOCKOUT BOXES CAN SAVE YOU LOTS OF MONEY:

- Example: Assume 5 workers need to lock out 10 energy control points
- Using hasps, 50 locks are required (all 5 workers must apply individual locks to each control point)
- Using a lockout box, only 15 locks are required (10 job locks applied to control points and 5 employee locks applied to lockout box). That is 70% fewer locks!
- Less weight hanging from the energy point – 1 lock instead of 5!
- Finally, checking the locks on the lock box allows you track who is still working. With hasps, you need to walk around to each energy control point to see whose lock is still in place.

## Portable Metal Group Lockout Boxes

- Made of heavy duty steel, powder-coated for extra rust resistance
- 13 lock holes on lid, plus lockable clasp on front (locks not included)
- Standard lock box
  - When used for storage, holds up to 40 padlocks
- Extra-large lock box
  - When used for storage, holds up to 75 padlocks

Catalog #	Dimensions	Description
65699	6" x 9" x 3 1/2"	Red - Standard
51171	6" x 7 3/8" x 9 1/2"	Red - Extra-Large

## Combined Lock Storage / Group Lockout Box

- Handy box features a lockable storage compartment and a group lockout compartment.
- Made of heavy duty steel, powder coated for extra rust resistance
- Group lockout compartment has clear Lexan window with keyhole slot
- Standard box
  - Storage compartment holds approx. 50 padlocks
  - 17 padlock holes in group lock box lid
- Extra -large lock box
  - Storage compartment holds approx. 125 padlocks
  - 34 padlock holes in group lock box lid

Catalog #	Dimensions	Description
105716	8 1/2" x 6" x 6"	Standard
105717	10 1/2" x 9" x 9"	Large



# GROUP LOCKOUT BOXES



## Portable Plastic Group Lockout Box

- Injection molded using Isoplast Polymers for rugged durability
- Won't corrode! Excellent chemical and heat resistance properties
- Lock rails hold up to 16 padlocks (locks not included)
- Slot in front allows keys to be inserted when box is locked
- Transparent polycarbonate windows let you view contents
- Pre-drilled holes in back allow for easy wall-mounting
- Comes with 12 hooks for hanging keys, locks, etc., inside box
- Patent Applied For

Catalog #	Dimensions	Description
50937	7 1/2" x 8 1/2" x 4 1/4"	Portable Plastic Lock Box



## Acrylic Wall-Mounted Group Lockout Boxes

- Made of acrylic plastic
- Pre-drilled holes in back for easy wall mounting
- Transparent front cover allows easy viewing of contents
- Pre-attached plastic hooks for hanging keys, tag stubs, etc
- Available in 3 sizes

Catalog #	Description	Max. Number of padlocks	Number of key hooks
LG003E	Small: 6" x 6" x 2 1/2"	6	3
LG008E	Medium: 7 1/2" x 12" x 2 1/2"	10	8
GLOBOX	Large: 7 1/2" x 15 3/4" x 2 1/2"	14	18



## Miniature Wall Lock Box

- Injection molded for extra durability
- Won't corrode! Excellent chemical and heat resistance properties
- Lock rails hold up to 8 padlocks
- Transparent window lets you view contents from outside
- Slot-in front allows keys to be inserted when locked
- Pre-drilled holes in back allow for easy wall-mounting
- Comes with 6 hooks for hanging keys, locks, etc, inside

Catalog #	Dimensions	Description
50938	6 1/5" x 4" x 5 1/2"	Miniature Wall lock Box
50939	12/pack	Extra Key Hooks Only

## GROUP LOCKOUT BOXES

# GROUP LOCKOUT BOXES



### Metal Wall-Mounted Group Lockout Boxes

- Made of durable, powder-coated steel with key slot on top
- Includes clear Lexan window that slides out when locks are removed
- Comes with key pegs and ID labels to simplify key management
- Predrilled holes and hardware included for quick mounting
- Small lock box:
  - 7 key pegs that hold 5 keys each
  - 7 lock holes along bottom
- Large lock box:
  - 15 key pegs that hold 5 keys each
  - 12 lock holes along bottom

Catalog #	Dimensions	Description
105714	7" x 8" x 2 1/4"	Small Metal Lock Box
105715	7" x 16" x 2 1/4"	Large Metal Lock Box

### Portable / Wall Group Lockout Box

- Made of yellow powder-coated metal
- Accommodates 8-10 locks (depending on lock size)
- Can be used alone or in combination with Metal Lockout Cabinet


Catalog #	Dimensions	Description
LG252M	6" x 15" x 3"	PRINZING Metal Wall Lock Box



### SHOCK-STOP™ Group Lockout Box

- Combines lock box with storage board for hasps
- Lock box accepts up to 6 locks and provides rail for storing locks when not in use
- Comes standard with two SHOCK-STOP™ hasps
- Mounting hardware and instructions included

Catalog #	Dimensions	Description
87692	16 1/2" x 10 1/2" x 2 1/2"	Group Lock Box
87693	5/pack	Hasp Only



## LOCKOUT KITS

### PERSONAL LOCKOUT KITS

Personal lockout kits come equipped with keyed-alike padlocks, allowing all the locks in a kit to be opened with a single key. This simplifies key management and ensures that employees can quickly and easily find the right key. For kits containing padlocks that are keyed different (each padlock has its own unique key), see the standard lockout kits on the following pages. Or select a personal lockout kit without padlocks, and purchase the padlocks separately.



#### Personal Padlock Pouch

- Compact kit that contains padlocks, tags and hasps

##### Components:

- 2 x 1" Group Lockout Hasps (65375)
- 2 x Heavy Duty Lockout Tags (65520) with Nylon Cable Ties
- 2 x Keyed-alike Safety Padlocks (99552) or Steel Padlocks (99500)
- 1 x Lockout Belt Pouch (51172)

Catalog #	Description
105969	Padlock kit with Keyed-Alike Safety Padlocks
105970	Padlock kit with Keyed-Alike Steel Padlocks



#### Personal Breaker Lockout Pouch

- Pouch contains 1 each of our most popular circuit breaker lockouts
- Covers 120v/277v and 480/600v breakers in single and multi-pole configurations

##### Components:

- 1 x 120/277V Clamp-On Breaker Lockout with cleats (65396)
- 1 x 480/600V Clamp-On Breaker Lockout with cleats (65397)
- 1 x Universal Multi-pole Breaker Lockout (66321)
- 2 x 1" Group Lockout Hasps (65375)
- 2 x Heavy Duty Lockout Tags (65520) with Nylon Cable Ties
- 1 x Lockout Belt Pouch (51172)

Catalog #	Description
105966	Personal Breaker Lockout Pouch (Kit)
105967	Kit with 2 Keyed-Alike Safety Padlocks
105968	Kit with 2 Keyed-Alike Steel Padlocks



#### Personal Breaker Lockout Kit

- Tool box contains 2 each of our most popular breaker lockouts
- Covers 120v/277v and 480/600v breakers in single and multi-pole configurations

##### Components:

- 2 x 120/277V Clamp-On Breaker Lockouts with cleats (65396)
- 2 x 480/600V Clamp-On Breaker Lockouts with cleats (65397)
- 2 x Universal Multi-pole Breaker Lockouts (66321)
- 3 x 1" Red Lockout Hasps (65375)
- 3 x Heavy Duty Lockout Tags (65520) with Nylon Cable Ties
- 1 x Small Lockout Toolbox (105905)

Catalog #	Description
105963	Personal Breaker Lockout Kit
105964	Kit with 3 Keyed-Alike Safety Padlocks
105965	Kit with 3 Keyed-Alike Steel Padlocks

## LOCKOUT KITS

## PERSONAL LOCKOUT KITS



### Personal Basic Lockout Kit

- Contains the basic devices needed to lockout common breakers, valves and plugs

#### Components:

- 1 x 1/2" - 2 1/2" Small Ball Valve Lockout (BS07A)
- 1 x 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 x 120/277V Clamp-On Breaker Lockout with cleat (65396)
- 1 x Universal Multi-pole Breaker Lockout (66321)
- 1 x Small 110V Electrical Plug Lockout (65674)
- 2 x 1" Lockout Hasps (65375)
- 2 x Heavy Duty Lockout Tags (65520) with Nylon Cable Ties
- 1 x Small Lockout Toolbox (105905)

Catalog #	Description
104794	Personal Basic Lockout Kit
104795	Kit with 2 Keyed-alike Safety Padlocks
104796	Kit with 2 Keyed-alike Steel Padlocks



Includes Mini Cable Lockout, featured on page 28-29

### Personal Electrical Lockout Kit

- Provides lockouts for use on most circuit breakers, electrical plugs and disconnect switches

#### Components:

- 1 x Mini Cable Lockout (50940)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 2 x 120/277V Clamp-On Breaker Lockouts with cleats (65396)
- 1 x 480/600V Clamp-On Breaker Lockout with cleat (65397)
- 2 x Universal Multi-pole Breaker Lockout (66321)
- 1 x Oversized Breaker Lockout (65329)
- 3 x 1" Group Lockout Hasps (65375)
- 3 x Heavy Duty Lockout Tags (65520) with Nylon Cable Ties
- 1 x Medium Lockout Toolbox (105906)

Catalog #	Description
105960	Personal Electrical Lockout Kit
105961	Kit with 3 Keyed-alike Safety Padlocks
105962	Kit with 3 Keyed-alike Steel Padlocks



Includes Plug Valve Lockouts, featured on page 30-31

### Personal Valve Lockout Kit

- Contains devices for locking out a wide range of gate and ball valves

#### Components:

- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 1 x 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 x 1/2" - 2 1/2" Small Ball Valve Lockouts (BS07A)
- 1 x All Purpose Cable Lockout (50943)
- 3 x 1" Group Lockout Hasps (65375)
- 3 x Heavy Duty Lockout Tags (65520) with Nylon Cable Ties
- 1 x Medium Lockout Toolbox (105906)

Catalog #	Description
105957	Personal Valve Lockout Kit
105958	Kit w/ 3 Keyed-Alike Safety Padlocks
105959	Kit w/ 3 Keyed-Alike Steel Padlocks



Includes Plug Valve Lockouts, featured on page 30-31

### Personal Valve & Electrical Lockout Kit

- Provides everything you need to lockout breakers, plugs and valves of various types and sizes

#### Components:

- 1 x All Purpose Cable Lockout (50943)
- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 1 x Plug Valve Lockout for stem dia up to 7/8" (113231)
- 1 x Plug Valve Lockout for stem dia 9/32" - 1 3/8" (113232)
- 1 x 1/2" - 2 1/2" Small Ball Valve Lockout (BS07A)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 2 x 120/277V Clamp-On Breaker Lockouts with cleats (65396)
- 1 x 480/600V Clamp-On Breaker Lockout with cleat (65397)
- 2 x Universal Multi-pole Breaker Lockouts (66321)
- 3 x 1" Group Lockout Hasps (65375)
- 3 x Heavy Duty Lockout Tags (65520) with Nylon Cable Ties
- 1 x Medium Lockout Toolbox (105906)

Catalog #	Description
105954	Personal Valve & Electrical Kit
105955	Kit with 3 Keyed-Alike Safety Padlocks
105956	Kit with 3 Keyed-Alike Steel Padlocks



## LOCKOUT KITS

### STANDARD LOCKOUT KITS

The Standard Lockout Kits shown can be purchased with or without padlocks and tags. The padlocks included in these kits are keyed differently (each lock has its own unique key). For kits with keyed-alike padlocks (all locks can be opened with the same key), see Personal Lockout Kits.



### Portable Padlock Pouch

- Portable kit with padlocks, tags and hasps

#### Components:

- 2 x Choose between keyed-different safety padlocks (99552) or steel padlocks (99500)
- 2 x Heavy Duty Lockout Tags (65520) with Nylon Cable Ties
- 1 x 1" Group Lockout Hasp (65375)
- 1 x 1.5" Group Lockout Hasp (65376)
- 1 x Lockout Belt Pouch (51172)

Catalog #	Description
99290	Kit with 2 Safety Padlocks
99292	Kit with 2 Steel Padlocks

### Breaker Lockout Sampler Pouch

- Contains one each of our most popular breaker lockout

#### Components:

- 1 x 120V Snap-On Breaker Lockout (65387)
- 1 x 120/277V Clamp-On Breaker Lockout with cleat (65396)
- 1 x 480/600V Clamp-On Breaker Lockout with cleat (65397)
- 1 x Universal Multi-Pole Breaker Lockout (66321)
- 1 x Oversized Breaker Lockout (65329)
- 1 x Lockout Belt Pouch (51172)

#### Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
99293	Breaker Lockout Sampler Toolbox (Kit)
99296	Kit with 2 Safety Padlocks & 2 Tags
99297	Kit with 2 Steel Padlocks & 2 Tags

### 120/277V Breaker Lockout Pouch

- Contains all the devices you need to lockout most 120/277V breakers

#### Components:

- 2 x 120V Snap-On Breaker Lockouts (65387)
- 2 x 120/277V Clamp-On Breaker Lockout with cleats (65396)
- 2 x Universal Multi-Pole Breaker Lockout with cleats (66321)
- 1 x Lockout Belt Pouch (51172)

#### Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
99300	120/277V Breaker Lockout Pouch (Kit)
99302	Kit with 2 Safety Padlocks & 2 Tags
99303	Kit with 2 Steel Padlocks & 2 Tags

## LOCKOUT KITS

### STANDARD LOCKOUT KITS



Includes Mini Cable Lockout

### Breaker Lockout Toolbox

- Everything you need to lockout most circuit breakers

#### Components:

- 1 x Mini Cable Lockout (50940)
- 2 x 120V Snap-On Breaker Lockout (65387)
- 2 x 120/277V Clamp-On Breaker Lockouts with cleats (65396)
- 2 x 480/600V Clamp-On Breaker Lockouts with cleats (65397)
- 1 x Universal Multi-Pole Breaker Lockout (66321)
- 1 x Oversized Breaker Lockout (65329)
- 1 x Lockout Toolbox (65290)

#### Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
99305	Breaker Lockout Toolbox (Kit)
99307	Kit with 2 Safety Padlocks & 2 Tags
99308	Kit with 2 Steel Padlocks & 2 Tags



Includes Mini Cable Lockout

### Electrical Lockout Toolbox

- All the basics for locking out breakers, electrical plugs, wall switches and fuses

#### Components:

- 1 x Mini Cable Lockout (50940)
- 2 x 120V Snap-On Breaker Lockouts (65387)
- 2 x 120/277V Clamp-On Breaker Lockouts with cleats (65396)
- 2 x 480/600V Clamp-On Breaker Lockouts with cleats (65397)
- 2 x Universal Multi-Pole Breaker Lockouts (66321)
- 2 x Cleats for 120/277V Clamp-On Lockouts (65404)
- 2 x Cleats for 480/600V Clamp-On Lockouts (65406)
- 1 x Oversized Breaker Lockout (65329)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 1 x Wall Switch Lockout (65392)
- 1 x Small Fuse Blockout (65690)
- 1 x Large Fuse Blockout (65691)
- 1 x Extra-Large Lockout Toolbox (LKP-TKLBOX)
- 1 x Red Belt Pouch (51172)

#### Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
99310	Breaker Lockout Sampler Toolbox (Kit)
99312	Kit with 2 Safety Padlocks & 2 Tags
99313	Kit with 2 Steel Padlocks & 2 Tags

## LOCKOUT KITS

# STANDARD LOCKOUT KITS



### Gate Valve Lockout Pouch

- Lockout virtually any type and size of gate valve with just two versatile lockouts

#### Components:

- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 1 x All Purpose Cable Lockout with 8' sheathed cable (50943)

#### Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
101416	Gate Valve Lockout Satchel (Kit)
102692	Kit with 2 Safety Padlocks & 2 Tags
102693	Kit with 2 Steel Padlocks & 2 Tags

### Valve Lockout Pouch

- Economical kit for locking out gate, ball and plug valves

#### Components:

- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 2 x 1 1/2" - 2 1/2" Small Ball Valve Lockout (BS07A)
- 1 x Large Lockout Pouch (50979)
- 1 x Plug Valve Lockout for stem diameter up to 7/8" (113231)
- 1 x Plug Valve Lockout for stem diameter 29/32" - 1 3/8" (113232)

#### Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
99679	Valve Lockout Pouch (Kit)
99680	Kit with 2 Safety Padlocks & 2 Tags
99681	Kit with 2 Steel Padlocks & 2 Tags

### Gate Valve Lockout Satchel

- Contains devices for locking out a wide range of gate and ball valves

#### Components:

- 1 x 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 x 2 1/2" - 5" Gate Valve Lockout (65561)
- 1 x 5" - 6 1/2" Gate Valve Lockout (65562)
- 1 x 6 1/2" - 10" Gate Valve Lockout (65563)
- 1 x 10" - 13" Gate Valve Lockout (65564)
- 1 x Lockout Satchel (51173)

#### Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
99676	Gate Valve Lockout Satchel (Kit)
99677	Kit with 2 Safety Padlocks & 2 Tags
99678	Kit with 2 Steel Padlocks & 2 Tags



COMBINATION LOCKOUT KITS



Combination Lockout Satchel

• Everything you need to lock out the most common mechanical and electrical control points, with extra valve lockout devices

Components:

- 1 x Large Univ. Valve Lockout with Blocking Arm (50899 and 65403)
- 1 x All Purpose Cable Lockout with 8' Sheathed Cable (50943)
- 1 x 1/4" - 1" Ball Valve Lockout (65666)
- 1 x 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 x 2 1/2" - 5" Gate Valve Lockout (65561)
- 1 x 5" - 6 1/2" Gate Valve Lockout (65562)
- 1 x 120V Snap-On Breaker Lockout (65387)
- 1 x 120/277V Clamp-On Breaker Lockout with cleat (65396)

Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
99686	Combination Lockout Satchel (Kit)
99687	Kit with 2 Safety Padlocks & 2 Tags
99688	Kit with 2 Steel Padlocks & 2 Tags



Combination Lockout Duffel

• Everything you need to lock out the most common mechanical and electrical control points, with extra electrical lockout devices

Components:

- 1 x Mini Cable Lockout (50940)
- 1 x 120V Snap-On Breaker Lockout (65387)
- 1 x 120/277V Clamp-On Breaker Lockout (65396)
- 1 x 480/600V Clamp-On Breaker Lockout (65397)
- 1 x Universal Multi-Pole Breaker Lockout (66321)
- 1 x Oversized Breaker Lockout (65329)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 1 x Wall Switch Lockout (65392)
- 1 x Plug Valve Lockout for stem diameter up to 7/8" (113231)
- 1 x Plug Valve Lockout for stem diameter 29/32" - 13/8" (113232)
- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 1 x 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 x 1/4" - 1" Ball Valve Lockout (65666)
- 1 x Large Univ. Valve Lockout with Blocking Arm (50899 and 65403)
- 1 x Lockout Belt Pouch (51172)
- 1 x Lockout Duffel Bag (99162)

Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
99689	Combination Lockout Duffel (Kit)
99690	Kit with 2 Safety Padlocks & 2 Tags
99691	Kit with 2 Steel Padlocks & 2 Tags



## LOCKOUT KITS

## COMBINATION LOCKOUT KITS



### Valve Lockout Toolbox

- Everything you need to lock out gate, ball, butterfly and other valves

#### Components:

- 1 x Small Univ. Valve Lockout w/ Blocking Arm (50924 and 65402)
- 1 x All Purpose Cable Lockout w/ 8' Sheathed Cable (50943)
- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 1 x 1/4" - 1" Ball Valve Lockout (65666)
- 1 x 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 x Extra-Large Lockout Toolbox (LKP-TKLBOX)

#### Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
105969	Padlock kit with Keyed-Alike Safety Padlocks
105970	Padlock kit with Keyed-Alike Steel Padlocks



### Combination Lockout Toolbox

- All the basics for lockout out gate and ball valves, breakers, switches and plugs

#### Components:

- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 1 x 1/4" - 1" Ball Valve Lockout (65666)
- 1 x 1/4" - 3" Ball Valve Lockout (65669)
- 1 x 120V Snap-On Breaker Lockout (65387)
- 1 x 120/277V Clamp-On Breaker Lockout with cleat (65396)
- 1 x 480/600V Clamp-On Breaker Lockout with cleat (65397)
- 1 x Universal Multi-Pole Breaker Lockout (66321)
- 1 x 110V Electrical Plug Lockout (65674)
- 1 x Wall Switch Lockouts (65392)
- 1 x Lockout Belt Pouch (51172)
- 1 x Extra-Large Lockout Toolbox (LKP-TKLBOX)

#### Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500)
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog #	Description
99682	Combination Lockout Toolbox (Kit)
99684	Kit with 2 Safety Padlocks & 2 Tags
99685	Kit with 2 Steel Padlocks & 2 Tags

## LOCKOUT KITS

### CUSTOMIZABLE KITS

Create your own custom lockout kits by picking one of the storage/carrying cases below and filling it with the lockout devices you need



#### Lockout Belt Pouch

- Made of heavy duty nylon with loops for hanging on a belt

Catalog #	Dimensions	Description
51172	4 <sup>3</sup> / <sub>4</sub> " x 7 <sup>1</sup> / <sub>2</sub> " x 2"	Lockout Belt Pouch



#### Large Lockout Pouch

- Made of nylon with attachment loop on back

Catalog #	Dimensions	Description
50979	8" x 7" x 3"	Large Lockout Pouch



#### Lockout Bag

- Made of rugged canvas with drawstring
- Capable of being locked closed

Catalog #	Dimensions	Description
65780	18" x 9 <sup>3</sup> / <sub>4</sub> "	Lockout Security Bag



#### Lockout Satchel

- Made of 1000 Denier Red Cordura Nylon with 39" shoulder strap
- Includes latchable front pocket and two side mesh holders

Catalog #	Dimensions	Description
51173	14" x 4" x 15"	Lockout Satchel

## LOCKOUT KITS

## CUSTOMIZABLE KITS



### Extra-Large Lockout Toolbox

Catalog #	Description
LKX-TKLBO	Lockout Toolbox



### Lockout Duffel Bag

- Made of 600 denier polyester with 39" removable shoulder strap and 8 inside pockets

Catalog #	Dimensions	Description
99162	10" x 16 1/2" x 8 1/2"	Lockout Duffel Bag



### Lockout Toolboxes

- Made of rugged polypropylene with nickel-plated steel clasps
- Two handy storage pockets built into lid
- Comes with removable tray for organizing contents

Catalog #	Dimensions	Description
105905	7.1" x 14" x 5.5"	Small Toolbox
105906	7.8" x 16.2" x 7.3"	Medium Toolbox



### PRINZING Metal Lockout Cabinet

- All metal, yellow powder-coated cabinet comes with one adjustable shelf (extra shelves available)
- Capable of being locked closed
- Can also be easily wall mounted using predrilled holes in back
- Lockout safety tips printed on inside door

Catalog #	Dimensions	Description
LC252M	16" x 14" x 6"	Metal Lockout Cabinet
LC254M		Extra Shelf



## LOCKOUT STATIONS

## LOCKOUT STATIONS



Open Style Without Doors



Enclosed Style With Lockable Acrylic Doors

### Extra-Large Lockout Station

- Provides everything you need to lock out both mechanical and electrical control points
- Includes Universal Valve Lockout and All Purpose Cable Lockout
- Constructed of sturdy polystyrene with pre-drilled holes for easy wall mounting
- Pegboard-style holes for hooks drilled into back and sides (8 hooks supplied standard)
- Built-in lock rail holds 20 - 25 locks depending on lock size
- Available with or without lockable acrylic doors

#### Components:

- 1 x All Purpose Cable Lockout with 8' Sheathed Cable (50943)
- 1 x Large Univ. Valve Lockout with Blocking Arm (50899 and 65403)
- 2 x 120V Snap-On Breaker Lockouts (65387)
- 2 x 120/277V Clamp-On Breaker Lockouts (65396)
- 2 x 480/600V Clamp-On Breaker Lockouts (65397)
- 2 x Universal Multi-Pole Breaker Lockouts (66321)
- 1 x Oversized Breaker Lockout (65329)
- 2 x Cleats for 120/277V Clamp-On Lockouts (65404)
- 2 x Cleats for 480/600V Clamp-On Lockouts (65406)
- 1 x Wall Switch Lockout (65392)
- 1 x 110V Electrical Plug Lockout (65674)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 1 x 1/4" - 1" Ball Valve Lockout (65666)
- 1 x 1 1/4" - 3" Ball Valve Lockout (65669)
- 2 x 1" - 2 1/2" Gate Valve Lockouts (65560)
- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 2 x Labeled Lockout Hasps (65960)

#### Padlock Options:

- Choose between 18 keyed-different safety padlocks (99552) or 18 steel padlocks (99500)
- Padlocks come with 25 heavy duty, re-usable lockout tags (65520) and nylon cable ties

### Open Style Without Doors

Catalog #	Dimensions	Description
99693	30" x 25" x 5 1/4"	Station with Components and 18 Brady Safety Padlocks, 25 Tags
99694	30" x 25" x 5 1/4"	Station with Components and 18 Brady Steel Padlocks, 25 Tags
50993	30" x 25" x 5 1/4"	Extra-Large Lockout Station (unfilled)

### Enclosed Style With Lockable Acrylic Doors

Catalog #	Dimensions	Description
99696	30" x 25" x 5 1/4"	Station with Components and 18 Brady Safety Padlocks, 25 Tags
99700	30" x 25" x 5 1/4"	Station with Components and 18 Brady Steel Padlocks, 25 Tags
50995	30" x 25" x 5 1/4"	Extra-Large Lockout Station (unfilled)



## LOCKOUT STATIONS

## LOCKOUT STATIONS



### Large Lockout Station

- Provides everything you need for locking out all types of valves and plugs
- Includes Universal Valve Lockout and All Purpose Cable Lockout
- Constructed of sturdy white polystyrene with predrilled holes for easy wall mounting
- Pegboard-style holes for hooks drilled into back (6 hooks supplied standard)
- Built-in lock rail holds 15 - 20 locks depending on lock size
- Available with or without lockable acrylic doors

#### Components:

- 1 x All Purpose Cable Lockout with 8' Sheathed Cable (50943)
- 1 x Large Universal Valve Lockout with Blocking Arm (50899 and 65403)
- 1 x 110V Electrical Plug Lockout (65674)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 1 x 1/4" - 1" Ball Valve Lockout (65666)
- 1 x 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 2 x Labeled Lockout Hasps (65960)

#### Padlock Options:

- Choose between 12 keyed-different safety padlocks (99552) or 12 steel padlocks (99500)
- Padlocks come with 25 heavy duty, re-usable lockout tags (65520) and nylon cable ties

### Open Style Without Doors

Catalog #	Dimensions	Description
99699	26" x 19 1/2" x 5"	Station with Components and 12 Brady Safety Padlocks, 25 Tags
99697	26" x 19 1/2" x 5"	Station with Components and 12 Brady Steel Padlocks, 25 Tags
50994	26" x 19 1/2" x 5"	Large Lockout Station (unfilled)

### Enclosed Style With Lockable Acrylic Doors

Catalog #	Dimensions	Description
99703	26" x 19 1/2" x 5"	Enclosed Station with Components and 12 Brady Safety Padlocks, 25 Tags
99704	26" x 19 1/2" x 5"	Enclosed Station with Components and 12 Brady Steel Padlocks, 25 Tags
50996	26" x 19 1/2" x 5"	Large Enclosed Lockout Station (unfilled)



Open style without doors



Enclosed Style With Lockable Acrylic Doors



### Lockout Station V-Sign

- Enhance the visibility of your Lockout Station with this V-shaped polyethylene sign
- Sign size: 8" x 9" x 1" flange (overall width is 14")

Catalog #	Description
66328	Lockout Stations V-Sign

LOCKOUT STATIONS



**Small Lockout Station**

- Provides everything you need for locking out all types of electrical control points
- Includes Mini Cable Lockout
- Station constructed of sturdy white polystyrene with predrilled holes for easy wall mounting
- Built-in lock rail holds 10 - 15 locks depending on lock size
- Pegboard-style holes for hooks drilled into back (4 hooks supplied standard)

**Components:**

- 1 x Mini Cable Lockout (50940)
- 2 x 120V Snap-On Breaker Lockouts (65387)
- 2 x 120/277V Clamp-On Breaker Lockouts with cleats (65396)
- 2 x 480/600V Clamp-On Breaker Lockouts with cleats (65397)
- 2 x Universal Multi-Pole Breaker Lockouts (66321)
- 1 x Oversized Breaker Lockout (65329)
- 1 x Wall Switch Lockout (65392)
- 1 x 110V Electrical Plug Lockout (65674)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 1 x Small fuse blockout (65690)
- 1 x Large fuse blockout (65691)
- 2 x Labeled Lockout Hasps (65960)

**Padlock Options:**

- Choose between 6 keyed different safety padlocks (99552) or 6 steel padlocks (99500)
- Padlocks come with 12 heavy duty, re-usable lockout tags (65520) and nylon cable ties



**Small Lockout Station with Brady Safety Padlocks**

Catalog #	Dimensions	Description
99706	18" x 12" x 4"	Station with Components & 6 Brady Safety Padlocks, 12 Tags
99707	18" x 12" x 4"	Station with Components & 6 Brady Steel Padlocks, 12 Tags
50997	18" x 12" x 4"	Small Lockout Station (unfilled)

**Combined Lockout /Group Lockout Box Station**

- All metal, yellow powder-coated cabinet comes with one adjustable shelf (extra shelves available)
- Capable of being locked closed
- Lockout safety tips printed on inside door
- Lock box attaches to bottom of cabinet, accommodates 8 - 10 locks depending on lock size

**Components:**

- 1 x 120V Snap-On Breaker Lockouts (65387)
- 1 x 120/277V Clamp-On Breaker Lockout with cleats (65396)
- 1 x 480/600V Clamp-On Breaker Lockout with cleats (65397)
- 1 x Universal Multi-Pole Breaker Lockout (66321)
- 1 x Oversized Breaker Lockout (65329)
- 1 x Wall Switch Lockout (65392)
- 1 x 110V Electrical Plug Lockout (65674)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 1 x 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 x 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)

**Padlock Options:**

- Choose between 6 keyed-different safety padlocks (99552) or 6 steel padlocks (99500)
- Padlocks come with 12 heavy duty, re-usable lockout tags (65520) and nylon cable ties



Catalog #	Dimensions	Description
99709	16" x 14" x 6"	Station with Components & 6 Brady Safety Padlocks, 12 Tags
99710	16" x 14" x 6"	Station with Components & 6 Brady Steel Padlocks, 12 Tags
LG252M	6" x 15" x 3"	Metal Wall Lock Box (Lock Box Only)

## LOCKOUT STATIONS

## PRINZING KITS & STATIONS



### Economy Lockout Kit (LKX)

- Our economy kit provides 9 components to ensure equipment is either de-energized or locked out in accordance with OSHA regulation 1910.47
- Includes all components of the Economy Lockout Kit (LKX), plus the Sign & Rack (LKX-Rack) which conveniently holds the kit's carrying case

#### Economy Lockout Kit Components:

- 3 x 1 1/2" Steel Lockout Hasps (T220)
- 3 x Blue Prinzing Padlocks (LC041-BU)
- 14 x 2 Padlock Identifier Stickers (LID-2)
- 1 x pack (10) - Lockout Tags with Ties (LT10)
- 3 x Single Pole Breaker Lockouts (BLO1)
- 2 x Multi Pole Breaker Lockouts (BLO3)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 1 x Lockout Training Booklet (2112X)
- 1 x Rugged Polyethylene Carrying Case (7" x 12" x 5")

\* Lockout Kit - Complete Set Includes all of the above, plus the Sign & Rack (LKX-Rack)

### Lockout Kit - Complete Set (LKXSET)

Catalog #	Description
LKXSET	Lockout Kit - Complete Set
LKX	Economy Lockout Kit with Toolbox
LKX-Rack	Sign & Rack only
LKX-TKLBOX	Toolbox only



### Ultimate Lockout Kit

- The ultimate portable solution for a very wide range of lockout applications

#### Components:

- 1 x Safetee™ Donut 1" - 2 1/2" (SD02)
- 1 x Safetee™ Donut 5" - 6 1/2" (SD06)
- 1 x Ball Valve Lockout (BS07A)
- 1 x Ball Valve Lockout (BS08A)
- 1 x Electrical Plug / Pneumatic Lockout (PL027E)
- 10 x "Danger Do Not Operate" Lockout Tags (LT10)
- 1 x Cable Lockout Device (CABLO)
- 2 x No-hole Breaker Lockout (BL04)
- 2 x Breaker Lockout, Triple-pole (BL03)
- 1 x Breaker Lockout, Multi-pole (BL07)
- 2 x 1 1/2" Steel Lockout Hasp (T220)
- 1 x Wall Switch Lockout (WSLO)
- 1 x Lockout Safety Training Booklet (2112X)
- 1 x 120-600 AC Voltage Sensor (ESAC600)
- 3 x Prinzing Padlocks 3/4" Blue (LC041-BU)
- 1 x Lockout Bag "Duffel Style" (LX980E)

Catalog #	Description
LK981E	Ultimate Lockout Kit
LK980E	Lockout Bag Only



## LOCKOUT STATIONS

## PRINZING KITS & STATIONS



### Industrial Strength Lockout Station

- Lockable all metal, yellow powder coated cabinet comes with one adjustable shelf (extra shelves available)
- Lockout safety tips are conveniently located inside of door for frequent reminders of proper lockout procedures
- Can be wall mounted or easily transported

#### Components:

- 3 x Red Safety padlocks (99552)
- 3 x Yellow Safety padlocks (99570)
- 1 x Safetee™ Donut - 2 1/2" - 5" (SDO4)
- 1 x Safetee™ Donut - 1" - 2 1/2" (SD02)
- 1 x Single pole breaker lockout (BLO1)
- 10 x Lockout tags with ties (LT10)
- 2 x Multi pole breaker lockout (BLO3)
- 1 x 1" Multiple lockout device (T218)
- 1 x Single pole breaker lockout (BLO4)
- 1 x 1 1/2" Multiple lockout device (T220)
- 1 x 3-in-1 Electrical plug lockout (PLO23)
- 1 x Small plug lockout (PLO21)

Catalog #	Dimensions	Description
LC251M	16" x 14" x 6"	Industrial Strength Lockout Station
LC252M	16" x 14" x 6"	Cabinet Only



Safety Lockout Center



Bilingual Safety Lockout Center

### Safety Lockout Center

- Provides ready access to locks, tags, lockout devices and information
- Made of tough acrylic plastic

#### (3002) Components:

- 6 - Multi-color padlocks
- 2 x pack (10) Bilingual lockout tags with ties (TG400B-10)
- 5 x 1 1/2" multiple lockout devices (T220)
- 15 x English Lockout Safety booklets (2112X)
- 10 x Spanish Lockout Safety booklets (2112SPX)

#### (3001) Components:


- 6 x Multi-color steel padlocks
- 2 x pack (10) lockout tags with ties (LT10)
- 5 x 1 1/2" multiple lockout devices (T220)
- 1 x pack (25) Lockout Safety booklets (2112X)

Catalog #	Dimensions	Description
3001	30" x 24" x 4 1/2"	Safety Lockout Center
3012	30" x 24" x 4 1/2"	Board Only (3001 model)
3002	30" x 24" x 4 1/2"	Bilingual Safety Lockout Center
3013	30" x 24" x 4 1/2"	Board Only (3002 model)

## LOCKOUT STATIONS

## READY ACCESS STORAGE STATIONS

Brady's new Ready Access storage stations ensure that lockout devices remain easily accessible and ready for use whenever needed. These compact stations are made of rugged, rustproof polypropylene and come with an attachable handle for easy portability. The stations can also be permanently wall mounted out near the point of need, allowing employees to grab the tools they need without wasted search and retrieval time. The lockable cover guards against theft and unauthorized usage, and protects the contents from exposure to harsh industrial environments. Your lockout devices stay clean and secure, ready for use whenever and wherever needed.



### Ready Access Padlock Station

- Holds up to 10 padlocks, 6 hasps and 10 tags
- Made of thermformed polypropylene for rugged durability
- Semi-transparent hinged cover with locking mechanism protects contents from harsh environments and prevents unauthorized access
- Slots in back for wall mounting
- Attachable carrying handle facilitates easy portability
- Space-saving design delivers footprint half the size of competitors

Catalog #	Dimensions	Description
105928	17" x 13.25" x 2.5"	Padlock Station with 5 Safety Padlocks
105929	17" x 13.25" x 2.5"	Padlock Station with 5 Steel Padlocks
105930	17" x 13.25" x 2.5"	Padlock Station with 10 Safety Padlocks
105931	17" x 13.25" x 2.5"	Padlock Station with 10 Steel Padlocks
105932	17" x 13.25" x 2.5"	Ready Access Padlock Station (Unfilled)

### Ready Access Padlock Station - with 5 Padlocks

#### Components:

- 1 x Ready Access Padlock Station (105932)
- 5 x Keyed-different safety padlocks (99552) or steel padlocks (99500)
- 5 x Heavy Duty, re-usable lockout tags (65520) with nylon cable tie
- 2 x 1" Group Lockout Hasps (65375)
- 2 x 1.5" Group Lockout Hasps (65376)

### Ready Access Padlock Station - with 10 Padlocks

#### Components:

- 1 x ReadyAccess Padlock Station (105932)
- 10 x Keyed-different safety padlocks (99552) or steel padlocks (99500)
- 10 x Heavy duty, re-usable lockout tags (65520) with nylon cable ties
- 3 x 1" Group Lockout Hasps (65375)
- 3 x 1.5" Group Lockout Hasps (65376)

### Ready Access Lockout Station

- Made of thermformed polypropylene for rugged durability
- Semi-transparent hinged cover with locking mechanism protects contents from harsh environments and prevents unauthorized access
- Slots in back for wall mounting
- Attachable carrying handle facilitates easy portability
- 4 detachable hanging hooks
- Storage Compartment dimensions: 4.25" x 16" x 5.12"

Catalog #	Dimensions	Description
105942	17" x 17" x 6.75"	Ready Access Lockout Station Only (unfilled)



## LOCKOUT STATIONS

### READY ACCESS STORAGE STATIONS



#### Ready Access Valve Lockout Station

**Components:**

- 1 x Ready Access Lockout Station (105942)
- 2 x Adjustable Gate Valve Lockouts (64057)
- 1 x All Purpose Cable Lockout (50943)
- 2 x Ball Valve Lockouts (BSO7A)
- 2 x 1" Group Lockout Hasps (65375)
- 1 x 1.5" Group Lockout Hasp (65376)
- 6 x Keyed different safety padlocks (99552) or steel padlocks (99500)
- 6 x Heavy duty, re-usable lockout tags (65520) with nylon cable ties

Catalog #	Description
105936	Valve Lockout Station (No Padlocks)
105937	Station with 6 Safety Padlocks
105938	Station with 6 Steel Padlocks



#### Ready Access Electrical Lockout Station

**Components:**

- 1 x Ready Access Lockout Station (105942)
- 2 x 3-in-1 Electrical Plug Lockouts (PLO23)
- 1 x Mini Cable Lockout (50940)
- 2 x 120/277V Clamp-On Breaker Lockouts with cleats (65396)
- 2 x 480/600V Clamp-On Breaker Lockouts with cleats (65397)
- 2 x Universal Multipole Breaker Lockouts (66321)
- 1 x Oversized Breaker Lockout (65329)
- 2 x 1" Group Lockout Hasps (65375)
- 1 x 1.5" Group Lockout Hasps (65376)
- 6 x Keyed different safety padlocks (99552) or steel padlocks (99500)
- 6 x Heavy duty, re-usable lockout tags (65520) with nylon cable ties

Catalog #	Description
105939	Electrical Lockout Station (No Padlocks)
105940	Station with 6 Safety Padlocks
105941	Station with 6 Steel Padlocks



#### Ready Access Valve & Electrical Lockout Station

**Components:**

- 1 x Ready Access Lockout Station (105942)
- 1 x Adjustable Gate Valve Lockout (64057)
- 1 x All Purpose Cable Lockout (50943)
- 1 x Ball Valve Lockout (BSO7A)
- 1 x 3-in-1 Electrical Plug Lockout (PLO23)
- 2 x 120/277V Clamp-On Breaker Lockouts with cleats (65396)
- 1 x 480/600V Clamp-On Breaker Lockout with cleat (65397)
- 2 x Universal Multipole Breaker Lockouts (66321)
- 2 x 1" Group Lockout Hasps (65375)
- 1 x 1.5" Group Lockout Hasp (65376)
- 6 x Keyed-different safety padlocks (99552) or steel padlocks (99500)
- 6 x Heavy duty, re-usable lockout tags (65520) with nylon cable ties

Catalog #	Description
105933	Valve & Electrical Station (No Padlocks)
105934	Station with 6 Safety Padlocks
105935	Station with 6 Steel Padlocks




## TRAINING & AWARENESS AIDS



### Lockout/Tagout Handbook

- 16-page training booklet with quiz instructs workers how to protect themselves from hazardous energy

Catalog #	Description	Quantity
66219	Lockout/Tagout Handbook	10/pack
63004	Spanish-language Handbook	10/pack



### PRINZING Lockout Safety Poster

- Training poster reinforces your energy control program

Catalog #	Dimensions	Description
LOSP8	18" x 24"	Lockout Safety Poster
LOSP8SP	18" x 24"	Spanish-language version



## TRAINING & AWARENESS AIDS



### Lockout/Tagout e-Learning Courses

Train your employees on lockout compliance with Brady's new online training courses. The courses feature interactive features, real-life application scenarios and quizzes to facilitate learning and remembering. Employees can access the courses online from your facility, which eliminates the costs of off-site training. Certificate available upon completion.

Catalog #	Description
142253	LOTO For Authorized Workers (approx. length 1hr 30min)
142254	LOTO For Corporate Safety Leader (approx. length 1hr)
142255	e-Learning Bundle: (1) LOTO For Auth Worker and (1) LOTO for Corp Safety Leader

Only Available at [www.BradyID.com](http://www.BradyID.com)



### LOTO for Authorized & Affected Personnel

- Provides a comprehensive introduction to the key components of an effective LOTO program
- Run time: 17 minutes (DVD format)
- Comes with reproducible quiz and certificate
- Spanish language video also available (quiz and certificate in English only)

Catalog #	Description
51454	LOTO For Authorized & Affected Personnel DVD (English)
51455	LOTO For Authorized & Affected Personnel DVD (Spanish)




### Lockout/Tagout Training: A Program for Employees

Train employees to protect themselves and others during machine servicing and maintenance. This program shows how to recognize all potential hazards and handle them safely. Includes:

- Live action 13 minute, DVD video
- Instructors guidebook with quizzes, 24 pages
- 10 employee handbooks
- 10 certificate of completion wallet cards
- Training log book
- Full-color poster
- Sample tag & warning decal
- Carrying case

Catalog #	Description	Qty
104275	Complete Kit - DVD version - English	1
104216	Complete Kit - DVD version - Spanish	1



### Lockout For Life

- Learn from other workers' tragic mistakes. This motivational video presents six real-life dramatizations of actual lockout accidents and analyzes how they could have been prevented
- Suitable for new and experienced employees
- Run time: 19 minutes (VHS or DVD formats)

Catalog #	Description
66255	Lockout For Life VHS video (includes 10 booklets)
51793	Lockout For Life DVD English/Spanish (includes 10 English booklets)
51544	Lockout For Life VHS video (Spanish)
65555	Additional booklets (10/pack)



## OSHA TRAINING REQUIREMENTS

Singapore Standard 571:2011, the Code of Practice for Energy Lockout and Tagout deals with the control of hazardous energy in workplace situations and provides detailed guidance on procedures, techniques and methods for energy lockout and tagout. The SS571:2011 takes reference from OSHA Regulations (Standards-29 CFR-1910.147, ANSI Z244.1:2003 (2008) and CSA Z460:2005. Brady is part of the working group appointed by the Technical Committee of Singapore's Workplace Safety and Health to assist in the preparation of SS 571 : 2011. For more information, please visit [www.standards.org.sg](http://www.standards.org.sg)



### OSHA Training Requirements

- Those who will perform servicing or maintenance (authorized employees) must be trained to:
  - Recognize hazardous energy sources and understand the energy type and magnitude
  - Identify and properly operate the applicable energy-isolating devices
  - Safely apply and remove lockout/tagout devices
- Those who operate the machinery or work in the area where LOTO is performed (affected employees) must be trained to:
  - Recognize when lockout/tagout activities are in progress
  - Understand the purpose of the energy control program and the importance of not tampering with lockout/tagout devices when encountered in the workplace
- Additional training is required when using tagout instead of lockout. See Section (C)(7)(ii) in the 1910.147 standard
- Employers must document when training took place, who attended, and the topics covered
- Employees must be retrained under the following situations:
  - Employee assigned to new job
  - Change made to energy control policies or procedures
  - Machinery installed or modified, presenting a new hazard
  - Whenever the employer has reason to believe that there are problems with the employee's understanding or use of the procedures
- Authorized employees must undergo an annual review to ensure they fully understand their responsibilities under the program



# ENERGY CONTROL PROCEDURES



## Lockout Pro™ Graphical Procedure Writing Software

### Create Machine-specific procedures in minutes

- Start immediately with easy-to-use templates and built-in defaults
- Access a database of standard graphics, terms, and information
- Insert images to create clear, machine-specific procedures that identify the location of control points
- Print to a standard inkjet or laser printer, or to Brady's GlobalMark® 2 Industrial Label Maker or HandiMark® Portable Label Maker
- Provide viewing and printing access to users in multiple locations with the FREE viewer and HTML viewer applications
- Export to CMMS or ERP

### Create, maintain, train, update – with one program

- Use Lockout PRO software's built-in sample energy control policy to develop your own comprehensive energy control program
- Create machine-specific lockout procedures for different locations; ensure that location-specific safety needs are addressed
- Manage and update your procedures with automatic time- and date-stamping
- Train your employees with online tutorials and built-in video training clips in Enterprise versions
- Access current OSHA lockout/tagout standard with a few clicks
- Call to learn about a separate optional annual audit service for your Lockout Pro procedures

Catalog #	Description
LOPDESK1001	Lockout Pro Desktop Software
LOPCORP2001	Lockout Pro Enterprise Corporate with web viewer
LOPBASIC3001	Lockout Pro Basic (Only 3 Administrators)
LOPADUSER1	Additional Administrator (adds 1 admin)
99004	GlobalMark2 Multicolor printer + LockoutPro
99009	GlobalMark2 ColorCut printer + LockoutPro

## Create Custom Graphical Lockout/Tagout Procedures Online

Create Graphical Lockout/Tagout Procedures for your facility in minutes. Procedures comply with OSHA's lockout standards for controlling hazardous energy sources.

- Upload your own digital photos
- Download and print from your own printer
- Save for up to 30 days

### Try the Custom Design Tool at [www.BradyID.com](http://www.BradyID.com)!

Components:


- 1) Select your category
- 2) Customize your product
- 3) Add to your shopping cart

## Not Sure Which Circuit Breaker Lockout To Use?

### OTHER WAYS OF PROVIDING ACCESS TO PROCEDURES

- Print procedures to adhesive or magnetic labels and adhere to directly to machine.
- Attach procedures to work orders manually or by linking the digital procedure file to work orders generated in a computer maintenance management system
- Provide access to procedures online, allowing workers to view and print procedures from their own computer

Brady's Lockout PRO software allows you to implement any of the methods above.



# WORKPLACE SAFETY AND COMPLIANCE SOLUTIONS



As a global leader in identification and workplace safety, Brady is a resource you can trust for Safety, Facility and Regulatory Compliance Solutions to protect your premises, products and people. Brady has been providing remedies for global ecological disasters with our range of sorbent and spill containment products. Our regulatory compliance solutions include lockout/tagout devices for hazardous energy control, industrial printers for creation of safety signs and labels, sorbent and spill containment for cleaning up spills, customized pipe markers and glow-in-the-dark emergency egress markings for your facilities.

**Brady is your trusted safety solutions advisor. Because like you, we want our workers to be safe**



## Safety Sign & Label Printers

Brady's industrial printers and label makers offer reliable, on-demand labeling solutions for any industry. Designed with thermal transfer printing capabilities, Brady's printers create clear, professional-looking labels, signs and tags - with the durability to withstand even the harshest environments. Whether it's a small handheld printer or a large, multi-color industrial printer, Brady has an easy-to-use label printing solution to fit your needs.



## Safety Signage & Regulatory Markings

As a global leader in facility signage, there's no other company that can help you communicate critical information better than Brady. We offer more than 8,000 different signs for safety, maintenance and facility identification. Brady signs feature bright colors, bold text and intuitive pictographs to ensure that the communication is highly visible and easily understood. The signs are compliant with the latest standards and regulations, and designed to withstand even the harshest industrial environments. Brady also offers a comprehensive collection of pipe and valve marking supplies, tools and identification systems to help workers trace process problems and find solutions faster. Together with a full line of electricity free photoluminescent signs ideal for areas with possible electrical power failure.



## Anti-skid Tape & ToughStripe® Floor Marking

Brady offers thousands of high performance labels, markers and tapes that can help your company communicate important safety and facility identification messages. Protect your employees from accidental slips, trips and falls with Brady's sure traction and high visibility warning Anti-Skid Tape. ToughStripe® Floor Marking Tape is perfect for high and heavy traffic areas in your facility. It is test-proven to withstand forklift traffic better than other tape-based floor marking products.



## SPC Sorbents & Spill Containment

Brady's SPC sorbents & spill control products help you keep your employees and work environment safe from unexpected spills, leaks, drips or other accidents. SPC sorbents are available for cleaning up oil, water and chemical based spills. Select from traditional polypropylene or eco-friendly Re-Form™ sorbents and spill kits to help comply with the latest OSHA and EPA safety regulations.



## Lockout / Tagout (LOTO)

The world leader in lockout/tagout products and services, Brady offers a broad range of durable, easy-to-use lockout devices that cover most mechanical and electrical applications. In addition, Brady covers other critical aspects of a compliant, effective energy control program by providing innovative solutions for training employees, creating documented procedures, and identifying energy sources. Brady's services help companies with limited resources quickly get their program up to speed, ensuring that lockout activities are implemented in a way that promotes optimum safety while maximizing efficiency and reducing downtime.

To find out more about Brady and our products, please visit [www.bradyid.com/ap](http://www.bradyid.com/ap)

## CONTACT US

Brady's global presence makes it easy for you to do business with us wherever you are. To find out more about Brady and our products, please visit us at [www.bradyid.com/ap](http://www.bradyid.com/ap) or email us at [ContactUs\\_SEA@bradycorp.com](mailto:ContactUs_SEA@bradycorp.com).

### APAC Offices

#### AUSTRALIA

Telephone: (612) 8717 6300

#### CHINA

Telephone: (86) 21 6100 6588

#### HONG KONG

Telephone: (852) 2216 9283

#### INDIA

Telephone: (91) 80 66582 900

#### INDONESIA

Telephone: (60) 4 646 2700

#### JAPAN

Telephone: (81) 042 655 2535

#### MALAYSIA

Telephone: (60) 4 646 2700

#### PHILIPPINES

Telephone: (65) 6477 7261

#### SINGAPORE

Telephone: (65) 6477 7261

#### SOUTH KOREA

Telephone: (02) 2192 0700

#### TAIWAN

Telephone: (86) 2 2657 6108

#### THAILAND

Telephone: (66) 2 793 9211

#### VIETNAM

Telephone: (66) 2 793 9211

### International Offices

#### EUROPE

Website: [www.bradyeurope.com](http://www.bradyeurope.com)

#### NORTH AMERICA

Website: [www.bradyid.com](http://www.bradyid.com)