



## i2369Vm

58.4cm (23") LED MONITOR

### Line:

---

Line:	Value
Paneltype:	IPS
Monitor Size:	23"
Visible Screen Size:	58.4cm
Screen Format:	16:9
Brightness:	250 (typ) cd/m <sup>2</sup>
Contrast Ratio Dynamic:	50.000.000:1 (DCR)
Contrast Ratio Typical:	1000:1
Pixel / Dot / Pitch:	0.265 (H) x 0.265 (V)
Display Area:	509.76 (H) x 286.74 (V)
Viewing Angle:	178°/178° (CR 10)
Response Time:	5 ms GtG

### Scanning Frequency:

---

Scanning Frequency:	H: 30-83 kHz / V: 50-76 HZ
Pixel Frequency:	170 MHz

### Resolution:

---

Maximum Resolution:	1920 x 1080@60 Hz
Recommend Resolution:	1920 x 1080@60 Hz
Colors:	16.7 M
HDCP compatible:	Yes

### Signal Input:

---

Analogue Input: D-Sub:	Yes
Digital Input: DVI-D / HDMI:	No / Yes (2)
Composite CVBS Input:	No
Component CVBS Input:	No
S-Video Input:	No
Component Input:	No
SCART:	No
CI Card:	No
Display Port Input:	Yes

### Connectors:

---

D-Sub 15 pin:	Yes
DVI-D 24-pin:	No
HDMI:	Yes (2)
Display Port Input:	Yes

### Power:

---

Power Source:	90 ~ 240 VAC, 50 / 60 Hz
Power Consumption:	On: 33W, Standby: <0.5W, Off: <0.5W





## i2369Vm

58.4cm (23") LED MONITOR

### Tuner System:

---

-

### Other Features:

---

User Control:	Button
Speaker:	Yes
Wallmount:	Yes
Height adjustment:	No
Pivot:	No
Swivel:	No
Regulations:	Energy Star 5.0 TCO '06
Other Features:	-5°~+15° Tilt Eco Mode e-Saver i-Menu Kensington Security Lock MHL Screen+ VESA 75 mm

### Accessories:

---

Accessories:	Power cable Driver CD Warranty Card
--------------	---

### Dimensions:

---

Dimensions (WxHxD):	531.4 x 398 x 204
Warranty:	3 Years
EAN:	4038986142090

