

Push Buttons

High Voltage

800 Series

The 820 and 821 are rugged, fast break contact Push Buttons that operate regardless of how pressure is released. The 821 is ideal for mounting on thin metal panels. The 821 may be used with 149-1 mounting plate.

Features and Specifications

- Force fit (820)
- Locknut mounting (821)
- Convenient screw terminals
- Momentary contact
- Normally open contacts
- Rated at 250,000 operations at 1 amp, 125V



Ordering Information

Description	Cat. No.	Operating Voltage	Current	Finish			Hole Depth
				Housing	Center	Hole Size	
Push Buttons	820	12V AC	15 A	Heavy Duty-Chrome Plated	Black	3/4" (19mm)	1 3/4" (44mm)
		24V AC	15 A				
		48V AC	10 A				
		125V AC	5 A				
		250V AC	5 A				
	821	12V AC	15 A	Heavy Duty-Chrome Plated	Black	7/8" (22mm)	1 3/4" (44mm)
		24V AC	15 A				
		48V AC	10 A				
		125V AC	5 A				
		250V AC	5 A				

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
820	0.06	0.10
821	0.06	0.10

