

TM2AMM3HT

analog input/output module M238 - 2 inputs
voltage/current high level - 1 output

Product availability: Stock - Normally stocked in distribution facility
Price*: 483.00 USD



Main

Commercial Status	Commercialised
Range of product	Modicon M238 logic controller
Product or component type	Input/Output analog module
Analogue input number	2
Input level	High level
Analogue input type	Voltage 0...10 V non differential Current 4...20 mA non differential
Analogue output number	1
Analogue output type	Voltage 0...10 V Current 4...20 mA
Cross talk	<= 2 LSB

Complementary

Range compatibility	Advantys OTB Twido
Analogue input resolution	12 bits
Analogue output resolution	12 bits
LSB value	4.8 μ A current current 2.5 mV voltage voltage
Permissible continuous overload	40 mA current 13 V voltage
Input impedance	>= 1 MOhm voltage >= 10 Ohm current
Load type	Resistive
Load impedance ohmic	>= 2000 Ohm voltage <= 300 Ohm current
Stabilisation time	20 ms
Conversion time	20 ms + 1 controller cycle time
Sampling duration	<= 10 ms
Acquisition period	60 ms per channel + 1 controller cycle time
Measurement error	+/- 0.2 % of full scale 4...20 mA 4...20 mA 25 °C +/- 0.2 % of full scale 0...10 V 0...10 V 25 °C
Temperature coefficient	+/-0.015 %FS/°C 4...20 mA 4...20 mA +/-0.015 %FS/°C 0...10 V 0...10 V +/-0.006 %FS/°C 4...20 mA +/-0.006 %FS/°C 0...10 V
Repeat accuracy	+/-0.5 %FS input/output
Non-linearity	+/- 0.2 %FS voltage voltage +/- 0.2 %FS current current
Output error	+/- 1 %FS
Output ripple	<= 1 LSB
Total error	+/-1 %FS voltage voltage +/-1 %FS current current
Type of cable	Shielded cable
Insulation between channel and internal logic	Photocoupler
Supply	External supply

[Us] rated supply voltage	24 V DC
Supply voltage limits	19.2...30 V
Electrical connection	1 removable screw terminal block
Current consumption	50 mA 5 V DC internal 50 mA 24 V DC external
Product weight	0.19 lb(US) (0.085 kg)

Environment

Dielectric strength	500 V between the I/O and the external supply circuit 500 V between the I/O and internal logic 500 V between I/O channel
Width	0.93 in (23.5 mm)
Depth	2.76 in (70 mm)
Height	3.54 in (90 mm)

Ordering and shipping details

Category	22531 - PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	00785901825845
Nbr. of units in pkg.	1
Package weight(Lbs)	0.44
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	JP

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0830 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental

Contractual warranty

Period	18 months
--------	-----------