

Di-Li Mikroskope



Monitor-Set Di-Li 2062

Das Set besteht aus HD-Videokamera mit C-mount Anschluß, Monitor und Netzteil um aus einem normalen Mikroskop ein Videomikroskop mit Monitor zu machen.

HD-Mikroskopkamera

Zusätzlich hat die Kamera einen USB-Ausgang.

Auflösung 1024 x 768 Pixeln Video (XGA).

Auflösung 1600 x 1200 Pixeln USB

Außerdem verfügt die Kamera über Fadenkreuzlinien, die die Qualitätskontrolle erleichtern.

Mit digital Zoom am Video-Ausgang 0-10fach

Monitor hochauflösend 15 Zoll

Monitor-Set Di-Li 2062 -HD-Video-Camera + Monitor 15" + USB-

Sensor 2.0MP, 1/3INCH

Resolution 1600 × 1200

Frame rate 10-15

White balance Auto

Brightness control Auto

Color Color/Grey

Mirror Horizontal/Vertical Flip

Freeze image Yes

OSD English

Digital zoom 10X digital zoom

Edge Enhancement Yes

Contrast Yes

Chroma Yes

Cross hair cursor Yes

Denoise Yes

VGA (RGB) 720P/1024×768/1280×1024/1366×768 @ 60HZ

USB output USB2.0 (1600*1200、800*600) Driver- free

Mount CS-mount

Monitor

Visible diagonal screen size: 15"

Response time: 3.7ms

Angle of view: horizontal 170°, vertical 160°

Contrast ratio: 1,000:1

Brightness: 250cd/m², 16.7 million colours