



datasheet for AK 2 S
 article number: 932146100



product description:	order number: 932 146-100
description:	Insulated, high strength alligator clip. Clamping range up to 9.5 mm bolt diameter. The flat part of the jaws (fine wire section) allows even the finest wires to be clamped. 4 mm diameter socket connection and screw connection up to 1.5 mm ² .
typ:	AK 2 S schwarz/black
system:	4mm system
order number:	932 146-100
clamping range:	9.5 mm
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	clamp
type of termination:	4 mm socket (unsprung), screw
rated voltage:	30 VAC / 60 VDC
rated current:	25 A
Please consider derating curve!	
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PP
environmental conditions:	
temperature range:	-25 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 HB
drawing	
	