

datasheet for MLN 100/2,5 Au
 article number: 934063700



product description:	order number: 934 063-700
description:	Measuring lead, at either end 4 mm diameter plug with caged spring and 4 mm diameter socket for tower construction. Gold-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, grip and lead shatter-proof. Built in colour indicator for easy identification of insulation damages.
typ:	MLN 100/2,5 Au schwarz/black
system:	4 mm system
order number:	934 063-700
color	●
other color versions:	●●●●●●●●●●
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions	4 mm
type of contact:	pin (spring loaded)
cable type:	LEH-XY
cable specification:	highly flexible lead
wire stranding:	320 x 0.10 mm
rated voltage:	30 VAC / 60 VDC
rated current:	32 A
Please consider derating curve!	
contact resistance:	12 mOhm
cable length:	100 cm
conductor size:	2.5 mm ²
cable material:	PVC
cable color:	black
material	
contact material:	contact pin: brass contact spring: copper - beryllium
contact surface material:	gold
housing material:	PA
environmental conditions:	
temperature range:	-15 °C to +70 °C
inflammable class:	

housing (basic material):	UL 94 V - 2
drawing	