

datasheet for PRUEF 2  
article number: 973368100



<b>product description:</b>	<b>order number: 973 368-100</b>
<b>description:</b>	Test tip witz shatter-proof insulated sleeve. Insulation and oxide layers can be penetrated by the slender stainless steel tip. 4mm diameter brass socket connection. Accessory (optional): tip prodector, IC-tap SS 260
<b>typ:</b>	PRUEF 2 schwarz / black
<b>system:</b>	4mm system
<b>order number:</b>	973 368-100
<b>color</b>	●
<b>other color versions:</b>	● ●
<b>technical data</b>	
<b>measurement category acc. to IEC 61010:</b>	CAT I
<b>pin dimensions</b>	2 mm
<b>type of contact:</b>	test tip (unsprung)
<b>type of termination:</b>	4 mm socket (unsprung)
<b>rated voltage:</b>	30 VAC / 60 VDC
<b>contact resistance:</b>	50 mOhm
<b>material</b>	
<b>contact material:</b>	tip: stainless steel socket: brass
<b>contact surface material:</b>	tip: nickel
<b>housing material:</b>	PP
<b>environmental conditions:</b>	
<b>temperature range:</b>	-20 °C to +80 °C
<b>inflammable class:</b>	
<b>housing (basic material):</b>	UL 94 HB
<b>drawing</b>	