

Weller®

HIGH-PERFORMANCE LED SOLDERING IRONS

LIGHT DUTY



15-WATT LED SOLDERING IRON



Three 5mm high-temperature, long-life LEDs at 25 lumens/ft² for superior soldering accuracy and application illumination



Co-molded, soft-grip ribbed handle design for maximum comfort and reduced slippage



Triangular area for maximum of tip control and round handle for ease of tip rotation



High-performance, stainless-steel heater technology with heat up to 750°F



A 7-year warranty, longest in the industry



Cord strain relief for extended life



Possible applications: micro-components, electronic kits, low-voltage wiring, wire connection <18 AWG (0.04" diameter)

UL Listed – cUL available

IMPORTANT: use only Weller® tips



PRODUCT DETAILS

| | |
|--------------------|--|
| Catalog number: | SP15NUS |
| UPC number: | 03703266842 |
| Type: | Non-temperature controlled |
| Wattage: | 15W |
| Temperature: | 750° F / 400° C |
| Cord length: | 5 feet |
| Iron tip: | S5, screwdriver, 0.078" |
| Package includes: | Peg hook, retail packaging, iron stand, user manual |
| Compatible tips: | S3, screwdriver, 0.138" S31*, conical, 0.015" S32*, screwdriver, 0.078" *Long-life tips |
| Stock item: | Normal stock item |
| Packaging (LxWxH): | 11" x 4.25" x 1.89" |
| Gross weight: | 0.317 lbs. |

A family of wattages: **15** **25** **40** **80** Find your favorite.

