

Weller®

HIGH-PERFORMANCE LED SOLDERING IRONS

MEDIUM DUTY



40-WATT LED SOLDERING IRON KIT



Three 5mm high-temperature, long-life LEDs at 25 lumens/ft² for superior soldering accuracy and application illumination



Co-molded, soft-grip ribbed handle design for maximum comfort and reduced slippage



Triangular area for maximum of tip control and round handle for ease of tip rotation



High-performance, stainless-steel heater technology with heat up to 900°F



A 7-year warranty, longest in the industry



Cord strain relief for extended life

Possible applications: hobby models, small appliance, small engine repair, crafts, wire connection <8 AWG (0.13" diameter)

UL Listed – cUL available

IMPORTANT: use only Weller® tips



PRODUCT DETAILS

Catalog number:	SP40NKUS
UPC number:	037103266927
Type:	Non-temperature controlled
Wattage:	40W
Temperature:	900° F / 482° C
Cord length:	5 feet
Iron tip:	MT10, chisel, 0.25"
Package includes:	Peg hook, retail packaging, iron stand, user manual, Soldering aide tool, lead-free solder, ST3 and ST7 tips
Compatible tips:	ST1, screwdriver, 0.063" ST2, screwdriver, 0.093" ST3, screwdriver, 0.125" ST4, screwdriver, 0.188" ST5, flat, 0.031" ST6, screwdriver, 0.031" ST7, conical, 0.031" ST8, screwdriver, 0.062"
Stock item:	Normal stock item
Packaging (LxWxH):	12.37" x 4.87" x 1.76"
Gross weight:	0.432 lbs.

A family of wattages: **15** **25** **40** **80** Find your favorite.



www.WellerRed.com

© 2013 Apex Tool Group, LLC | 1000 Lufkin Road | Apex, NC 27539-8160 | USA | Phone 919.387.2543 | Fax 877.395.9963 | Specifications subject to change without notice.