

6.02013.00 ASA 32 L

## 1200 Watt All-purpose Vacuum Cleaner ASA 32 L with automatic switch on



- Mobile, compact vacuum cleaner for liquids and dry solids with commercial registration
- Suitable for extracting dusts and chips from power tools as well as for cleaning the construction site, workshop, vehicle and much more
- Certified for extracting dust particles of dust class L (AGW values  $\geq 1 \text{ mg/m}^3$ )
- Also suitable for absorbing non-flammable liquids
- Automatic shutoff that is disconnected while absorbing the suction flow as soon as the maximum filling height of the container is reached
- Special air cooling system for long service life of the powerful motor
- Integrated socket with automatic start mechanism. When the connected electrical tool is turned on, the motor of the multi-purpose vacuum cleaner also starts running automatically.
- Sturdy and washable pleated filter with large surface against quick clogging
- Easy and quick filter change
- Option to wind up the cable
- Practical accessory case and storage area



## Comparative technical values

Air output (at fan)	4.200 l/min
Vacuum	210 hPa (mbar)
Filter surface	3.600 cm <sup>2</sup>
Rated input power	1.200 W
Container volume	32 l
Suction hose:	
- Diameter	35 mm
- Length	3,2 m
Weight	7 kg

## Scope of delivery

Suction hose (Ø 35 mm, 3.2 m long), 2 suction pipes, 1 Cellulose pleated filter, Grouting nozzle, Pipe holder, Floor nozzle (260 mm wide), Suction nozzle (120 mm wide)