

## 31-piece tool set

**CM.EL29**

- Supplied loose.

ΔΔ : 1,9 kg.

Code	Qty	Description
<b>AN</b>	3	Screwdrivers for slotted heads 3x75 - 4x100 - 5.5x150 mm
<b>ANP</b>	3	Insulated screwdrivers for Phillips® heads no. 0 - 1 - 2
<b>406.8MT</b>	1	Semi-flush diagonal cutter
<b>432.MT</b>	1	Precision half-round straight pliers
<b>149.Y</b>	1	Precision tweezers
<b>AEF.J3</b>	8	Micro-Tech® screwdrivers
<b>841.2</b>	1	Scissors
<b>845.1</b>	1	Interchangeable-blade scalpel
<b>1230.30</b>	1	Soldering iron 30 W
<b>661626</b>	1	Reel of solder wire
<b>839A.1</b>	1	Desoldering pump
<b>DELA1031.01</b>	1	Rule 150 mm
<b>113A.6C</b>	1	Adjustable wrench
<b>AS.6L140T2</b>	6	Roll set of needle files
<b>181.18G</b>	1	Lockable multigrip pliers



## Set CM.EL29 with soft case BV.16

**2138.EL29**

- Dimensions : 440 x 315 x 75 mm.

ΔΔ : 2,8 kg.



## 41-piece metric tool set

**CM.EL30**

- Supplied loose.

ΔΔ : 2,5 kg.

Code	Qty	Description
<b>22.JE6T</b>	6	Roll set of miniature open-end wrenches 3.2 to 13 mm
<b>A.65x150</b>	4	Insulated screwdrivers 3.5x75 - 4x100 - 5.5x150 - 6.5x150 mm
<b>AP.VE</b>	3	Insulated screwdrivers for Phillips® heads no. 0-1-2
<b>AD.VE</b>	3	Insulated screwdrivers for Pozidriv® heads no. 0-1-2
<b>AMR</b>	1	Multiblade screwdrivers 1.5 - 2 and 2.5 mm
<b>HT.2X2,4</b>	1	Tuning screwdriver for slotted heads 2 and 2.4 mm
<b>74.JL9</b>	9	Nut spinners 3.2 to 10 mm
<b>405.12MT</b>	1	Precision diagonal cutters
<b>406.MT</b>	1	Diagonal cutters
<b>431.MT</b>	1	Short-nose pliers
<b>433.LMT</b>	1	Angled half-round nose pliers
<b>449I</b>	1	Crimping pliers
<b>1230.30</b>	1	Soldering iron 30 W
<b>661626</b>	1	Reel of solder wire
<b>839A.1</b>	1	Desoldering pump
<b>841.4</b>	1	Electricians scissors
<b>840.1</b>	1	Electricians knife with wire stripper
<b>AIG.PAM140T2</b>	1	Flat needle file 140 mm
<b>AIG.RD160T2</b>	1	Round needle file 160 mm
<b>149.Y</b>	1	Precision tweezers
<b>1830.1</b>	1	Extra-soft silk brush

