




74 Metric wrench sets


- Supplied as wallet or rack sets.



			mm	$\Delta\Delta$ kg
74.JL9	N.38A-10D		3,2 - 4 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10	1
74.JL14	•		3,2 - 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14	1,69
74.P14E	•		3,2 - 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14	1,81



74T Metric forged Tee-handled 6-point nut spinners


- For higher torques.
- High-strength forged carbon steel.
- Permanently moulded acetate tee-handle resists oil, grease and hydrocarbons.
- Polished chrome finish.



	A mm	E mm	B mm	C mm	D mm	L mm	$\Delta\Delta$ g
74T.5	5	85	8	25	130	160	80
74T.5,5	5,5	85	9	30	130	160	85
74T.6	6	85	9	35	130	160	100
74T.7	7	85	11	35	130	160	115
74T.8	8	85	12	50	130	160	120
74T.9	9	85	13	50	130	160	120
74T.10	10	85	14	50	130	160	125
74T.11	11	85	16	50	130	160	130
74T.12	12	85	18	50	130	160	132
74T.13	13	85	19	55	130	160	135
74T.14	14	85	20	55	130	160	138



94A Metric box-shank nut spinners



- Ideal for long threaded rods.
- Chrome finish.

	A mm	B mm	C mm	E mm	L mm	$\Delta\Delta$ g
94A.3,2	3,2	7	125	25	225	70
94A.4	4	7	125	25	225	75
94A.5	5	7	125	25	225	80
94A.5,5	5,5	7	125	25	225	100
94A.6	6	9	125	28	235	110
94A.7	7	9	125	28	235	125
94A.8	8	11	125	28	235	152
94A.9	9	11	125	28	235	160
94A.10	10	13	125	32	245	165
94A.11	11	13	125	32	245	245
94A.12	12	16	125	39	260	260
94A.13	13	16	125	39	260	275
94A.14	14	18	125	39	260	280



94A Metric box-shank nut spinner sets

- Supplied as wallet sets.

		\varnothing mm	$\Delta\Delta$ kg
94A.JL9	N.38A-10D	3,2-4-5-5,5-6-7-8-9-10	1,2
94A.JE13T	N.38A-14A	3,2-4-5-5,5-6-7-8-9-10- 11-12-13-14	2,295

