

Your shopping cart

[Products](#)
[MyHARTING](#)
[Downloads / Catalogue order](#)

Han B Base Panel 2 levers

[Spotted an error?](#) | [Print page](#) | [Back](#)



Image is for illustration purposes only. Please refer to product description.

Part number:	09 30 010 0301
Description:	Han B Base Panel 2 levers
Type sheet:	PDF
Colour, locking element:	RAL 7032 (light grey)
Flammability locking lever acc. to UL 94:	V 0
Panel cut out (mm x mm):	60 x 35
Protection class acc. to UL 50:	NEMA Typ 4/4X/12
RoHS conformity:	Yes
Size:	10 B
Material, hood/housing:	aluminium die-cast
Material, seal:	NBR
Colour, hood/housing:	RAL 7037 (grey)
Degree of protection acc. to DIN EN 60 529:	IP 65
Locking type:	2 levers on the housing
Material, locking element:	Stainless steel
Locking lever:	Han-Easy Lock®
Type of hood/housing:	Housings, bulkhead mounting
Series:	Han® B
Housing:	Yes
Limiting temperature, min.:	-40 °C
Limiting temperature, max.:	125 °C
Style:	Low construction

[Login to MyHARTING](#)
 for pricing and stock check

Quantity:
[Shopping cart](#)
[Email inquiry](#)

Catalogue
 Chapter Han® Hoods and Housings with metric thread - Page 43

[Browse](#)
[Download](#)

Find products that perfectly fit to this one and configure your entire connector!
[Combinable products](#)

Downloads

Title	Download
Type sheet	PDF
Type sheet	DXF
CAD data 3D	STEP
CAD data 3D	JT
Chapter Han® Hoods and Housings with metric thread - Page 43	PDF

Recently viewed - [Delete](#)

 Han B Base Panel 2 levers Show product details	 Han E M Crimp Contact Ag WG 16AWG Show product details
 Han D F Crimp Contact Ag AWG 26 - 22 Show product details	 Han Q 5/0 Female Insert Crimp Show product details

Recently searched - [Delete](#)

- All categories: [09 33 000 6104](#) (1)
- All categories: [09 15 000 6204](#) (1)
- All categories: [0912 005 3101](#) (1)
- All categories: [0932 032 3101](#) (1)
- All categories: [09 99 000 0021](#) (1)
- All categories: [09 33 000 6202](#) (1)
- All categories: [09 99 000 0110](#) (1)
- All categories: [0914 012 3101](#) (1)
- All categories: [09 14 017 3001](#) (1)
- All categories: [0916 072 3101](#) (1)



Han EE 32 Pos. Insert
Female Crimp

[Show product details](#)



HAN CRIMP TOOL
WITH LOCATOR

[Show product details](#)

Han E F Crimp
Contact Ag 2.5
mm/14AWG

[Show product details](#)



Han Hand Crimp Tool

[Show product details](#)



Han DD module,
crimp female

[Show product details](#)



Han DDD module,
crimp male

[Show product details](#)

[Home](#) | [Contact](#) | [Privacy Policy](#) | [Terms of Use](#) | [Sales and delivery conditions](#) | [Imprint](#)

HARTING contact: HARTING Ltd. | CASWELL ROAD | NN4 7PW NORTHAMPTON | Great Britain
HARTING support: +44 1604 827500 | **E-mail address** (For questions regarding products, orders and user accounts)

Website support: +49 5772 47-9399 | **E-mail address** (For technical problems regarding the website)

[ABOUT SSL CERTIFICATES](#)

Follow us on

