




FGG.00.304.CLAD35

MECHANICAL DETAILS

| | |
|--------------------------|---------------------------------------------------------------------------------------------------|
| Shell Style Model | FG* : Straight plug cable collet |
| Keying | 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Housing Material | Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces |
| Cable Fixing | 2.8 - 3.5 mm |
| Variant 2 | : |

| | A | L | M | S1 | S2 |
|-----|------|------|------|------|------|
| Mm. | 6.4 | 28.5 | 20.5 | 5.5 | 5 |
| In. | 0.25 | 1.12 | 0.81 | 0.22 | 0.20 |




Available Download

[unipole_multipole.pdf](#)

PERFORMANCE DETAIL

| | |
|-----------------------|-------------------------------|
| Insert | 0.304 : 4 Low Voltage |
| Insulator | L: PEEK |
| Specifications | |
| Contact Type: | Solder |
| Max. Matings: | 5000 |
| Contact Dia.: | 0.5 mm (0.02in) |
| Bucket Dia.: | 0.4 mm (0.016in) |
| Max. Solid | 0.09 mm ² (AWG 28) |
| Max. Stranded | 0.05 mm ² (AWG 30) |
| R (max): | 8.7 mOhm |



OTHER CHARACTERISTICS

| | |
|--------------------------|---------|
| Shell Style/Model | Libellé |
| IP Rating | 50 |



Related links

- [Contact](#)
- [Quote Request](#)
- [Catalogs Downloads](#)
- [Catalogs Requests](#)
- [Sample Request](#)
- [3D drawings](#)