



PKG.M0.8GL.LN

MECHANICAL DETAILS

Shell Style Model PK* : Fixed receptacle with two nuts (back panel mounting)


Keying 1 key (alpha=0; Plug: male contact; Receptacle: female contact)

Housing Material PSU (Polysulfone), gray

Cable Fixing 0 - 0 mm

Variant 2 N : Black front nut

	A	Lmax	N
Mm.	19.5	25	22.2
In.	0.77	0.98	0.87



PERFORMANCE DETAIL

Insert 1P.M08 : 8 Low Voltage

Insulator Specifications

Contact Type: Solder

Max. Matings: 1000

Contact Dia.: 0.7 mm (0.0275in)

Bucket Dia.: 0.6 mm (0.024in)

Max. Solid 0.14 mm² (AWG 26)

Max. Stranded 0.14 mm² (AWG 26)

R (max): 6.5 mOhm



OTHER CHARACTERISTICS

Shell Style/Model Libellé

F ret (min): 50 N

F ret (max): 150 N

IP Rating 50



Available Download



Related links

- [Contact](#)
- [Quote Request](#)
- [Catalogs Downloads](#)
- [Catalogs Requests](#)
- [Sample Request](#)
- [3D drawings](#)