

Coded safety switch PSENcode



The coded safety switch PSENcode provides rapid diagnostics thanks to a clear LED display - whether for safety gate or position monitoring.



PSEN cs2.1p / PSEN cs2.1 1Unit

Product number: 540100

Type:	PSEN cs2.1p
Product version:	1.3
Approvals:	CE, cULus Listed, TÜV, GOST
Sensor principle:	Transponder
Type of coding:	Fully coded
Number of OSSD outputs:	2
Number of inputs:	2
Connection type:	M12, 8pol. male
Supply voltage:	24 V
Supply voltage type:	DC
Power consumption DC:	2.0 W
Assured switching distance:	15.0 mm
Assured release distance:	40 mm
Protection type, housing:	IP67
Width dimension:	40.0 mm
Height dimension:	75.0 mm
Depth dimension:	40.0 mm
Gross weight:	184 g
Net weight:	150 g

Copyright 2000-2012 Pilz GmbH & Co. KG All rights reserved. All pictures, graphics, texts, sound files, video files and animation files on this website are subject to copyright and/or other laws to protect intellectual property. No data may be copied, amended or used in other publications, whether in electronic or printed format, without the express agreement of Pilz GmbH & Co. KG.