

Safe hinge switch PSEnhinge



The limit stop on the safe hinge switch can be individually selected and is suitable for rotatable and hinged gates and flaps.



PSEN hs1.1p

Product number: 570270

Type:	PSEN hs1
Product version:	1.0
Approvals:	CE, BG, cCSAus
Number of N/C:	2
Max. current at AC15:	3.0 A
Voltage at AC15:	230 V
Connection type:	M12
Protection type, housing:	IP67
Width dimension:	82.0 mm
Height dimension:	147.0 mm
Depth dimension:	19.5 mm
Gross weight:	400 g
Net weight:	330 g

Copyright 2000-2012 Pilz GmbH & Co. KG All rights reserved. All pictures, graphics, texts, sound files, video files and animation files on this website are subject to copyright and/or other laws to protect intellectual property. No data may be copied, amended or used in other publications, whether in electronic or printed format, without the express agreement of Pilz GmbH & Co. KG.