



Item no.: 261-112/341-000
 Product description: 2-CONDUCTOR TERMINAL STRIP PUSH BUTTONS ON BOTH SIDES WITH FIXING FLANGE FOR SCREW OR SIMILAR MOUNTING TYPES 3.2 MM Ø MOUNTING ADAPTER AVAILABLE FOR TS 35 (209-123) 12 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
pole count	12
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 14 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	24 A
Weight	32.24 g
Color	gray
Wiring type	Side-entry
No. of connection Points	24
No. of potentials	12
Height	23.2 mm
Height	0.914 in
Width	86.5 mm

Width	3.406 in
Depth	28 mm
Depth	1.103 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
xxx-xxx/000-006	blue

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected