


## Front panels, U profile, shieldable



Product illustrations are exemplary illustrations and can deviate from supplied products.

**Part no.:** 20848-013

**Features:**

- High stability through U profile
- Front panel, U profile, Al, front anodised, rear conductive, 2 alignment pins pressed-in, stainless steel
- Differences in the finish between 2 ... 12 HP and 14 ... 84 HP

Add to basket



**Standard pack quantity 5**



**Technical Information:**

Description	Height	Width	Height	B
Front panels, U profile, shieldable	3 U	14 HP	128.4 mm	70.8 mm

**Downloads:**

Download CAD data in DWG/DXF/PDF format ([Log in](#) required) 

To gain access to the additional information you must [log in](#).  
If you do not yet have a user name, you may [register here](#).

**Accessories:**

Part no.	Description	
<a href="#">21101-853</a>	Textile EMC gasket 3 U, PU 10 pieces	Add to basket
<a href="#">21101-854</a>	Textile EMC gasket 3 U, PU 100 pieces	Add to basket

**Note:**

- Standard pack quantity:  
2 to 28 HP: 5 pieces,  
42 to 84 HP: 1 piece,  
supplied in standard pack quantities (SPQ) only
- Please order EMC profile seal and fixing materials separately