



Global Part Number	PKM44EWH1001C
Previous Part Number	
Sound Pressure Level	75dB min.
Measure Condition of Sound Pressure Level	[30Vp-p,1kHz,square wave,1m]
Oscillating Frequency	
Measure Condition of Oscillation Frequency	
Current Consumption	
Measure Condition of Current Consumption	
Min. of Operating Voltage Range	
Max. of Operating Voltage Range	30.0 Vp-p max.
Capacitance	68.0nF ±30%
Measure Condition of Capacitance	[120Hz]
Type	Lead Wire Type
Operating Temperature Range	-20 to +70°C
Storage Temperature Range	-30 to +80°C