

18V Drill / Screwdrivers - Cordless



Model Number	DC728KA	DC759KA	DC920KB
No Load Speed	0-400/0-1400 rpm	0-400/0-1400 rpm	0-400/0-2000 rpm
Drilling Capacity Steel	10 mm	13 mm	13 mm
Drilling Capacity Wood	38 mm	38 mm	50 mm
Maximum Torque	40 N-m	44 N-m	56 N-m
Battery	2 x 1.3Ah Ni Cd	2 x 2.0Ah Ni Cd	2 x 2.6Ah Ni MH
Weight	2.0 kg	5.2 kg	2.7 kg

DC729KA



18V mid handle drill/driver. Two speed settings, variable speed and reverse switch for controllable use. 17 position adjustable torque control. Supplied with charger, 2 x 1.3Ah Ni Cd battery packs and carrying case.

Description	Order Code	Price Each
DC729KA drill/screwdriver	135-2956	
Replacement battery DE9098	135-2986	

DC759KA



18V drill driver for drilling and screwdriving applications. Two speed settings, variable speed and reverse action. 17 position adjustable torque control. 13mm single sleeve keyless chuck. Supplied with charger, 2 x 2.0Ah Ni Cd battery packs and carry case.

Description	Order Code	Price Each
DC759KA drill/screwdriver	135-2962	
Replacement battery DE9095	135-2983	

DC920KB



18V heavy duty drill/driver suitable for heavy duty drilling and screwdriving applications. Three speed settings for optimum performance in high torque, normal use and high speed applications. Twenty two position adjustable torque control settings for precise screwdriving. 13mm keyless chuck with automatic spindle lock. Supplied with one hour charger, 2 x 2.6Ah Ni MH battery packs and heavy duty carry case.

484361

Description	Order Code	Price Each
DC920KB drill/screwdriver	135-2964	
Replacement battery DE9503	135-2989	