


KEMET Part Number: PMR209MC6100M022R30
(P409CE104M250AH220)

Capacitor, film, 0.1 uF, +/-20% Tol, -40/+85C, Integrated Resistor (X2), 630V@85C, Lead Spacing=20.3 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	24	MAX
H	14	MAX
T	7.6	MAX
S	20.3	+/-0.4
LL	30	+5
F	0.8	+/-0.05

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	250

General Information	
Supplier:	KEMET
Miscellaneous Electrical:	Resistor tol: +/-30%

Specifications	
Capacitance:	0.1 uF
Rated Temperature:	85C
Voltage @ rated temp:	630V
Voltage AC:	250VAC
Tolerance:	+/-20%
Body Type:	Radial Molded
Dielectric:	Metallized Paper
Application:	Integrated Resistor (X2)
Temperature Range:	-40/+85C
Electrical Name (Other):	Resistor
Electrical Value (Other):	22
Electrical Units (Other):	Ohms
Insulation Resistance:	3 GOhm