

**W-Series, Accessories
WQV 6/10**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Order No.	1052260000
Type	WQV 6/10
Version	W-Series, Accessories, Cross-connector, For the terminals, No. of poles: 10
GTIN (EAN)	4008190153977
Qty.	20 pc(s).

W-Series, Accessories
WQV 6/10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	77.3 mm	Width	7.6 mm
Height	18 mm	Net weight	16.75 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Additional technical data

Installation advice	Direct mounting	Version	For the terminals
---------------------	-----------------	---------	-------------------

Dimensions

TS 35 offset	28 mm
--------------	-------

Rated data

Rated voltage	0 V	Rated current	57 A
---------------	-----	---------------	------

Material data

Material	PA 66	Colour	Yellow
UL 94 flammability rating	V-2		

System specifications

Product family	W-Series, Accessories
----------------	-----------------------

Classifications

ETIM 2.0	EC000489	ETIM 3.0	EC000489
UNSPSC	30-21-18-01	eClass 4.1	27-14-11-99
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Approvals

ROHS	Conform
------	---------

Downloads

DXF	08861_WQV_6-10_DXF.dxf
3-D model	