

Multi-purpose cutters

N ^o	← a →		← b →		kg	☐	€
	mm	"	mm	"			
D47-2	140	5 1/2	31	1 1/4	0,05	15	8,00
D48-2	195	7 3/4	42	1 5/8	0,11	10	9,00



- NEW: ERGO-handle for increased comfort – reduced hand fatigue!
- Stainless steel blades
- On carded hang pack

Angled combi snips

N ^o	← a →		← b →		kg	☐	€
	mm	"	mm	"			
D48A-2	190	7 1/2	36	1 3/8	0,11	10	9,50



- NEW: ERGO-handle for increased comfort – reduced hand fatigue!
- Stainless steel blades
- Offset blades
- On carded hang pack

Cable cutters

N ^o	← a →		kg	☐	€
	mm	"			
D49-2	165	6 1/2	0,12	10	9,00



- NEW: ERGO-handle for increased comfort – reduced hand fatigue!
- For multicore cables with diameter up to 10 mm
- Stainless steel blades
- On carded hang pack

MULTISNIP Master



N ^o	Contents/pc.	← a →		← b →		kg	☐	€
		mm	"	mm	"			
D51A		235	9 1/4	50	2	0,18	5	12,50
D51A-D	20 units of D51A in the display	-	-	-	-	4,20	1	250,00
DMS-D	6xD22A/6xD51A 8xD48A	-	-	-	-	5,63	1	389,90



- For long continuous straight and curved cuts
- All metal parts are made of stainless steel
- Handle made of robust fibreglass-reinforced plastic with a soft material insert
- Angled cutter head for greater safety – keep the material at a distance and keep your hand out of the danger zone
- On carded hang pack