




Dimensions (mm)



ALL DIMENSIONS IN MILLIMETRES

DIMENSION	IEC		EVER READY	
	MAX	MIN	MAX	MIN
A	172		168.7	160.3
B			152.4	
C			27	23.8
Ø	67		66.7	63.5

Technical Information

Univercell Battery No **DB8014**

Battery chemistry Alkaline Manganese Dioxide

Voltage 1.5v (nominal open circuit)

Capacity 40Ah nominal

Nominal Weight 420g

Terminals: This battery has two 4BA screw terminals with non-insulated nuts

Charge at NOT RECHARGABLE

Recommended operating temperature 20 = / -5°C

Recommended storage temperature 20° ± -5°C

Issue 1	Date: 19/06/13
---------	----------------



UNIVERCELL BATTERY CO. LTD
 Unit 9B, Stafford Park 12, Telford, Shropshire, TF3 3BJ (UK)
 Tel: +44 (0)1952 293388 Fax: +44 (0)1952-290473
 Email: Sales@univercell-batteries.co.uk
www.univercell-batteries.co.uk



FM29249