

Accessories

Test Leads / Cables / Probes

Adaptors

LCR Fixtures

Cases / Bags / Racks

Special Applications

ATA-001

ATA-002

GAP-801

GAP-802

GDM-01

GDM-SC1

GHT-106R

GKT-001

GKT-002

GKT-003

GKT-006A

GPS-001

GRC-1201

GTC-001

GTC-002

RLB-001

TL-06

Home > Product > Accessories > Special Applications > RLB-001

RLB-001

+ SHARE

PRINT

Features

- * 1GHz Return Loss Bridge
- * N-Type Connector, Source/Load:Female, Couple:Male
- * Impedance : 50 ohms
- * 88 x 54 x 32(mm), 230g
- * For : GSP-Series



| Description | Specification | Accessories | Ordering Information | Download |
|--------------------------|---|-------------|----------------------|----------|
| PARAMETER | | | | |
| Frequency Range | 10MHz ~ 1GHz | | | |
| Directivity | 10MHz ~ 100MHz: >48dB 100MHz ~ 1000MHz: >38dB | | | |
| Insertion Loss | Source to Load: <10dB Load to Coupler: <6dB | | | |
| Return Loss | Source Return Loss: >7dB Load Return Loss: >11dB Coupler Return Loss: >11dB | | | |
| Characteristic Impedance | 50 ohm | | | |
| Connector | N Type Source and Load: Female Coupler: Male | | | |
| Dimension & Weight | 88(W) x 54(H) x 32(D) mm 230g | | | |

Product Search

Please input keyword

SEARCH

Sales Contact