

Cover for Holder OG (Clip) 5x20, OG (Halter) 5x20, UH, UHB

**References**

Fits to type: OG (Clip) 5x20; OG (Holder) 5x20; UH; UHB

**Weblinks**


pdf-datasheet, html-datasheet, General Product Information, Approvals, CE declaration of conformity, RoHS, CHINA-RoHS, e-Shop, SCHURTER-Stock-Check, Distributor-Stock-Check, Detailed request for product

**Technical Data**

Fuse-Link	5 x 20 mm
Admissible Ambient Air Temp.	-40 °C to 85 °C
Material: Cover	Thermoplastic Transparent UL 94V-0
Storage Conditions	0 °C to 60 °C, max. 70% r.h.

**Dimensions**

26.2 mm

**Variants**

Description	Order Number
Transparent Cover 1.6 W	0853.9561
Transparent Cover 2.5 W	0853.9562

**Packaging Unit**

Plastic Bag (100 pcs.)