


# Han® 3 A RJ45 Hybrid



Han® 3 A, Hybrid, components device side panel feed-throughs

Identification	Part No.	Drawing	Dimensions in mm
<b>RJ45 female</b> for direct device integration solder variant SMD 90° angled I	09 45 551 1100 <sup>1)</sup> 09 45 551 1110 <sup>2)</sup>		pcb layout 
<b>Power module with 4 contacts</b> for direct device integration II	09 45 525 0040		
<b>Housing bulkhead mounting separate</b> incl. flat seal for direct device integration Plastic version, black Metal version Standard, grey III	09 45 525 0021 10 12 005 1004		Dimensions valid for plastic version 
<b>Panel feed-through set</b> Plastic version, black, Cat. 5 Metal version Standard, grey, Cat. 5 Metal version M, black, Cat. 5 Metal version Standard, grey, Cat. 6 Metal version M, black, Cat. 6 IV	09 45 225 1300 10 12 005 1002 09 45 215 1301 09 45 215 1760 09 45 215 1761		
<b>Protection cover for panel feed-through</b> IP 65 / IP 67 Plastic version, black Metal version Standard, grey Metal version M, black	09 20 003 5449 09 20 003 5425 09 37 003 5405		

1) Packaging: Blister à 120 pieces

2) Packaging: Tape & Reel à 130 pieces

Technical characteristics and general informations see page 04.15