
















Metal hoods/housings for industrial applications / 1 lever locking system

Identification	Image	Part number		Cable entry metric	Drawing	Dimensions in mm
		Low construction	High construction			
Hoods side entry		19 30 006 1540 19 30 006 1541		1 x 20 1 x 25		
side entry			19 30 006 0546 19 30 006 0547	1 x 25 1 x 32		
Hoods top entry		19 30 006 1440		1 x 20		
top entry			19 30 006 0446 19 30 006 0447	1 x 25 1 x 32		
Hoods without cable entry			09 30 006 0801	—		

Han Hoods
Housings