



Cutters Micro-Tech[®] "compact" handling 405.MT

- These clamps combine cutting performance maneuverability thanks to their new bullet-shaped thin.
 - The models fall restraint avoid the ejection wire. The 405.MT For cutting of piano wire up to 0.4 mm.
- Weight: 60 g.

| | |
|-----------------------------|--|
| B [mm] | 10.5 |
| C [mm] | 9.5 |
| E [mm] | 7 |
| L [mm] | 110 |
| Cutting | h |
| Cu - Ni Ø [mm] | 0.3 to 1.3 |
| Description SKU | Cutting pliers precision |
| Fe 30 HRc diam. [Mm] | 0.7 |
| Standard | NF ISO 9654, ISO 9654, DIN ISO 9654, ASME B107.500 |
| Piano diam. [Mm] | 0.4 |
| Reference | 405.MT |
| Fall restraint | - |