

# Scroll 8D

# 8" TABLET PC

# ANDROID™ 4.2 JELLY BEAN

by **Storage Options**

Accessories available at  
[storageoptions.com](http://storageoptions.com)

Scroll 8D is a capacitive touch-screen Dual-Core Android 4.2 tablet that incorporates Bluetooth wireless technology. Portable, with its highly responsive 8" high resolution (1024 x 768) screen, powerful hardware and a stylish, slim design, the Scroll 8D is the perfect companion for internet browsing, games, videos and a host of other applications.

A powerful Dual Core Boxchip A20 processor combined with a speedy Quad-Core Mali-400 Graphics Processor mean that the Scroll 8D is capable of handling demanding games and online content seamlessly. Add the latest Android 4.2 (Jelly Bean) operating system, which is designed to optimise tablet enjoyment and functionality, and a great all round experience is guaranteed.

Scroll 8D is also a highly versatile multimedia device – enjoy your favourite music or connect to a 3D or HD TV or monitor via an optional high-speed HDMI cable to enjoy your selection of films in full 1080p HD or 3D.

- Intuitive 8" High Resolution 1024 x 768 Capacitive Screen
- Dual Core Boxchip Cortex A20 Processor
- Quad Core Mali-400 Graphics Processor
- Wireless Bluetooth® Technology to Connect Peripherals
- Front and Rear Cameras
- Android™ 4.2 (Jelly Bean)

**Part No. 65491**

**Contents - Tablet PC, Power Adaptor, USB Cable, On-The-Go Cable and Manual.**

\*Bluetooth accessories, micro SD card and HDMI cable are available separately and not included.



**ANDROID™ 4.2**

# Scroll 8D

# 8" TABLET PC

# ANDROID™ 4.2 JELLY BEAN

by **Storage Options**

Accessories available at  
[storageoptions.com](http://storageoptions.com)



## Software

- Android™ 4.2.2 (Jelly Bean)

## Hardware

- Processor: A20 Dual Core Cortex A7 Processor
- Display: 8" 1024 x 768 Capacitive Touch Screen
- Memory: 1GB RAM
- Internal Memory: 8GB Memory Built-in, Micro SD Card Expandable Up to 64GB
- Battery: 4200 mAh Lithium Ion Rechargeable Battery
- Camera: Front and Rear Facing Cameras
- G-Sensor: 16 bit G-sensor, Monitors / Rotates Screen Through 360°
- Speakers: Built-in Speaker
- Headphones: 3.5mm Earphone Jack

## Connectivity

- Wireless Networking: Wi-Fi 802.11b/g/n
- Bluetooth: Version 4.0
- TV Output: HDMI TV-Output (Mini HDMI)
- Micro USB Host Port: For Peripheral Connection (e.g. Keyboard, Flash Drive)
- Power: 5V DC

## Multimedia

- Video Support: Full HD 1080P Supports AVI, H.264, MPEG2, MPEG4, MKV, MP4
- E-Book Support: PDF, EPUB, MOBI

## Features

- Music, Photos, Movies, E-mail, 3D Games, 1080P 3D Video Output!

## Case

- Slim Aluminium & Plastic Casing

## Dimensions

- 213mm x 143mm x 13mm



ANDROID™ 4.2