

Thick Film Chip Resistor 0402




Features

- Small size and light weight
- Suitable for both wave and reflow soldering
- Reduction of assembly costs

Performance Specification

Temperature Coefficient	: 1Ω to 10Ω ±400PPM/°C 11Ω to 100Ω ±200PPM/°C >100Ω ±100PPM/°C
Short Time Overload	: ±5% : ±(2% +0.1Ω)Max. ±1% : ±(1% +0.1Ω)Max.
Insulation Resistance	: Min. 1,000MΩ
Dielectric Withstanding Voltage	: No evidence of flashover, mechanical damage, arcing or insulation breakdown.
Terminal Bending	: ±(1% +0.05Ω) Max.
Soldering Heat	: ±(1% +0.05Ω) Max.
Solderability	: Min. 95% coverage
Temperature Cycling	: ±5% : ±(1% +0.05Ω) Max. ±1% : ±(0.5% +0.05Ω) Max.
Humidity (Steady State)	: ±5% : ±(3% +0.1Ω) Max. ±1% : ±(0.5% +0.1Ω) Max.
Load Life in Humidity	: ±5% : ±(3% +0.1Ω) Max. ±1% : ±(1% +0.1Ω) Max.
Load Life	: ±5% : ±(3% +0.1Ω) Max. ±1% : ±(1% +0.1Ω) Max.


Derating Curve



Thick Film Chip Resistor 0402



Dimension



Type	Dimension (mm)				
	L	W	H	l ₁	l ₂
0402	1 ±0.1	0.5 ±0.05	0.35 ±0.05	0.2 ±0.1	0.25 ±0.1

Type	Power Rating at 70°C	Max. Working Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Tolerance %	Resistance Range
0402	1/16W	1A	2A	-	Jumper	<50mΩ
		50V	100V	100V	±1%	10Ω to 1MΩ
					±2%	1Ω to 10MΩ
					±5%	1Ω to 10MΩ

Part Number Table

Description	Part Number	Description	Part Number
Resistor, 1K, 0.063W, 1%, 0402, Reel	MC00625W040211K	Resistor, 1K2, 0.063W, 1%, 0402, Reel	MC00625W040211K2
Resistor, 1K, 0.063W, 1%, 0402	MC00625W040211K	Resistor, 1K2, 0.063W, 1%, 0402	MC00625W040211K2
Resistor, 1M, 0.063W, 1%, 0402, Reel	MC00625W040211M	Resistor, 1M2, 0.063W, 1%, 0402, Reel	MC00625W040211M20
Resistor, 1M, 0.063W, 1%, 0402	MC00625W040211M	Resistor, 1M2, 0.063W, 1%, 0402	MC00625W040211M20
Resistor, 1R, 0.063W, 1%, 0402, Reel	MC00625W040211R0	Resistor, 1R2, 0.063W, 1%, 0402, Reel	MC00625W040211R20
Resistor, 1R, 0.063W, 1%, 0402	MC00625W040211R0	Resistor, 1R2, 0.063W, 1%, 0402	MC00625W040211R20
Resistor, 1K05, 0.063W, 1%, 0402, Reel	MC00625W040211K05	Resistor, 1K21, 0.063W, 1%, 0402, Reel	MC00625W040211K21
Resistor, 1K05, 0.063W, 1%, 0402	MC00625W040211K05	Resistor, 1K21, 0.063W, 1%, 0402	MC00625W040211K21
Resistor, 1M05, 0.063W, 1%, 0402, Reel	MC00625W040211M05	Resistor, 1M21, 0.063W, 1%, 0402, Reel	MC00625W040211M21
Resistor, 1M05, 0.063W, 1%, 0402	MC00625W040211M05	Resistor, 1M21, 0.063W, 1%, 0402	MC00625W040211M21
Resistor, 1K1, 0.063W, 1%, 0402, Reel	MC00625W040211K1	Resistor, 1K27, 0.063W, 1%, 0402, Reel	MC00625W040211K27
Resistor, 1K1, 0.063W, 1%, 0402	MC00625W040211K1	Resistor, 1K27, 0.063W, 1%, 0402	MC00625W040211K27
Resistor, 1M1, 0.063W, 1%, 0402, Reel	MC00625W040211M10	Resistor, 1M27, 0.063W, 1%, 0402, Reel	MC00625W040211M27
Resistor, 1M1, 0.063W, 1%, 0402	MC00625W040211M10	Resistor, 1M27, 0.063W, 1%, 0402	MC00625W040211M27
Resistor, 1R1, 0.063W, 1%, 0402, Reel	MC00625W040211R10	Resistor, 1K3, 0.063W, 1%, 0402, Reel	MC00625W040211K3
Resistor, 1R1, 0.063W, 1%, 0402	MC00625W040211R10	Resistor, 1K3, 0.063W, 1%, 0402	MC00625W040211K3
Resistor, 1K15, 0.063W, 1%, 0402, Reel	MC00625W040211K15	Resistor, 1M3, 0.063W, 1%, 0402, Reel	MC00625W040211M30
Resistor, 1K15, 0.063W, 1%, 0402	MC00625W040211K15	Resistor, 1M3, 0.063W, 1%, 0402	MC00625W040211M30

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 1R3, 0.063W, 1%, 0402, Reel	MC00625W040211R30	Resistor, 1M8, 0.063W, 1%, 0402	MC00625W040211M80
Resistor, 1R3, 0.063W, 1%, 0402	MC00625W040211R30	Resistor, 1R8, 0.063W, 1%, 0402, Reel	MC00625W040211R80
Resistor, 1K33, 0.063W, 1%, 0402, Reel	MC00625W040211K33	Resistor, 1R8, 0.063W, 1%, 0402	MC00625W040211R80
Resistor, 1K33, 0.063W, 1%, 0402	MC00625W040211K33	Resistor, 1K87, 0.063W, 1%, 0402, Reel	MC00625W040211K87
Resistor, 1K4, 0.063W, 1%, 0402, Reel	MC00625W040211K4	Resistor, 1K87, 0.063W, 1%, 0402	MC00625W040211K87
Resistor, 1K4, 0.063W, 1%, 0402	MC00625W040211K4	Resistor, 1K96, 0.063W, 1%, 0402, Reel	MC00625W040211K96
Resistor, 1M4, 0.063W, 1%, 0402, Reel	MC00625W040211M40	Resistor, 1K96, 0.063W, 1%, 0402	MC00625W040211K96
Resistor, 1M4, 0.063W, 1%, 0402	MC00625W040211M40	Resistor, 10K, 0.063W, 1%, 0402, Reel	MC00625W0402110K
Resistor, 1K47, 0.063W, 1%, 0402, Reel	MC00625W040211K47	Resistor, 10K, 0.063W, 1%, 0402	MC00625W0402110K
Resistor, 1K47, 0.063W, 1%, 0402	MC00625W040211K47	Resistor, 10M, 0.063W, 1%, 0402, Reel	MC00625W0402110M0
Resistor, 1M47, 0.063W, 1%, 0402, Reel	MC00625W040211M47	Resistor, 10M, 0.063W, 1%, 0402	MC00625W0402110M0
Resistor, 1M47, 0.063W, 1%, 0402	MC00625W040211M47	Resistor, 10R, 0.063W, 1%, 0402, Reel	MC00625W0402110R
Resistor, 1K5, 0.063W, 1%, 0402, Reel	MC00625W040211K5	Resistor, 10R, 0.063W, 1%, 0402	MC00625W0402110R
Resistor, 1K5, 0.063W, 1%, 0402	MC00625W040211K5	Resistor, 10K5, 0.063W, 1%, 0402, Reel	MC00625W0402110K5
Resistor, 1M5, 0.063W, 1%, 0402, Reel	MC00625W040211M50	Resistor, 10K5, 0.063W, 1%, 0402	MC00625W0402110K5
Resistor, 1M5, 0.063W, 1%, 0402	MC00625W040211M50	Resistor, 10R5, 0.063W, 1%, 0402, Reel	MC00625W0402110R5
Resistor, 1R5, 0.063W, 1%, 0402, Reel	MC00625W040211R5	Resistor, 10R5, 0.063W, 1%, 0402	MC00625W0402110R5
Resistor, 1R5, 0.063W, 1%, 0402	MC00625W040211R5	Resistor, 100K, 0.063W, 1%, 0402, Reel	MC00625W04021100K
Resistor, 1K54, 0.063W, 1%, 0402, Reel	MC00625W040211K54	Resistor, 100K, 0.063W, 1%, 0402	MC00625W04021100K
Resistor, 1K54, 0.063W, 1%, 0402	MC00625W040211K54	Resistor, 100R, 0.063W, 1%, 0402, Reel	MC00625W04021100R
Resistor, 1R54, 0.063W, 1%, 0402, Reel	MC00625W040211R54	Resistor, 100R, 0.063W, 1%, 0402	MC00625W04021100R
Resistor, 1R54, 0.063W, 1%, 0402	MC00625W040211R54	Resistor, 105K, 0.063W, 1%, 0402, Reel	MC00625W04021105K
Resistor, 1K6, 0.063W, 1%, 0402, Reel	MC00625W040211K6	Resistor, 105K, 0.063W, 1%, 0402	MC00625W04021105K
Resistor, 1K6, 0.063W, 1%, 0402	MC00625W040211K6	Resistor, 105R, 0.063W, 1%, 0402, Reel	MC00625W04021105R
Resistor, 1M6, 0.063W, 1%, 0402, Reel	MC00625W040211M60	Resistor, 105R, 0.063W, 1%, 0402	MC00625W04021105R
Resistor, 1M6, 0.063W, 1%, 0402	MC00625W040211M60	Resistor, 11K, 0.063W, 1%, 0402, Reel	MC00625W0402111K
Resistor, 1R6, 0.063W, 1%, 0402, Reel	MC00625W040211R60	Resistor, 11K, 0.063W, 1%, 0402	MC00625W0402111K
Resistor, 1R6, 0.063W, 1%, 0402	MC00625W040211R60	Resistor, 11R, 0.063W, 1%, 0402, Reel	MC00625W0402111R
Resistor, 1K62, 0.063W, 1%, 0402, Reel	MC00625W040211K62	Resistor, 11R, 0.063W, 1%, 0402	MC00625W0402111R
Resistor, 1K62, 0.063W, 1%, 0402	MC00625W040211K62	Resistor, 11K5, 0.063W, 1%, 0402, Reel	MC00625W0402111K5
Resistor, 1K69, 0.063W, 1%, 0402, Reel	MC00625W040211K69	Resistor, 11K5, 0.063W, 1%, 0402	MC00625W0402111K5
Resistor, 1K69, 0.063W, 1%, 0402	MC00625W040211K69	Resistor, 11R5, 0.063W, 1%, 0402, Reel	MC00625W0402111R5
Resistor, 1M69, 0.063W, 1%, 0402, Reel	MC00625W040211M69	Resistor, 11R5, 0.063W, 1%, 0402	MC00625W0402111R5
Resistor, 1M69, 0.063W, 1%, 0402	MC00625W040211M69	Resistor, 110K, 0.063W, 1%, 0402, Reel	MC00625W04021110K
Resistor, 1K78, 0.063W, 1%, 0402, Reel	MC00625W040211K78	Resistor, 110K, 0.063W, 1%, 0402	MC00625W04021110K
Resistor, 1K78, 0.063W, 1%, 0402	MC00625W040211K78	Resistor, 110R, 0.063W, 1%, 0402, Reel	MC00625W04021110R
Resistor, 1K8, 0.063W, 1%, 0402, Reel	MC00625W040211K8	Resistor, 110R, 0.063W, 1%, 0402	MC00625W04021110R
Resistor, 1K8, 0.063W, 1%, 0402	MC00625W040211K8	Resistor, 115K, 0.063W, 1%, 0402, Reel	MC00625W04021115K
Resistor, 1M8, 0.063W, 1%, 0402, Reel	MC00625W040211M80	Resistor, 115K, 0.063W, 1%, 0402	MC00625W04021115K

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 115R, 0.063W, 1%, 0402, Reel	MC00625W04021115R	Resistor, 130R, 0.063W, 1%, 0402	MC00625W04021130R
Resistor, 115R, 0.063W, 1%, 0402	MC00625W04021115R	Resistor, 133K, 0.063W, 1%, 0402, Reel	MC00625W04021133K
Resistor, 12K, 0.063W, 1%, 0402, Reel	MC00625W0402112K	Resistor, 133K, 0.063W, 1%, 0402	MC00625W04021133K
Resistor, 12K, 0.063W, 1%, 0402	MC00625W0402112K	Resistor, 133R, 0.063W, 1%, 0402, Reel	MC00625W04021133R
Resistor, 12R, 0.063W, 1%, 0402, Reel	MC00625W0402112R	Resistor, 133R, 0.063W, 1%, 0402	MC00625W04021133R
Resistor, 12R, 0.063W, 1%, 0402	MC00625W0402112R	Resistor, 14K, 0.063W, 1%, 0402, Reel	MC00625W0402114K
Resistor, 12K1, 0.063W, 1%, 0402, Reel	MC00625W0402112K1	Resistor, 14K, 0.063W, 1%, 0402	MC00625W0402114K
Resistor, 12K1, 0.063W, 1%, 0402	MC00625W0402112K1	Resistor, 14R, 0.063W, 1%, 0402, Reel	MC00625W0402114R
Resistor, 12R1, 0.063W, 1%, 0402, Reel	MC00625W0402112R1	Resistor, 14R, 0.063W, 1%, 0402	MC00625W0402114R
Resistor, 12R1, 0.063W, 1%, 0402	MC00625W0402112R1	Resistor, 14K7, 0.063W, 1%, 0402, Reel	MC00625W0402114K7
Resistor, 12K4, 0.063W, 1%, 0402, Reel	MC00625W0402112K4	Resistor, 14K7, 0.063W, 1%, 0402	MC00625W0402114K7
Resistor, 12K4, 0.063W, 1%, 0402	MC00625W0402112K4	Resistor, 14R7, 0.063W, 1%, 0402, Reel	MC00625W0402114R7
Resistor, 12K7, 0.063W, 1%, 0402, Reel	MC00625W0402112K7	Resistor, 14R7, 0.063W, 1%, 0402	MC00625W0402114R7
Resistor, 12K7, 0.063W, 1%, 0402	MC00625W0402112K7	Resistor, 140K, 0.063W, 1%, 0402, Reel	MC00625W04021140K
Resistor, 12R7, 0.063W, 1%, 0402, Reel	MC00625W0402112R7	Resistor, 140K, 0.063W, 1%, 0402	MC00625W04021140K
Resistor, 12R7, 0.063W, 1%, 0402	MC00625W0402112R7	Resistor, 140R, 0.063W, 1%, 0402, Reel	MC00625W04021140R
Resistor, 120K, 0.063W, 1%, 0402, Reel	MC00625W04021120K	Resistor, 140R, 0.063W, 1%, 0402	MC00625W04021140R
Resistor, 120K, 0.063W, 1%, 0402	MC00625W04021120K	Resistor, 147K, 0.063W, 1%, 0402, Reel	MC00625W04021147K
Resistor, 120R, 0.063W, 1%, 0402, Reel	MC00625W04021120R	Resistor, 147K, 0.063W, 1%, 0402	MC00625W04021147K
Resistor, 120R, 0.063W, 1%, 0402	MC00625W04021120R	Resistor, 147R, 0.063W, 1%, 0402, Reel	MC00625W04021147R
Resistor, 121K, 0.063W, 1%, 0402, Reel	MC00625W04021121K	Resistor, 147R, 0.063W, 1%, 0402	MC00625W04021147R
Resistor, 121K, 0.063W, 1%, 0402	MC00625W04021121K	Resistor, 15K, 0.063W, 1%, 0402, Reel	MC00625W0402115K
Resistor, 121R, 0.063W, 1%, 0402, Reel	MC00625W04021121R	Resistor, 15K, 0.063W, 1%, 0402	MC00625W0402115K
Resistor, 121R, 0.063W, 1%, 0402	MC00625W04021121R	Resistor, 15R, 0.063W, 1%, 0402, Reel	MC00625W0402115R
Resistor, 127K, 0.063W, 1%, 0402, Reel	MC00625W04021127K	Resistor, 15R, 0.063W, 1%, 0402	MC00625W0402115R
Resistor, 127K, 0.063W, 1%, 0402	MC00625W04021127K	Resistor, 15K4, 0.063W, 1%, 0402, Reel	MC00625W0402115K4
Resistor, 127R, 0.063W, 1%, 0402, Reel	MC00625W04021127R	Resistor, 15K4, 0.063W, 1%, 0402	MC00625W0402115K4
Resistor, 127R, 0.063W, 1%, 0402	MC00625W04021127R	Resistor, 15R4, 0.063W, 1%, 0402, Reel	MC00625W0402115R4
Resistor, 13K, 0.063W, 1%, 0402, Reel	MC00625W0402113K	Resistor, 15R4, 0.063W, 1%, 0402	MC00625W0402115R4
Resistor, 13K, 0.063W, 1%, 0402	MC00625W0402113K	Resistor, 150K, 0.063W, 1%, 0402, Reel	MC00625W04021150K
Resistor, 13R, 0.063W, 1%, 0402, Reel	MC00625W0402113R	Resistor, 150K, 0.063W, 1%, 0402	MC00625W04021150K
Resistor, 13R, 0.063W, 1%, 0402	MC00625W0402113R	Resistor, 150R, 0.063W, 1%, 0402, Reel	MC00625W04021150R
Resistor, 13K3, 0.063W, 1%, 0402, Reel	MC00625W0402113K3	Resistor, 150R, 0.063W, 1%, 0402	MC00625W04021150R
Resistor, 13K3, 0.063W, 1%, 0402	MC00625W0402113K3	Resistor, 154K, 0.063W, 1%, 0402, Reel	MC00625W04021154K
Resistor, 13R3, 0.063W, 1%, 0402, Reel	MC00625W0402113R3	Resistor, 154K, 0.063W, 1%, 0402	MC00625W04021154K
Resistor, 13R3, 0.063W, 1%, 0402	MC00625W0402113R3	Resistor, 154R, 0.063W, 1%, 0402, Reel	MC00625W04021154R
Resistor, 130K, 0.063W, 1%, 0402, Reel	MC00625W04021130K	Resistor, 154R, 0.063W, 1%, 0402	MC00625W04021154R
Resistor, 130K, 0.063W, 1%, 0402	MC00625W04021130K	Resistor, 16K, 0.063W, 1%, 0402, Reel	MC00625W0402116K
Resistor, 130R, 0.063W, 1%, 0402, Reel	MC00625W04021130R	Resistor, 16K, 0.063W, 1%, 0402	MC00625W0402116K

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 16R, 0.063W, 1%, 0402, Reel	MC00625W0402116R	Resistor, 180K, 0.063W, 1%, 0402	MC00625W04021180K
Resistor, 16R, 0.063W, 1%, 0402	MC00625W0402116R	Resistor, 180R, 0.063W, 1%, 0402, Reel	MC00625W04021180R
Resistor, 16K2, 0.063W, 1%, 0402, Reel	MC00625W0402116K2	Resistor, 180R, 0.063W, 1%, 0402	MC00625W04021180R
Resistor, 16K2, 0.063W, 1%, 0402	MC00625W0402116K2	Resistor, 187K, 0.063W, 1%, 0402, Reel	MC00625W04021187K
Resistor, 16R2, 0.063W, 1%, 0402, Reel	MC00625W0402116R2	Resistor, 187K, 0.063W, 1%, 0402	MC00625W04021187K
Resistor, 16R2, 0.063W, 1%, 0402	MC00625W0402116R2	Resistor, 187R, 0.063W, 1%, 0402, Reel	MC00625W04021187R
Resistor, 16K9, 0.063W, 1%, 0402, Reel	MC00625W0402116K9	Resistor, 187R, 0.063W, 1%, 0402	MC00625W04021187R
Resistor, 16K9, 0.063W, 1%, 0402	MC00625W0402116K9	Resistor, 19K6, 0.063W, 1%, 0402, Reel	MC00625W0402119K6
Resistor, 16R9, 0.063W, 1%, 0402, Reel	MC00625W0402116R9	Resistor, 19K6, 0.063W, 1%, 0402	MC00625W0402119K6
Resistor, 16R9, 0.063W, 1%, 0402	MC00625W0402116R9	Resistor, 19R6, 0.063W, 1%, 0402, Reel	MC00625W0402119R6
Resistor, 160K, 0.063W, 1%, 0402, Reel	MC00625W04021160K	Resistor, 19R6, 0.063W, 1%, 0402	MC00625W0402119R6
Resistor, 160K, 0.063W, 1%, 0402	MC00625W04021160K	Resistor, 196K, 0.063W, 1%, 0402, Reel	MC00625W04021196K
Resistor, 160R, 0.063W, 1%, 0402, Reel	MC00625W04021160R	Resistor, 196K, 0.063W, 1%, 0402	MC00625W04021196K
Resistor, 160R, 0.063W, 1%, 0402	MC00625W04021160R	Resistor, 196R, 0.063W, 1%, 0402, Reel	MC00625W04021196R
Resistor, 162K, 0.063W, 1%, 0402, Reel	MC00625W04021162K	Resistor, 196R, 0.063W, 1%, 0402	MC00625W04021196R
Resistor, 162K, 0.063W, 1%, 0402	MC00625W04021162K	Resistor, 2K, 0.063W, 1%, 0402, Reel	MC00625W040212K
Resistor, 162R, 0.063W, 1%, 0402, Reel	MC00625W04021162R	Resistor, 2K, 0.063W, 1%, 0402	MC00625W040212K
Resistor, 162R, 0.063W, 1%, 0402	MC00625W04021162R	Resistor, 2M, 0.063W, 1%, 0402, Reel	MC00625W040212M00
Resistor, 169K, 0.063W, 1%, 0402, Reel	MC00625W04021169K	Resistor, 2M, 0.063W, 1%, 0402	MC00625W040212M00
Resistor, 169K, 0.063W, 1%, 0402	MC00625W04021169K	Resistor, 2R, 0.063W, 1%, 0402, Reel	MC00625W040212R0
Resistor, 169R, 0.063W, 1%, 0402, Reel	MC00625W04021169R	Resistor, 2R, 0.063W, 1%, 0402	MC00625W040212R0
Resistor, 169R, 0.063W, 1%, 0402	MC00625W04021169R	Resistor, 2K05, 0.063W, 1%, 0402, Reel	MC00625W040212K05
Resistor, 17K8, 0.063W, 1%, 0402, Reel	MC00625W0402117K8	Resistor, 2K05, 0.063W, 1%, 0402	MC00625W040212K05
Resistor, 17K8, 0.063W, 1%, 0402	MC00625W0402117K8	Resistor, 2K15, 0.063W, 1%, 0402, Reel	MC00625W040212K15
Resistor, 17R8, 0.063W, 1%, 0402, Reel	MC00625W0402117R8	Resistor, 2K15, 0.063W, 1%, 0402	MC00625W040212K15
Resistor, 17R8, 0.063W, 1%, 0402	MC00625W0402117R8	Resistor, 2K2, 0.063W, 1%, 0402, Reel	MC00625W040212K2
Resistor, 178K, 0.063W, 1%, 0402, Reel	MC00625W04021178K	Resistor, 2K2, 0.063W, 1%, 0402	MC00625W040212K2
Resistor, 178K, 0.063W, 1%, 0402	MC00625W04021178K	Resistor, 2M2, 0.063W, 1%, 0402, Reel	MC00625W040212M20
Resistor, 178R, 0.063W, 1%, 0402, Reel	MC00625W04021178R	Resistor, 2M2, 0.063W, 1%, 0402	MC00625W040212M20
Resistor, 178R, 0.063W, 1%, 0402	MC00625W04021178R	Resistor, 2R2, 0.063W, 1%, 0402, Reel	MC00625W040212R2
Resistor, 18K, 0.063W, 1%, 0402, Reel	MC00625W0402118K	Resistor, 2R2, 0.063W, 1%, 0402	MC00625W040212R2
Resistor, 18K, 0.063W, 1%, 0402	MC00625W0402118K	Resistor, 2K26, 0.063W, 1%, 0402, Reel	MC00625W040212K26
Resistor, 18R, 0.063W, 1%, 0402, Reel	MC00625W0402118R	Resistor, 2K26, 0.063W, 1%, 0402	MC00625W040212K26
Resistor, 18R, 0.063W, 1%, 0402	MC00625W0402118R	Resistor, 2K37, 0.063W, 1%, 0402, Reel	MC00625W040212K37
Resistor, 18K7, 0.063W, 1%, 0402, Reel	MC00625W0402118K7	Resistor, 2K37, 0.063W, 1%, 0402	MC00625W040212K37
Resistor, 18K7, 0.063W, 1%, 0402	MC00625W0402118K7	Resistor, 2K4, 0.063W, 1%, 0402, Reel	MC00625W040212K4
Resistor, 18R7, 0.063W, 1%, 0402, Reel	MC00625W0402118R7	Resistor, 2K4, 0.063W, 1%, 0402	MC00625W040212K4
Resistor, 18R7, 0.063W, 1%, 0402	MC00625W0402118R7	Resistor, 2M4, 0.063W, 1%, 0402, Reel	MC00625W040212M40
Resistor, 180K, 0.063W, 1%, 0402, Reel	MC00625W04021180K	Resistor, 2M4, 0.063W, 1%, 0402	MC00625W040212M40

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 2R4, 0.063W, 1%, 0402, Reel	MC00625W040212R40	Resistor, 205R, 0.063W, 1%, 0402	MC00625W04021205R
Resistor, 2R4, 0.063W, 1%, 0402	MC00625W040212R40	Resistor, 21K5, 0.063W, 1%, 0402, Reel	MC00625W0402121K5
Resistor, 2K49, 0.063W, 1%, 0402, Reel	MC00625W040212K49	Resistor, 21K5, 0.063W, 1%, 0402	MC00625W0402121K5
Resistor, 2K49, 0.063W, 1%, 0402	MC00625W040212K49	Resistor, 21R5, 0.063W, 1%, 0402, Reel	MC00625W0402121R5
Resistor, 2R49, 0.063W, 1%, 0402, Reel	MC00625W040212R49	Resistor, 21R5, 0.063W, 1%, 0402	MC00625W0402121R5
Resistor, 2R49, 0.063W, 1%, 0402	MC00625W040212R49	Resistor, 215K, 0.063W, 1%, 0402, Reel	MC00625W04021215K
Resistor, 2K61, 0.063W, 1%, 0402, Reel	MC00625W040212K61	Resistor, 215K, 0.063W, 1%, 0402	MC00625W04021215K
Resistor, 2K61, 0.063W, 1%, 0402	MC00625W040212K61	Resistor, 215R, 0.063W, 1%, 0402, Reel	MC00625W04021215R
Resistor, 2R61, 0.063W, 1%, 0402, Reel	MC00625W040212R61	Resistor, 215R, 0.063W, 1%, 0402	MC00625W04021215R
Resistor, 2R61, 0.063W, 1%, 0402	MC00625W040212R61	Resistor, 22K, 0.063W, 1%, 0402, Reel	MC00625W0402122K
Resistor, 2K7, 0.063W, 1%, 0402, Reel	MC00625W040212K7	Resistor, 22K, 0.063W, 1%, 0402	MC00625W0402122K
Resistor, 2K7, 0.063W, 1%, 0402	MC00625W040212K7	Resistor, 22R, 0.063W, 1%, 0402, Reel	MC00625W0402122R
Resistor, 2M7, 0.063W, 1%, 0402, Reel	MC00625W040212M70	Resistor, 22R, 0.063W, 1%, 0402	MC00625W0402122R
Resistor, 2M7, 0.063W, 1%, 0402	MC00625W040212M70	Resistor, 22K6, 0.063W, 1%, 0402, Reel	MC00625W0402122K6
Resistor, 2R7, 0.063W, 1%, 0402, Reel	MC00625W040212R70	Resistor, 22K6, 0.063W, 1%, 0402	MC00625W0402122K6
Resistor, 2R7, 0.063W, 1%, 0402	MC00625W040212R70	Resistor, 22R6, 0.063W, 1%, 0402, Reel	MC00625W0402122R6
Resistor, 2K74, 0.063W, 1%, 0402, Reel	MC00625W040212K74	Resistor, 22R6, 0.063W, 1%, 0402	MC00625W0402122R6
Resistor, 2K74, 0.063W, 1%, 0402	MC00625W040212K74	Resistor, 220K, 0.063W, 1%, 0402, Reel	MC00625W04021220K
Resistor, 2R74, 0.063W, 1%, 0402, Reel	MC00625W040212R74	Resistor, 220K, 0.063W, 1%, 0402	MC00625W04021220K
Resistor, 2R74, 0.063W, 1%, 0402	MC00625W040212R74	Resistor, 220R, 0.063W, 1%, 0402, Reel	MC00625W04021220R
Resistor, 2K87, 0.063W, 1%, 0402, Reel	MC00625W040212K87	Resistor, 220R, 0.063W, 1%, 0402	MC00625W04021220R
Resistor, 2K87, 0.063W, 1%, 0402	MC00625W040212K87	Resistor, 226K, 0.063W, 1%, 0402, Reel	MC00625W04021226K
Resistor, 2M87, 0.063W, 1%, 0402, Reel	MC00625W040212M87	Resistor, 226K, 0.063W, 1%, 0402	MC00625W04021226K
Resistor, 2M87, 0.063W, 1%, 0402	MC00625W040212M87	Resistor, 226R, 0.063W, 1%, 0402, Reel	MC00625W04021226R
Resistor, 20K, 0.063W, 1%, 0402, Reel	MC00625W0402120K	Resistor, 226R, 0.063W, 1%, 0402	MC00625W04021226R
Resistor, 20K, 0.063W, 1%, 0402	MC00625W0402120K	Resistor, 23K7, 0.063W, 1%, 0402, Reel	MC00625W0402123K7
Resistor, 20R, 0.063W, 1%, 0402, Reel	MC00625W0402120R	Resistor, 23K7, 0.063W, 1%, 0402	MC00625W0402123K7
Resistor, 20R, 0.063W, 1%, 0402	MC00625W0402120R	Resistor, 23R7, 0.063W, 1%, 0402, Reel	MC00625W0402123R7
Resistor, 20K5, 0.063W, 1%, 0402, Reel	MC00625W0402120K5	Resistor, 23R7, 0.063W, 1%, 0402	MC00625W0402123R7
Resistor, 20K5, 0.063W, 1%, 0402	MC00625W0402120K5	Resistor, 237K, 0.063W, 1%, 0402, Reel	MC00625W04021237K
Resistor, 20R5, 0.063W, 1%, 0402, Reel	MC00625W0402120R5	Resistor, 237K, 0.063W, 1%, 0402	MC00625W04021237K
Resistor, 20R5, 0.063W, 1%, 0402	MC00625W0402120R5	Resistor, 237R, 0.063W, 1%, 0402, Reel	MC00625W04021237R
Resistor, 200K, 0.063W, 1%, 0402, Reel	MC00625W04021200K	Resistor, 237R, 0.063W, 1%, 0402	MC00625W04021237R
Resistor, 200K, 0.063W, 1%, 0402	MC00625W04021200K	Resistor, 24K, 0.063W, 1%, 0402, Reel	MC00625W0402124K
Resistor, 200R, 0.063W, 1%, 0402, Reel	MC00625W04021200R	Resistor, 24K, 0.063W, 1%, 0402	MC00625W0402124K
Resistor, 200R, 0.063W, 1%, 0402	MC00625W04021200R	Resistor, 24R, 0.063W, 1%, 0402, Reel	MC00625W0402124R
Resistor, 205K, 0.063W, 1%, 0402, Reel	MC00625W04021205K	Resistor, 24R, 0.063W, 1%, 0402	MC00625W0402124R
Resistor, 205K, 0.063W, 1%, 0402	MC00625W04021205K	Resistor, 24K9, 0.063W, 1%, 0402, Reel	MC00625W0402124K9
Resistor, 205R, 0.063W, 1%, 0402, Reel	MC00625W04021205R	Resistor, 24K9, 0.063W, 1%, 0402	MC00625W0402124K9

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 24R9, 0.063W, 1%, 0402, Reel	MC00625W0402124R9	Resistor, 287K, 0.063W, 1%, 0402	MC00625W04021287K
Resistor, 24R9, 0.063W, 1%, 0402	MC00625W0402124R9	Resistor, 287R, 0.063W, 1%, 0402, Reel	MC00625W04021287R
Resistor, 240K, 0.063W, 1%, 0402, Reel	MC00625W04021240K	Resistor, 287R, 0.063W, 1%, 0402	MC00625W04021287R
Resistor, 240K, 0.063W, 1%, 0402	MC00625W04021240K	Resistor, 3K, 0.063W, 1%, 0402, Reel	MC00625W040213K
Resistor, 240R, 0.063W, 1%, 0402, Reel	MC00625W04021240R	Resistor, 3K, 0.063W, 1%, 0402	MC00625W040213K
Resistor, 240R, 0.063W, 1%, 0402	MC00625W04021240R	Resistor, 3M, 0.063W, 1%, 0402, Reel	MC00625W040213M00
Resistor, 249K, 0.063W, 1%, 0402, Reel	MC00625W04021249K	Resistor, 3M, 0.063W, 1%, 0402	MC00625W040213M00
Resistor, 249K, 0.063W, 1%, 0402	MC00625W04021249K	Resistor, 3R, 0.063W, 1%, 0402, Reel	MC00625W040213R0
Resistor, 249R, 0.063W, 1%, 0402, Reel	MC00625W04021249R	Resistor, 3R, 0.063W, 1%, 0402	MC00625W040213R0
Resistor, 249R, 0.063W, 1%, 0402	MC00625W04021249R	Resistor, 3K01, 0.063W, 1%, 0402, Reel	MC00625W040213K01
Resistor, 26K1, 0.063W, 1%, 0402, Reel	MC00625W0402126K1	Resistor, 3K01, 0.063W, 1%, 0402	MC00625W040213K01
Resistor, 26K1, 0.063W, 1%, 0402	MC00625W0402126K1	Resistor, 3M01, 0.063W, 1%, 0402, Reel	MC00625W040213M01
Resistor, 26R1, 0.063W, 1%, 0402, Reel	MC00625W0402126R1	Resistor, 3M01, 0.063W, 1%, 0402	MC00625W040213M01
Resistor, 26R1, 0.063W, 1%, 0402	MC00625W0402126R1	Resistor, 3K16, 0.063W, 1%, 0402, Reel	MC00625W040213K16
Resistor, 261K, 0.063W, 1%, 0402, Reel	MC00625W04021261K	Resistor, 3K16, 0.063W, 1%, 0402	MC00625W040213K16
Resistor, 261K, 0.063W, 1%, 0402	MC00625W04021261K	Resistor, 3R16, 0.063W, 1%, 0402, Reel	MC00625W040213R16
Resistor, 261R, 0.063W, 1%, 0402, Reel	MC00625W04021261R	Resistor, 3R16, 0.063W, 1%, 0402	MC00625W040213R16
Resistor, 261R, 0.063W, 1%, 0402	MC00625W04021261R	Resistor, 3K3, 0.063W, 1%, 0402, Reel	MC00625W040213K3
Resistor, 27K, 0.063W, 1%, 0402, Reel	MC00625W0402127K	Resistor, 3K3, 0.063W, 1%, 0402	MC00625W040213K3
Resistor, 27K, 0.063W, 1%, 0402	MC00625W0402127K	Resistor, 3M3, 0.063W, 1%, 0402, Reel	MC00625W040213M30
Resistor, 27R, 0.063W, 1%, 0402, Reel	MC00625W0402127R	Resistor, 3M3, 0.063W, 1%, 0402	MC00625W040213M30
Resistor, 27R, 0.063W, 1%, 0402	MC00625W0402127R	Resistor, 3R3, 0.063W, 1%, 0402, Reel	MC00625W040213R3
Resistor, 27K4, 0.063W, 1%, 0402, Reel	MC00625W0402127K4	Resistor, 3R3, 0.063W, 1%, 0402	MC00625W040213R3
Resistor, 27K4, 0.063W, 1%, 0402	MC00625W0402127K4	Resistor, 3K32, 0.063W, 1%, 0402, Reel	MC00625W040213K32
Resistor, 27R4, 0.063W, 1%, 0402, Reel	MC00625W0402127R4	Resistor, 3K32, 0.063W, 1%, 0402	MC00625W040213K32
Resistor, 27R4, 0.063W, 1%, 0402	MC00625W0402127R4	Resistor, 3M32, 0.063W, 1%, 0402, Reel	MC00625W040213M32
Resistor, 270K, 0.063W, 1%, 0402, Reel	MC00625W04021270K	Resistor, 3M32, 0.063W, 1%, 0402	MC00625W040213M32
Resistor, 270K, 0.063W, 1%, 0402	MC00625W04021270K	Resistor, 3R32, 0.063W, 1%, 0402, Reel	MC00625W040213R32
Resistor, 270R, 0.063W, 1%, 0402, Reel	MC00625W04021270R	Resistor, 3R32, 0.063W, 1%, 0402	MC00625W040213R32
Resistor, 270R, 0.063W, 1%, 0402	MC00625W04021270R	Resistor, 3K48, 0.063W, 1%, 0402, Reel	MC00625W040213K48
Resistor, 274K, 0.063W, 1%, 0402, Reel	MC00625W04021274K	Resistor, 3K48, 0.063W, 1%, 0402	MC00625W040213K48
Resistor, 274K, 0.063W, 1%, 0402	MC00625W04021274K	Resistor, 3K6, 0.063W, 1%, 0402, Reel	MC00625W040213K6
Resistor, 274R, 0.063W, 1%, 0402, Reel	MC00625W04021274R	Resistor, 3K6, 0.063W, 1%, 0402	MC00625W040213K6
Resistor, 274R, 0.063W, 1%, 0402	MC00625W04021274R	Resistor, 3M6, 0.063W, 1%, 0402, Reel	MC00625W040213M60
Resistor, 28K7, 0.063W, 1%, 0402, Reel	MC00625W0402128K7	Resistor, 3M6, 0.063W, 1%, 0402	MC00625W040213M60
Resistor, 28K7, 0.063W, 1%, 0402	MC00625W0402128K7	Resistor, 3R6, 0.063W, 1%, 0402, Reel	MC00625W040213R60
Resistor, 28R7, 0.063W, 1%, 0402, Reel	MC00625W0402128R7	Resistor, 3R6, 0.063W, 1%, 0402	MC00625W040213R60
Resistor, 28R7, 0.063W, 1%, 0402	MC00625W0402128R7	Resistor, 3K65, 0.063W, 1%, 0402, Reel	MC00625W040213K65
Resistor, 287K, 0.063W, 1%, 0402, Reel	MC00625W04021287K	Resistor, 3K65, 0.063W, 1%, 0402	MC00625W040213K65

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 3K83, 0.063W, 1%, 0402, Reel	MC00625W040213K83	Resistor, 33K2, 0.063W, 1%, 0402	MC00625W0402133K2
Resistor, 3K83, 0.063W, 1%, 0402	MC00625W040213K83	Resistor, 33R2, 0.063W, 1%, 0402, Reel	MC00625W0402133R2
Resistor, 3R83, 0.063W, 1%, 0402, Reel	MC00625W040213R83	Resistor, 33R2, 0.063W, 1%, 0402	MC00625W0402133R2
Resistor, 3R83, 0.063W, 1%, 0402	MC00625W040213R83	Resistor, 330K, 0.063W, 1%, 0402, Reel	MC00625W04021330K
Resistor, 3K9, 0.063W, 1%, 0402, Reel	MC00625W040213K9	Resistor, 330K, 0.063W, 1%, 0402	MC00625W04021330K
Resistor, 3K9, 0.063W, 1%, 0402	MC00625W040213K9	Resistor, 330R, 0.063W, 1%, 0402, Reel	MC00625W04021330R
Resistor, 3M9, 0.063W, 1%, 0402, Reel	MC00625W040213M90	Resistor, 330R, 0.063W, 1%, 0402	MC00625W04021330R
Resistor, 3M9, 0.063W, 1%, 0402	MC00625W040213M90	Resistor, 332K, 0.063W, 1%, 0402, Reel	MC00625W04021332K
Resistor, 3R9, 0.063W, 1%, 0402, Reel	MC00625W040213R90	Resistor, 332K, 0.063W, 1%, 0402	MC00625W04021332K
Resistor, 3R9, 0.063W, 1%, 0402	MC00625W040213R90	Resistor, 332R, 0.063W, 1%, 0402, Reel	MC00625W04021332R
Resistor, 30K, 0.063W, 1%, 0402, Reel	MC00625W0402130K	Resistor, 332R, 0.063W, 1%, 0402	MC00625W04021332R
Resistor, 30K, 0.063W, 1%, 0402	MC00625W0402130K	Resistor, 34K8, 0.063W, 1%, 0402, Reel	MC00625W0402134K8
Resistor, 30R, 0.063W, 1%, 0402, Reel	MC00625W0402130R	Resistor, 34K8, 0.063W, 1%, 0402	MC00625W0402134K8
Resistor, 30R, 0.063W, 1%, 0402	MC00625W0402130R	Resistor, 34R8, 0.063W, 1%, 0402, Reel	MC00625W0402134R8
Resistor, 30K1, 0.063W, 1%, 0402, Reel	MC00625W0402130K1	Resistor, 34R8, 0.063W, 1%, 0402	MC00625W0402134R8
Resistor, 30K1, 0.063W, 1%, 0402	MC00625W0402130K1	Resistor, 348K, 0.063W, 1%, 0402, Reel	MC00625W04021348K
Resistor, 30R1, 0.063W, 1%, 0402, Reel	MC00625W0402130R1	Resistor, 348K, 0.063W, 1%, 0402	MC00625W04021348K
Resistor, 30R1, 0.063W, 1%, 0402	MC00625W0402130R1	Resistor, 348R, 0.063W, 1%, 0402, Reel	MC00625W04021348R
Resistor, 300K, 0.063W, 1%, 0402, Reel	MC00625W04021300K	Resistor, 348R, 0.063W, 1%, 0402	MC00625W04021348R
Resistor, 300K, 0.063W, 1%, 0402	MC00625W04021300K	Resistor, 36K, 0.063W, 1%, 0402, Reel	MC00625W0402136K
Resistor, 300R, 0.063W, 1%, 0402, Reel	MC00625W04021300R	Resistor, 36K, 0.063W, 1%, 0402	MC00625W0402136K
Resistor, 300R, 0.063W, 1%, 0402	MC00625W04021300R	Resistor, 36R, 0.063W, 1%, 0402, Reel	MC00625W0402136R
Resistor, 301K, 0.063W, 1%, 0402, Reel	MC00625W04021301K	Resistor, 36R, 0.063W, 1%, 0402	MC00625W0402136R
Resistor, 301K, 0.063W, 1%, 0402	MC00625W04021301K	Resistor, 36K5, 0.063W, 1%, 0402, Reel	MC00625W0402136K5
Resistor, 301R, 0.063W, 1%, 0402, Reel	MC00625W04021301R	Resistor, 36K5, 0.063W, 1%, 0402	MC00625W0402136K5
Resistor, 301R, 0.063W, 1%, 0402	MC00625W04021301R	Resistor, 36R5, 0.063W, 1%, 0402, Reel	MC00625W0402136R5
Resistor, 31K6, 0.063W, 1%, 0402, Reel	MC00625W0402131K6	Resistor, 36R5, 0.063W, 1%, 0402	MC00625W0402136R5
Resistor, 31K6, 0.063W, 1%, 0402	MC00625W0402131K6	Resistor, 360K, 0.063W, 1%, 0402, Reel	MC00625W04021360K
Resistor, 31R6, 0.063W, 1%, 0402, Reel	MC00625W0402131R6	Resistor, 360K, 0.063W, 1%, 0402	MC00625W04021360K
Resistor, 31R6, 0.063W, 1%, 0402	MC00625W0402131R6	Resistor, 360R, 0.063W, 1%, 0402, Reel	MC00625W04021360R
Resistor, 316K, 0.063W, 1%, 0402, Reel	MC00625W04021316K	Resistor, 360R, 0.063W, 1%, 0402	MC00625W04021360R
Resistor, 316K, 0.063W, 1%, 0402	MC00625W04021316K	Resistor, 365K, 0.063W, 1%, 0402, Reel	MC00625W04021365K
Resistor, 316R, 0.063W, 1%, 0402, Reel	MC00625W04021316R	Resistor, 365K, 0.063W, 1%, 0402	MC00625W04021365K
Resistor, 316R, 0.063W, 1%, 0402	MC00625W04021316R	Resistor, 365R, 0.063W, 1%, 0402, Reel	MC00625W04021365R
Resistor, 33K, 0.063W, 1%, 0402, Reel	MC00625W0402133K	Resistor, 365R, 0.063W, 1%, 0402	MC00625W04021365R
Resistor, 33K, 0.063W, 1%, 0402	MC00625W0402133K	Resistor, 38K3, 0.063W, 1%, 0402, Reel	MC00625W0402138K3
Resistor, 33R, 0.063W, 1%, 0402, Reel	MC00625W0402133R	Resistor, 38K3, 0.063W, 1%, 0402	MC00625W0402138K3
Resistor, 33R, 0.063W, 1%, 0402	MC00625W0402133R	Resistor, 38R3, 0.063W, 1%, 0402, Reel	MC00625W0402138R3
Resistor, 33K2, 0.063W, 1%, 0402, Reel	MC00625W0402133K2	Resistor, 38R3, 0.063W, 1%, 0402	MC00625W0402138R3

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 383K, 0.063W, 1%, 0402, Reel	MC00625W04021383K	Resistor, 4K87, 0.063W, 1%, 0402	MC00625W040214K87
Resistor, 383K, 0.063W, 1%, 0402	MC00625W04021383K	Resistor, 4M87, 0.063W, 1%, 0402, Reel	MC00625W040214M87
Resistor, 383R, 0.063W, 1%, 0402, Reel	MC00625W04021383R	Resistor, 4M87, 0.063W, 1%, 0402	MC00625W040214M87
Resistor, 383R, 0.063W, 1%, 0402	MC00625W04021383R	Resistor, 4K99, 0.063W, 1%, 0402, Reel	MC00625W040214K99
Resistor, 39K, 0.063W, 1%, 0402, Reel	MC00625W0402139K	Resistor, 4K99, 0.063W, 1%, 0402	MC00625W040214K99
Resistor, 39K, 0.063W, 1%, 0402	MC00625W0402139K	Resistor, 40K2, 0.063W, 1%, 0402, Reel	MC00625W0402140K2
Resistor, 39R, 0.063W, 1%, 0402, Reel	MC00625W0402139R	Resistor, 40K2, 0.063W, 1%, 0402	MC00625W0402140K2
Resistor, 39R, 0.063W, 1%, 0402	MC00625W0402139R	Resistor, 40R2, 0.063W, 1%, 0402, Reel	MC00625W0402140R2
Resistor, 390K, 0.063W, 1%, 0402, Reel	MC00625W04021390K	Resistor, 40R2, 0.063W, 1%, 0402	MC00625W0402140R2
Resistor, 390K, 0.063W, 1%, 0402	MC00625W04021390K	Resistor, 402K, 0.063W, 1%, 0402, Reel	MC00625W04021402K
Resistor, 390R, 0.063W, 1%, 0402, Reel	MC00625W04021390R	Resistor, 402K, 0.063W, 1%, 0402	MC00625W04021402K
Resistor, 390R, 0.063W, 1%, 0402	MC00625W04021390R	Resistor, 402R, 0.063W, 1%, 0402, Reel	MC00625W04021402R
Resistor, 4K02, 0.063W, 1%, 0402, Reel	MC00625W040214K02	Resistor, 402R, 0.063W, 1%, 0402	MC00625W04021402R
Resistor, 4K02, 0.063W, 1%, 0402	MC00625W040214K02	Resistor, 42K2, 0.063W, 1%, 0402, Reel	MC00625W0402142K2
Resistor, 4M02, 0.063W, 1%, 0402, Reel	MC00625W040214M02	Resistor, 42K2, 0.063W, 1%, 0402	MC00625W0402142K2
Resistor, 4M02, 0.063W, 1%, 0402	MC00625W040214M02	Resistor, 42R2, 0.063W, 1%, 0402, Reel	MC00625W0402142R2
Resistor, 4K22, 0.063W, 1%, 0402, Reel	MC00625W040214K22	Resistor, 42R2, 0.063W, 1%, 0402	MC00625W0402142R2
Resistor, 4K22, 0.063W, 1%, 0402	MC00625W040214K22	Resistor, 422K, 0.063W, 1%, 0402, Reel	MC00625W04021422K
Resistor, 4R22, 0.063W, 1%, 0402, Reel	MC00625W040214R22	Resistor, 422K, 0.063W, 1%, 0402	MC00625W04021422K
Resistor, 4R22, 0.063W, 1%, 0402	MC00625W040214R22	Resistor, 422R, 0.063W, 1%, 0402, Reel	MC00625W04021422R
Resistor, 4K3, 0.063W, 1%, 0402, Reel	MC00625W040214K3	Resistor, 422R, 0.063W, 1%, 0402	MC00625W04021422R
Resistor, 4K3, 0.063W, 1%, 0402	MC00625W040214K3	Resistor, 43K, 0.063W, 1%, 0402, Reel	MC00625W0402143K
Resistor, 4M3, 0.063W, 1%, 0402, Reel	MC00625W040214M30	Resistor, 43K, 0.063W, 1%, 0402	MC00625W0402143K
Resistor, 4M3, 0.063W, 1%, 0402	MC00625W040214M30	Resistor, 43R, 0.063W, 1%, 0402, Reel	MC00625W0402143R
Resistor, 4R3, 0.063W, 1%, 0402, Reel	MC00625W040214R30	Resistor, 43R, 0.063W, 1%, 0402	MC00625W0402143R
Resistor, 4R3, 0.063W, 1%, 0402	MC00625W040214R30	Resistor, 430K, 0.063W, 1%, 0402, Reel	MC00625W04021430K
Resistor, 4K42, 0.063W, 1%, 0402, Reel	MC00625W040214K42	Resistor, 430K, 0.063W, 1%, 0402	MC00625W04021430K
Resistor, 4K42, 0.063W, 1%, 0402	MC00625W040214K42	Resistor, 430R, 0.063W, 1%, 0402, Reel	MC00625W04021430R
Resistor, 4K64, 0.063W, 1%, 0402, Reel	MC00625W040214K64	Resistor, 430R, 0.063W, 1%, 0402	MC00625W04021430R
Resistor, 4K64, 0.063W, 1%, 0402	MC00625W040214K64	Resistor, 44K2, 0.063W, 1%, 0402, Reel	MC00625W0402144K2
Resistor, 4K7, 0.063W, 1%, 0402, Reel	MC00625W040214K7	Resistor, 44K2, 0.063W, 1%, 0402	MC00625W0402144K2
Resistor, 4K7, 0.063W, 1%, 0402	MC00625W040214K7	Resistor, 44R2, 0.063W, 1%, 0402, Reel	MC00625W0402144R2
Resistor, 4M7, 0.063W, 1%, 0402, Reel	MC00625W040214M70	Resistor, 44R2, 0.063W, 1%, 0402	MC00625W0402144R2
Resistor, 4M7, 0.063W, 1%, 0402	MC00625W040214M70	Resistor, 442K, 0.063W, 1%, 0402, Reel	MC00625W04021442K
Resistor, 4R7, 0.063W, 1%, 0402, Reel	MC00625W040214R7	Resistor, 442K, 0.063W, 1%, 0402	MC00625W04021442K
Resistor, 4R7, 0.063W, 1%, 0402	MC00625W040214R7	Resistor, 442R, 0.063W, 1%, 0402, Reel	MC00625W04021442R
Resistor, 4K75, 0.063W, 1%, 0402, Reel	MC00625W040214K75	Resistor, 442R, 0.063W, 1%, 0402	MC00625W04021442R
Resistor, 4K75, 0.063W, 1%, 0402	MC00625W040214K75	Resistor, 46K4, 0.063W, 1%, 0402, Reel	MC00625W0402146K4
Resistor, 4K87, 0.063W, 1%, 0402, Reel	MC00625W040214K87	Resistor, 46K4, 0.063W, 1%, 0402	MC00625W0402146K4

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 46R4, 0.063W, 1%, 0402, Reel	MC00625W0402146R4	Resistor, 5K11, 0.063W, 1%, 0402	MC00625W040215K11
Resistor, 46R4, 0.063W, 1%, 0402	MC00625W0402146R4	Resistor, 5R11, 0.063W, 1%, 0402, Reel	MC00625W040215R11
Resistor, 464K, 0.063W, 1%, 0402, Reel	MC00625W04021464K	Resistor, 5R11, 0.063W, 1%, 0402	MC00625W040215R11
Resistor, 464K, 0.063W, 1%, 0402	MC00625W04021464K	Resistor, 5K36, 0.063W, 1%, 0402, Reel	MC00625W040215K36
Resistor, 464R, 0.063W, 1%, 0402, Reel	MC00625W04021464R	Resistor, 5K36, 0.063W, 1%, 0402	MC00625W040215K36
Resistor, 464R, 0.063W, 1%, 0402	MC00625W04021464R	Resistor, 5M36, 0.063W, 1%, 0402, Reel	MC00625W040215M36
Resistor, 47K, 0.063W, 1%, 0402, Reel	MC00625W0402147K	Resistor, 5M36, 0.063W, 1%, 0402	MC00625W040215M36
Resistor, 47K, 0.063W, 1%, 0402	MC00625W0402147K	Resistor, 5R36, 0.063W, 1%, 0402, Reel	MC00625W040215R36
Resistor, 47R, 0.063W, 1%, 0402, Reel	MC00625W0402147R	Resistor, 5R36, 0.063W, 1%, 0402	MC00625W040215R36
Resistor, 47R, 0.063W, 1%, 0402	MC00625W0402147R	Resistor, 5K6, 0.063W, 1%, 0402, Reel	MC00625W040215K6
Resistor, 47K5, 0.063W, 1%, 0402, Reel	MC00625W0402147K5	Resistor, 5K6, 0.063W, 1%, 0402	MC00625W040215K6
Resistor, 47K5, 0.063W, 1%, 0402	MC00625W0402147K5	Resistor, 5M6, 0.063W, 1%, 0402, Reel	MC00625W040215M6
Resistor, 470K, 0.063W, 1%, 0402, Reel	MC00625W04021470K	Resistor, 5M6, 0.063W, 1%, 0402	MC00625W040215M6
Resistor, 470K, 0.063W, 1%, 0402	MC00625W04021470K	Resistor, 5R6, 0.063W, 1%, 0402, Reel	MC00625W040215R6
Resistor, 470R, 0.063W, 1%, 0402, Reel	MC00625W04021470R	Resistor, 5R6, 0.063W, 1%, 0402	MC00625W040215R6
Resistor, 470R, 0.063W, 1%, 0402	MC00625W04021470R	Resistor, 5K62, 0.063W, 1%, 0402, Reel	MC00625W040215K62
Resistor, 475R, 0.063W, 1%, 0402, Reel	MC00625W04021475R	Resistor, 5K62, 0.063W, 1%, 0402	MC00625W040215K62
Resistor, 475R, 0.063W, 1%, 0402	MC00625W04021475R	Resistor, 5R62, 0.063W, 1%, 0402, Reel	MC00625W040215R62
Resistor, 48K7, 0.063W, 1%, 0402, Reel	MC00625W0402148K7	Resistor, 5R62, 0.063W, 1%, 0402	MC00625W040215R62
Resistor, 48K7, 0.063W, 1%, 0402	MC00625W0402148K7	Resistor, 5K9, 0.063W, 1%, 0402, Reel	MC00625W040215K9
Resistor, 48R7, 0.063W, 1%, 0402, Reel	MC00625W0402148R7	Resistor, 5K9, 0.063W, 1%, 0402	MC00625W040215K9
Resistor, 48R7, 0.063W, 1%, 0402	MC00625W0402148R7	Resistor, 51K, 0.063W, 1%, 0402, Reel	MC00625W0402151K
Resistor, 487K, 0.063W, 1%, 0402, Reel	MC00625W04021487K	Resistor, 51K, 0.063W, 1%, 0402	MC00625W0402151K
Resistor, 487K, 0.063W, 1%, 0402	MC00625W04021487K	Resistor, 51R, 0.063W, 1%, 0402, Reel	MC00625W0402151R
Resistor, 487R, 0.063W, 1%, 0402, Reel	MC00625W04021487R	Resistor, 51R, 0.063W, 1%, 0402	MC00625W0402151R
Resistor, 487R, 0.063W, 1%, 0402	MC00625W04021487R	Resistor, 51K1, 0.063W, 1%, 0402, Reel	MC00625W0402151K1
Resistor, 49K9, 0.063W, 1%, 0402, Reel	MC00625W0402149K9	Resistor, 51K1, 0.063W, 1%, 0402	MC00625W0402151K1
Resistor, 49K9, 0.063W, 1%, 0402	MC00625W0402149K9	Resistor, 51R1, 0.063W, 1%, 0402, Reel	MC00625W0402151R1
Resistor, 49R9, 0.063W, 1%, 0402, Reel	MC00625W0402149R9	Resistor, 51R1, 0.063W, 1%, 0402	MC00625W0402151R1
Resistor, 49R9, 0.063W, 1%, 0402	MC00625W0402149R9	Resistor, 510K, 0.063W, 1%, 0402, Reel	MC00625W04021510K
Resistor, 499K, 0.063W, 1%, 0402, Reel	MC00625W04021499K	Resistor, 510K, 0.063W, 1%, 0402	MC00625W04021510K
Resistor, 499K, 0.063W, 1%, 0402	MC00625W04021499K	Resistor, 510R, 0.063W, 1%, 0402, Reel	MC00625W04021510R
Resistor, 5K1, 0.063W, 1%, 0402, Reel	MC00625W040215K1	Resistor, 510R, 0.063W, 1%, 0402	MC00625W04021510R
Resistor, 5K1, 0.063W, 1%, 0402	MC00625W040215K1	Resistor, 511K, 0.063W, 1%, 0402, Reel	MC00625W04021511K
Resistor, 5M1, 0.063W, 1%, 0402, Reel	MC00625W040215M10	Resistor, 511K, 0.063W, 1%, 0402	MC00625W04021511K
Resistor, 5M1, 0.063W, 1%, 0402	MC00625W040215M10	Resistor, 511R, 0.063W, 1%, 0402, Reel	MC00625W04021511R
Resistor, 5R1, 0.063W, 1%, 0402, Reel	MC00625W040215R10	Resistor, 511R, 0.063W, 1%, 0402	MC00625W04021511R
Resistor, 5R1, 0.063W, 1%, 0402	MC00625W040215R10	Resistor, 53K6, 0.063W, 1%, 0402, Reel	MC00625W0402153K6
Resistor, 5K11, 0.063W, 1%, 0402, Reel	MC00625W040215K11	Resistor, 53K6, 0.063W, 1%, 0402	MC00625W0402153K6

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 53R6, 0.063W, 1%, 0402, Reel	MC00625W0402153R6	Resistor, 6R2, 0.063W, 1%, 0402	MC00625W040216R20
Resistor, 53R6, 0.063W, 1%, 0402	MC00625W0402153R6	Resistor, 6K49, 0.063W, 1%, 0402, Reel	MC00625W040216K49
Resistor, 536K, 0.063W, 1%, 0402, Reel	MC00625W04021536K	Resistor, 6K49, 0.063W, 1%, 0402	MC00625W040216K49
Resistor, 536K, 0.063W, 1%, 0402	MC00625W04021536K	Resistor, 6K8, 0.063W, 1%, 0402, Reel	MC00625W040216K8
Resistor, 536R, 0.063W, 1%, 0402, Reel	MC00625W04021536R	Resistor, 6K8, 0.063W, 1%, 0402	MC00625W040216K8
Resistor, 536R, 0.063W, 1%, 0402	MC00625W04021536R	Resistor, 6M8, 0.063W, 1%, 0402, Reel	MC00625W040216M80
Resistor, 56K, 0.063W, 1%, 0402, Reel	MC00625W0402156K	Resistor, 6M8, 0.063W, 1%, 0402	MC00625W040216M80
Resistor, 56K, 0.063W, 1%, 0402	MC00625W0402156K	Resistor, 6R8, 0.063W, 1%, 0402, Reel	MC00625W040216R8
Resistor, 56R, 0.063W, 1%, 0402, Reel	MC00625W0402156R	Resistor, 6R8, 0.063W, 1%, 0402	MC00625W040216R8
Resistor, 56R, 0.063W, 1%, 0402	MC00625W0402156R	Resistor, 6K81, 0.063W, 1%, 0402, Reel	MC00625W040216K81
Resistor, 56K2, 0.063W, 1%, 0402, Reel	MC00625W0402156K2	Resistor, 6K81, 0.063W, 1%, 0402	MC00625W040216K81
Resistor, 56K2, 0.063W, 1%, 0402	MC00625W0402156K2	Resistor, 61K9, 0.063W, 1%, 0402, Reel	MC00625W0402161K9
Resistor, 56R2, 0.063W, 1%, 0402, Reel	MC00625W0402156R2	Resistor, 61K9, 0.063W, 1%, 0402	MC00625W0402161K9
Resistor, 56R2, 0.063W, 1%, 0402	MC00625W0402156R2	Resistor, 61R9, 0.063W, 1%, 0402, Reel	MC00625W0402161R9
Resistor, 560K, 0.063W, 1%, 0402, Reel	MC00625W04021560K	Resistor, 61R9, 0.063W, 1%, 0402	MC00625W0402161R9
Resistor, 560K, 0.063W, 1%, 0402	MC00625W04021560K	Resistor, 619K, 0.063W, 1%, 0402, Reel	MC00625W04021619K
Resistor, 560R, 0.063W, 1%, 0402, Reel	MC00625W04021560R	Resistor, 619K, 0.063W, 1%, 0402	MC00625W04021619K
Resistor, 560R, 0.063W, 1%, 0402	MC00625W04021560R	Resistor, 619R, 0.063W, 1%, 0402, Reel	MC00625W04021619R
Resistor, 562K, 0.063W, 1%, 0402, Reel	MC00625W04021562K	Resistor, 619R, 0.063W, 1%, 0402	MC00625W04021619R
Resistor, 562K, 0.063W, 1%, 0402	MC00625W04021562K	Resistor, 62K, 0.063W, 1%, 0402, Reel	MC00625W0402162K
Resistor, 562R, 0.063W, 1%, 0402, Reel	MC00625W04021562R	Resistor, 62K, 0.063W, 1%, 0402	MC00625W0402162K
Resistor, 562R, 0.063W, 1%, 0402	MC00625W04021562R	Resistor, 62R, 0.063W, 1%, 0402, Reel	MC00625W0402162R
Resistor, 59K, 0.063W, 1%, 0402, Reel	MC00625W0402159K	Resistor, 62R, 0.063W, 1%, 0402	MC00625W0402162R
Resistor, 59K, 0.063W, 1%, 0402	MC00625W0402159K	Resistor, 620K, 0.063W, 1%, 0402, Reel	MC00625W04021620K
Resistor, 59R, 0.063W, 1%, 0402, Reel	MC00625W0402159R	Resistor, 620K, 0.063W, 1%, 0402	MC00625W04021620K
Resistor, 59R, 0.063W, 1%, 0402	MC00625W0402159R	Resistor, 620R, 0.063W, 1%, 0402, Reel	MC00625W04021620R
Resistor, 590K, 0.063W, 1%, 0402, Reel	MC00625W04021590K	Resistor, 620R, 0.063W, 1%, 0402	MC00625W04021620R
Resistor, 590K, 0.063W, 1%, 0402	MC00625W04021590K	Resistor, 64K9, 0.063W, 1%, 0402, Reel	MC00625W0402164K9
Resistor, 590R, 0.063W, 1%, 0402, Reel	MC00625W04021590R	Resistor, 64K9, 0.063W, 1%, 0402	MC00625W0402164K9
Resistor, 590R, 0.063W, 1%, 0402	MC00625W04021590R	Resistor, 64R9, 0.063W, 1%, 0402, Reel	MC00625W0402164R9
Resistor, 6K04, 0.063W, 1%, 0402, Reel	MC00625W040216K04	Resistor, 64R9, 0.063W, 1%, 0402	MC00625W0402164R9
Resistor, 6K04, 0.063W, 1%, 0402	MC00625W040216K04	Resistor, 649K, 0.063W, 1%, 0402, Reel	MC00625W04021649K
Resistor, 6K19, 0.063W, 1%, 0402, Reel	MC00625W040216K19	Resistor, 649K, 0.063W, 1%, 0402	MC00625W04021649K
Resistor, 6K19, 0.063W, 1%, 0402	MC00625W040216K19	Resistor, 649R, 0.063W, 1%, 0402, Reel	MC00625W04021649R
Resistor, 6K2, 0.063W, 1%, 0402, Reel	MC00625W040216K2	Resistor, 649R, 0.063W, 1%, 0402	MC00625W04021649R
Resistor, 6K2, 0.063W, 1%, 0402	MC00625W040216K2	Resistor, 68K, 0.063W, 1%, 0402, Reel	MC00625W0402168K
Resistor, 6M2, 0.063W, 1%, 0402, Reel	MC00625W040216M20	Resistor, 68K, 0.063W, 1%, 0402	MC00625W0402168K
Resistor, 6M2, 0.063W, 1%, 0402	MC00625W040216M20	Resistor, 68R, 0.063W, 1%, 0402, Reel	MC00625W0402168R
Resistor, 6R2, 0.063W, 1%, 0402, Reel	MC00625W040216R20	Resistor, 68R, 0.063W, 1%, 0402	MC00625W0402168R

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 68K1, 0.063W, 1%, 0402, Reel	MC00625W0402168K1	Resistor, 78K7, 0.063W, 1%, 0402	MC00625W0402178K7
Resistor, 68K1, 0.063W, 1%, 0402	MC00625W0402168K1	Resistor, 78R7, 0.063W, 1%, 0402, Reel	MC00625W0402178R7
Resistor, 68R1, 0.063W, 1%, 0402, Reel	MC00625W0402168R1	Resistor, 78R7, 0.063W, 1%, 0402	MC00625W0402178R7
Resistor, 68R1, 0.063W, 1%, 0402	MC00625W0402168R1	Resistor, 787K, 0.063W, 1%, 0402, Reel	MC00625W04021787K
Resistor, 680K, 0.063W, 1%, 0402, Reel	MC00625W04021680K	Resistor, 787K, 0.063W, 1%, 0402	MC00625W04021787K
Resistor, 680K, 0.063W, 1%, 0402	MC00625W04021680K	Resistor, 787R, 0.063W, 1%, 0402, Reel	MC00625W04021787R
Resistor, 680R, 0.063W, 1%, 0402, Reel	MC00625W04021680R	Resistor, 787R, 0.063W, 1%, 0402	MC00625W04021787R
Resistor, 680R, 0.063W, 1%, 0402	MC00625W04021680R	Resistor, 8K2, 0.063W, 1%, 0402, Reel	MC00625W040218K2
Resistor, 681K, 0.063W, 1%, 0402, Reel	MC00625W04021681K	Resistor, 8K2, 0.063W, 1%, 0402	MC00625W040218K2
Resistor, 681K, 0.063W, 1%, 0402	MC00625W04021681K	Resistor, 8M2, 0.063W, 1%, 0402, Reel	MC00625W040218M20
Resistor, 681R, 0.063W, 1%, 0402, Reel	MC00625W04021681R	Resistor, 8M2, 0.063W, 1%, 0402	MC00625W040218M20
Resistor, 681R, 0.063W, 1%, 0402	MC00625W04021681R	Resistor, 8R2, 0.063W, 1%, 0402, Reel	MC00625W040218R20
Resistor, 7K15, 0.063W, 1%, 0402, Reel	MC00625W040217K15	Resistor, 8R2, 0.063W, 1%, 0402	MC00625W040218R20
Resistor, 7K15, 0.063W, 1%, 0402	MC00625W040217K15	Resistor, 8K25, 0.063W, 1%, 0402, Reel	MC00625W040218K25
Resistor, 7K5, 0.063W, 1%, 0402, Reel	MC00625W040217K5	Resistor, 8K25, 0.063W, 1%, 0402	MC00625W040218K25
Resistor, 7K5, 0.063W, 1%, 0402	MC00625W040217K5	Resistor, 8K66, 0.063W, 1%, 0402, Reel	MC00625W040218K66
Resistor, 7M5, 0.063W, 1%, 0402, Reel	MC00625W040217M50	Resistor, 8K66, 0.063W, 1%, 0402	MC00625W040218K66
Resistor, 7M5, 0.063W, 1%, 0402	MC00625W040217M50	Resistor, 82K, 0.063W, 1%, 0402, Reel	MC00625W0402182K
Resistor, 7R5, 0.063W, 1%, 0402, Reel	MC00625W040217R50	Resistor, 82K, 0.063W, 1%, 0402	MC00625W0402182K
Resistor, 7R5, 0.063W, 1%, 0402	MC00625W040217R50	Resistor, 82R, 0.063W, 1%, 0402, Reel	MC00625W0402182R
Resistor, 7K87, 0.063W, 1%, 0402, Reel	MC00625W040217K87	Resistor, 82R, 0.063W, 1%, 0402	MC00625W0402182R
Resistor, 7K87, 0.063W, 1%, 0402	MC00625W040217K87	Resistor, 82K5, 0.063W, 1%, 0402, Reel	MC00625W0402182K5
Resistor, 71K5, 0.063W, 1%, 0402, Reel	MC00625W0402171K5	Resistor, 82K5, 0.063W, 1%, 0402	MC00625W0402182K5
Resistor, 71K5, 0.063W, 1%, 0402	MC00625W0402171K5	Resistor, 82R5, 0.063W, 1%, 0402, Reel	MC00625W0402182R5
Resistor, 71R5, 0.063W, 1%, 0402, Reel	MC00625W0402171R5	Resistor, 82R5, 0.063W, 1%, 0402	MC00625W0402182R5
Resistor, 71R5, 0.063W, 1%, 0402	MC00625W0402171R5	Resistor, 820K, 0.063W, 1%, 0402, Reel	MC00625W04021820K
Resistor, 715K, 0.063W, 1%, 0402, Reel	MC00625W04021715K	Resistor, 820K, 0.063W, 1%, 0402	MC00625W04021820K
Resistor, 715K, 0.063W, 1%, 0402	MC00625W04021715K	Resistor, 820R, 0.063W, 1%, 0402, Reel	MC00625W04021820R
Resistor, 715R, 0.063W, 1%, 0402, Reel	MC00625W04021715R	Resistor, 820R, 0.063W, 1%, 0402	MC00625W04021820R
Resistor, 715R, 0.063W, 1%, 0402	MC00625W04021715R	Resistor, 825K, 0.063W, 1%, 0402, Reel	MC00625W04021825K
Resistor, 75K, 0.063W, 1%, 0402, Reel	MC00625W0402175K	Resistor, 825K, 0.063W, 1%, 0402	MC00625W04021825K
Resistor, 75K, 0.063W, 1%, 0402	MC00625W0402175K	Resistor, 825R, 0.063W, 1%, 0402, Reel	MC00625W04021825R
Resistor, 75R, 0.063W, 1%, 0402, Reel	MC00625W0402175R	Resistor, 825R, 0.063W, 1%, 0402	MC00625W04021825R
Resistor, 75R, 0.063W, 1%, 0402	MC00625W0402175R	Resistor, 86K6, 0.063W, 1%, 0402, Reel	MC00625W0402186K6
Resistor, 750K, 0.063W, 1%, 0402, Reel	MC00625W04021750K	Resistor, 86K6, 0.063W, 1%, 0402	MC00625W0402186K6
Resistor, 750K, 0.063W, 1%, 0402	MC00625W04021750K	Resistor, 86R6, 0.063W, 1%, 0402, Reel	MC00625W0402186R6
Resistor, 750R, 0.063W, 1%, 0402, Reel	MC00625W04021750R	Resistor, 86R6, 0.063W, 1%, 0402	MC00625W0402186R6
Resistor, 750R, 0.063W, 1%, 0402	MC00625W04021750R	Resistor, 866K, 0.063W, 1%, 0402, Reel	MC00625W04021866K
Resistor, 78K7, 0.063W, 1%, 0402, Reel	MC00625W0402178K7	Resistor, 866K, 0.063W, 1%, 0402	MC00625W04021866K

Thick Film Chip Resistor 0402



Description	Part Number	Description	Part Number
Resistor, 866R, 0.063W, 1%, 0402, Reel	MC00625W04021866R	Resistor, 909R, 0.063W, 1%, 0402, Reel	MC00625W04021909R
Resistor, 866R, 0.063W, 1%, 0402	MC00625W04021866R	Resistor, 909R, 0.063W, 1%, 0402	MC00625W04021909R
Resistor, 9K09, 0.063W, 1%, 0402, Reel	MC00625W040219K09	Resistor, 91K, 0.063W, 1%, 0402, Reel	MC00625W0402191K
Resistor, 9K09, 0.063W, 1%, 0402	MC00625W040219K09	Resistor, 91K, 0.063W, 1%, 0402	MC00625W0402191K
Resistor, 9K1, 0.063W, 1%, 0402, Reel	MC00625W040219K1	Resistor, 91R, 0.063W, 1%, 0402, Reel	MC00625W0402191R
Resistor, 9K1, 0.063W, 1%, 0402	MC00625W040219K1	Resistor, 91R, 0.063W, 1%, 0402	MC00625W0402191R
Resistor, 9M1, 0.063W, 1%, 0402, Reel	MC00625W040219M10	Resistor, 910K, 0.063W, 1%, 0402, Reel	MC00625W04021910K
Resistor, 9M1, 0.063W, 1%, 0402	MC00625W040219M10	Resistor, 910K, 0.063W, 1%, 0402	MC00625W04021910K
Resistor, 9R1, 0.063W, 1%, 0402, Reel	MC00625W040219R10	Resistor, 910R, 0.063W, 1%, 0402, Reel	MC00625W04021910R
Resistor, 9R1, 0.063W, 1%, 0402	MC00625W040219R10	Resistor, 910R, 0.063W, 1%, 0402	MC00625W04021910R
Resistor, 9K53, 0.063W, 1%, 0402, Reel	MC00625W040219K53	Resistor, 95K3, 0.063W, 1%, 0402, Reel	MC00625W0402195K3
Resistor, 9K53, 0.063W, 1%, 0402	MC00625W040219K53	Resistor, 95K3, 0.063W, 1%, 0402	MC00625W0402195K3
Resistor, 90K9, 0.063W, 1%, 0402, Reel	MC00625W0402190K9	Resistor, 95R3, 0.063W, 1%, 0402, Reel	MC00625W0402195R3
Resistor, 90K9, 0.063W, 1%, 0402	MC00625W0402190K9	Resistor, 95R3, 0.063W, 1%, 0402	MC00625W0402195R3
Resistor, 90R9, 0.063W, 1%, 0402, Reel	MC00625W0402190R9	Resistor, 953K, 0.063W, 1%, 0402, Reel	MC00625W04021953K
Resistor, 90R9, 0.063W, 1%, 0402	MC00625W0402190R9	Resistor, 953K, 0.063W, 1%, 0402	MC00625W04021953K
Resistor, 909K, 0.063W, 1%, 0402, Reel	MC00625W04021909K	Resistor, 953R, 0.063W, 1%, 0402, Reel	MC00625W04021953R
Resistor, 909K, 0.063W, 1%, 0402	MC00625W04021909K	Resistor, 953R, 0.063W, 1%, 0402	MC00625W04021953R

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.