


Item no.: 2092-1302  
 Product description: 2 POLE PIN SPACING 5 MM / 0.197 IN



Produkt kann von Bild abweichen / product may differ

Packing unit 200 pieces

RoHS compliant

Color	light gray
pole count	2
Height	15.4 mm
Height	0.606 in
Width	10 mm
Width	0.394 in
Depth	13.6 mm
Depth	0.535 in
Pin spacing from	5 mm
Pin spacing from	0.197 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Material group	I

Customs Tariff No.

85366990

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected