



Bezels

Bezel Mount Meters


Hoyt 5% Moving Magnet Meters



Bezel Mount

2000 SERIES BEZELS

Window (HW) & Bezel (HB) Series




Window Mount

Bezels

HOYT 250 Degree

Bezels Available




Bezel Mount The Hoyt bezels are available in sizes 2-1/2", 3-1/2", and 4-1/2" and offer a custom look to the panel surface. The bezel is molded from high strength plastic material which protects the meter from damage. This design features the zero adjuster within the window envelope therefore negating the requirement for drilling an additional hole. The optional bezel is available for use with the surface case styles and includes necessary mounting hardware.

C-8041 (overall size 1 - 3/4" x 1 - 5/32") for 3125/26

C-8370 (overall size 2 - 5/16" x 3 - 27/32") for 3135/36

G-8397 (overall size 3" x 5 - 1/4") for 3145/46

Edgewise Meters



Bezel Mount Meters

Bezels for mounting rectangular custom series models 2018, 2025/26, 2035/36, and 2045/46 behind the panel are sturdy, die cast black metal.

Bezel mount meters may be ordered with optional quick mount positive locking tabs. This series has clear polystyrene cases standard, but acrylic or high impact polycarbonate case are available in some models.



2000 SERIES BEZELS

Bezel Part Numbers

C-7052 (overall size 2" x 1-3/16") for 2018

C-7036 (overall size 3-1/8" x 1-23/32") for 2025/26

C-7048 (overall size 3-7/8" x 2-9/32") for 2035/36

C-7030 (overall size 4-31/32" x 2-29/32") for 2045/46